Product data sheet

Specification





servo motor BMI 1-phase - keyed IP65 single turn - 131072 p/t - brake

BMI0703T31F

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,367.87 USD

Main

| Range Compatibility | Lexium 32i |
|---------------------------|------------------------------|
| Product Or Component Type | Servo motor with power stage |
| Device Short Name | BMI |

Complementary Maximum Mechanical Speed

| Maximum Mechanical Speed | 8000 rpm |
|---------------------------|--|
| [Us] Rated Supply Voltage | 115230 V - 1510 % |
| Supply Voltage Limits | 100240 V |
| Phase | Single phase |
| Supply Frequency | 50/60 Hz - 55 % |
| Network Frequency Limits | 47.563 Hz |
| Emc Filter | Integrated |
| Continuous Output Current | 3.5 A 8 kHz |
| Output Current 3S Peak | 10.5 A 230 V 3 s |
| Continuous Stall Current | 3.5 A |
| Continuous Stall Torque | 30.09 lbf.in (3.4 N.m) 115230 V single phase |
| Peak Stall Torque | 76.12 lbf.in (8.6 N.m) 115 V single phase 76.12 lbf.in (8.6 N.m) 230 V single phase |
| Nominal Output Power | 700 W 230 V single phase 400 W 115 V single phase |
| Nominal Torque | 25.67 lbf.in (2.9 N.m) 115 V single phase 19.47 lbf.in (2.2 N.m) 230 V single phase |
| Nominal Speed | 3200 rpm 230 V single phase 1400 rpm 115 V single phase |
| Maximum Current Irms | 17.8 A 115 V, single phase 17.8 A 230 V, single phase |
| Product Compatibility | Drive control unit LXM32i CANopen Drive control unit LXM32i EtherCAT |
| Shaft End | Keyed |
| Second Shaft | Without second shaft end |
| Shaft Diameter | 0.55 in (14 mm) |
| Shaft Length | 1.18 in (30 mm) |
| Key Width | 0.20 in (5 mm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Feedback Type | Absolute single turn SinCos Hiperface |
|---------------------------------------|--|
| Speed Feedback Resolution | 131072 points/turn |
| Holding Brake | With |
| Holding Torque | 26.55 lbf.in (3 N.m) holding brake |
| Mounting Support | International standard flange |
| Motor Flange Size | 2.76 in (70 mm) |
| Electrical Connection | Printed circuit board connector |
| Torque Constant | 0.81 N.m/A 68 °F (20 °C) |
| Back Emf Constant | 54.44 V/krpm 68 °F (20 °C) |
| Number Of Motor Poles | 10 |
| Rotor Inertia | 1.78 kg.cm² |
| Stator Resistance | 2.58 Ohm 68 °F (20 °C) |
| Stator Inductance | 2.28 mH 68 °F (20 °C) |
| Stator Electrical Time Constant | 0.88 ms 68 °F (20 °C) |
| Maximum Radial Force Fr | 730 N 1000 rpm 580 N 2000 rpm 510 N 3000 rpm 460 N 4000 rpm 430 N 5000 rpm 400 N 6000 rpm |
| Maximum Axial Force Fa | 0.2 x Fr |
| Brake Pull-In Power | 5 W |
| Type Of Cooling | Natural convection |
| Length | 13.35 in (339 mm) |
| Number Of Motor Stacks | 3 |
| Centring Collar Diameter | 2.36 in (60 mm) |
| Centring Collar Depth | 0.10 in (2.5 mm) |
| Number Of Mounting Holes | 4 |
| Mounting Holes Diameter | 0.22 in (5.5 mm) |
| Circle Diameter Of The Mounting Holes | 2.953.23 in (7582 mm) |
| Distance Shaft Shoulder-Flange | 0.10 in (2.5 mm) |

Environment

Ip Degree Of Protection IP65

Ordering and shipping details

| Category | US1PC5618287 |
|-------------------|---------------|
| Discount Schedule | PC56 |
| Gtin | 3606485376851 |
| Returnability | No |
| Country Of Origin | DE |

Packing Units

Unit Type Of Package 1 PCE

| Number Of Units In Package 1 | 1 |
|------------------------------|-----------------------|
| Package 1 Height | 9.84 in (25.0 cm) |
| Package 1 Width | 7.32 in (18.6 cm) |
| Package 1 Length | 21.65 in (55.0 cm) |
| Package 1 Weight | 14.33 lb(US) (6.5 kg) |

Contractual warranty

Warranty 18 months

Sustainability Green Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Mercury Free | |
|----------|----------------------------|-----|
| | Rohs Exemption Information | Yes |
| ② | Pvc Free | |


Certifications & Standards

| Reach Regulation | REACh Declaration | | |
|---------------------------|---|--|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) | | |
| China Rohs Regulation | China RoHS declaration | | |
| Environmental Disclosure | Product Environmental Profile | | |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. | | |
| Circularity Profile | End of Life Information | | |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov | | |
| | | | |

Dimensions Drawings

External Dimensions

With Standard Braking Resistor



- (1) Module for supply voltage
- (2) I/O module
- (3) Standard braking resistor


Dimensions in mm

| W | Н | L | |
|----|-----|-----|--|
| 99 | 187 | 360 | |

Dimensions in in.

| W | Н | L | |
|------|------|-------|--|
| 3,90 | 7,36 | 14,17 | |

Mounting type B



- (1) Module for supply voltage
- (2) I/O module

BMI0703T31F

(3) Standard braking resistor


| Dimensions | in | mm |
|------------|----|----|
| | | |

| W | Н | L |
|----|-------|-----|
| 99 | 138,5 | 409 |

Dimensions in in.

| W | Н | L |
|------|------|------|
| 3,90 | 5,45 | 16,1 |

With External Braking Resistor



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

Dimensions in mm

| W | Н | L |
|----|-----|-----|
| 99 | 187 | 372 |


Dimensions in in.

| W | Н | L | | | |
|------|------|-------|--|--|--|
| 3,90 | 7,36 | 14,65 | | | |

Mounting type D

Product data sheet

BMI0703T31F




- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

Dimensions in mm

| W | Н | L |
|----|-----|-----|
| 99 | 160 | 409 |

Dimensions in in.

| D | | | | | |
|------|-----|------|--|--|--|
| W | Н | L | | | |
| 3,90 | 6,3 | 16,1 | | | |



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor


Dimensions in mm

| W | Н | L | | |
|----|-----|-----|--|--|
| 99 | 187 | 399 | | |

Dimensions in in.

| W | Н | L | | |
|------|------|-------|--|--|
| 3,90 | 7,36 | 15,71 | | |

Mounting type F



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

Dimensions in mm

| W | Н | L | | |
|----|-----|-----|--|--|
| 99 | 180 | 409 | | |


Dimensions in in.

| W | Н | L |
|------|------|------|
| 3,90 | 7,09 | 16,1 |

Performance Curves

Performance Curves

Torque/Speed Curves with 115 V Single Phase Supply Voltage




- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

| | | Power | At Speed | With Torque |
|-------------------------|---|-------|----------|-------------|
| max. Peak Power | | 889 W | 1360 rpm | 6.24 N.m |
| max Cont. Power (Drive) | • | 501 W | 1680 rpm | 2.85 N.m |

Performance Curves

Torque/Speed Curves with 230 V Single Phase Supply Voltage



- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

| | | Power | At Speed | With Torque |
|-------------------------|---|--------|----------|-------------|
| max. Peak Power | | 2314 W | 2800 rpm | 7.89 N.m |
| max Cont. Power (Drive) | • | 738 W | 3600 rpm | 1.96 N.m |