Product data sheet

Specifications





IEC contactor, TeSys Deca, nonreversing, 9A, 5HP at 480VAC, up to 100kA SCCR, 3 phase, 3 NO, 120VAC 50/60Hz coil, bulk pack

LC1D09G7TQ

Product availability: Stock - Normally stocked in distribution facility

Price*: 112.80 USD

Main

mann	
Range	TeSys TeSys Deca
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-3 AC-1 AC-3e
Poles Description	ЗР
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC
[le] Rated Operational Current	9 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit 25 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit 9 A (at <140 °F (60 °C)) at <= 440 V AC AC-3e for power circuit
[Uc] Control Circuit Voltage	120 V AC 50/60 Hz

Complementary

· · · · · · · · · · · · · · · · · ·		
Motor Power Kw	2.2 kW at 220230 V AC 50/60 Hz 4 kW at 380400 V AC 50/60 Hz 4 kW at 415440 V AC 50/60 Hz 5.5 kW at 500 V AC 50/60 Hz 5.5 kW at 660690 V AC 50/60 Hz	
Maximum Horse Power Rating	0.5 hp at 115 V AC 50/60 Hz for 1 phase motors 1 hp at 230/240 V AC 50/60 Hz for 1 phase motors 2 hp at 200/208 V AC 50/60 Hz for 3 phase motors 2 hp at 230/240 V AC 50/60 Hz for 3 phase motors 5 hp at 460/480 V AC 50/60 Hz for 3 phase motors 7.5 hp at 575/600 V AC 50/60 Hz for 3 phase motors	
Compatibility Code	LC1D	
Pole Contact Composition	3 NO	
Protective Cover	With	
[Ith] Conventional Free Air Thermal Current	10 A (at 140 °F (60 °C)) for signalling circuit 25 A (at 140 °F (60 °C)) for power circuit	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Irms Rated Making Capacity	250 A at 440 V for power circuit conforming to IEC 60947
	140 A AC for signalling circuit conforming to IEC 60947-5-1
	250 A DC for signalling circuit conforming to IEC 60947-5-1
Rated Breaking Capacity	250 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand	100 A - 1 s for signalling circuit
Current	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
	105 A 104 °F (40 °C) - 10 s for power circuit
	210 A 104 °F (40 °C) - 1 s for power circuit
	30 A 104 °F (40 °C) - 10 min for power circuit
	61 A 104 °F (40 °C) - 1 min for power circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
	25 A gG at <= 690 V coordination type 1 for power circuit
	20 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2.5 mOhm - Ith 25 A 50 Hz for power circuit
Power Dissipation Per Pole	1.56 W AC-1
·	0.2 W AC-3
	0.2 W AC-3e
[Li] Potod Insulation Voltage	
[Ui] Rated Insulation Voltage	Power circuit 690 V IEC 60947-4-1
	Power circuit 600 V CSA
	Power circuit 600 V UL
	Signalling circuit 600 V CSA
	Signalling circuit 600 V UL Signalling circuit 690 V IEC 60947-1
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	15 Mcycles
Electrical Durability	0.6 Mcycles 25 A AC-1 <= 440 V
,	2 Mcycles 9 A AC-3 <= 440 V
	2 Mcycles 9 A AC-3e <= 440 V
Control Circuit Type	AC 50/60 Hz
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	
Control Circuit Voltage Limits	0.30.6 Uc -40158 °F (-4070 °C) drop-out AC 50/60 Hz
	0.81.1 Uc -40140 °F (-4060 °C) operational AC 50 Hz
	0.851.1 Uc -40140 °F (-4060 °C) operational AC 60 Hz
	11.1 Uc 140158 °F (6070 °C) operational AC 50/60 Hz
Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 68 °F (20 °C))
	70 VA 50 Hz cos phi 0.75 (at 68 °F (20 °C))
Hold In Dowon Consumption to Ma	7 5 \ / A 20 \ \=
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C)) 7 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat Dissipation	23 W at 50/60 Hz
Operating Time	4 10 mo opening
	419 ms opening
	1222 ms closing
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)

Control circuit: screw clamp terminals 1 0.000.01 in ² (14 mm ²) - cable stiffness:
flexible without cable end
Control circuit: screw clamp terminals 2 0.000.01 in ² (14 mm ²) - cable stiffness:
flexible without cable end
Control circuit: screw clamp terminals 1 0.000.01 in ² (14 mm ²) - cable stiffness: flexible with cable end
Control circuit: screw clamp terminals 2 0.000.00 in ² (12.5 mm ²) - cable stiffness:
flexible with cable end
Control circuit: screw clamp terminals 1 0.000.01 in ² (14 mm ²) - cable stiffness:
solid
Control circuit: screw clamp terminals 2 0.000.01 in ² (14 mm ²) - cable stiffness:
solid
Power circuit: screw clamp terminals 1 0.000.01 in ² (14 mm ²) - cable stiffness:
flexible without cable end
Power circuit: screw clamp terminals 2 0.000.01 in ² (14 mm ²) - cable stiffness:
flexible without cable end
Power circuit: screw clamp terminals 1 0.000.01 in ² (14 mm ²) - cable stiffness:
flexible with cable end
Power circuit: screw clamp terminals 2 0.000.00 in ² (12.5 mm ²) - cable stiffness:
flexible with cable end
Power circuit: screw clamp terminals 1 0.000.01 in ² (14 mm ²) - cable stiffness:
solid
Power circuit: screw clamp terminals 2 0.000.01 in ² (14 mm ²) - cable stiffness:
solid
Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm
Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2
Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm
Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2
Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2
Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2
1 NO + 1 NC
Mechanically linked 1 NO + 1 NC IEC 60947-5-1
Mirror contact 1 NC IEC 60947-4-1
25400 Hz
17 V for signalling circuit
5 mA for signalling circuit
> 10 MOhm for signalling circuit
1.5 ms on de-energisation between NC and NO contact
1.5 ms on energisation between NC and NO contact
Rail
Plate

Environment

Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1
Product Certifications	BV CCC CSA DNV EAC GL LROS (Lloyds register of shipping) UL RINA UKCA
Ip Degree Of Protection	IP20 front face IEC 60529
Climatic Withstand	IACS E10 exposure to damp heat IEC 60947-1 Annex Q category D exposure to damp heat

Permissible Ambient Air Temperature Around The Device	-40140 °F (-4060 °C) 140158 °F (6070 °C) with derating
Operating Altitude	09842.52 ft (03000 m)
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open 2 Gn, 5300 Hz) Vibrations contactor closed 4 Gn, 5300 Hz) Shocks contactor open 10 Gn for 11 ms) Shocks contactor closed 15 Gn for 11 ms)
Height	3.03 in (77 mm)
Width	1.77 in (45 mm)
Depth	3.39 in (86 mm)
Net Weight	0.71 lb(US) (0.32 kg)

Ordering and shipping details

Category	US10I1222354
Discount Schedule	0112
Gtin	3606480191152
Returnability	Yes
Country Of Origin	US

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.91 in (15.0 cm)
Package 1 Width	11.81 in (30.0 cm)
Package 1 Length	15.75 in (40.0 cm)
Package 1 Weight	0.74 lb(US) (0.337 kg)
Unit Type Of Package 2	S02
Number Of Units In Package 2	24
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	18.83 lb(US) (8.543 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov