Product data sheet

Specification





AC servo motor BSH, Lexium 05, 2.83N.m, 6000rpm, untapped shaft, without brake, IP65

BSH0703T21A2A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,875.00 USD

Main

Product Or Component Type	Servo motor							
Device Short Name	BSH							
Maximum Mechanical Speed	8000 rpm							
Continuous Stall Torque	24.78 lbf.in (2.8 N.m) LXM05AD28M2, 200240 V, single phase							
	24.78 lbf.in (2.8 N.m) LXM05BD28M2, 200240 V, single phase							
	24.78 lbf.in (2.8 N.m) LXM05CD28M2, 200240 V, single phase							
	23.01 lbf.in (2.6 N.m) LXM32.D18M2 6 A, 230 V, single phase							
	25.05 lbf.in (2.83 N.m) LXM15LD28M3, 230 V, three phase							
	24.78 lbf.in (2.8 N.m) LXM05AD28F1, 110120 V, single phase							
	24.78 lbf.in (2.8 N.m) LXM05AD42M3X, 200240 V, three phase							
	24.78 lbf.in (2.8 N.m) LXM05BD28F1, 110120 V, single phase							
	24.78 lbf.in (2.8 N.m) LXM05BD42M3X, 200240 V, three phase							
	24.78 lbf.in (2.8 N.m) LXM05CD28F1, 110120 V, single phase							
	24.78 lbf.in (2.8 N.m) LXM05CD42M3X, 200240 V, three phase							
Peak Stall Torque	65.32 lbf.in (7.38 N.m) LXM05AD28F1, 110120 V, single phase							
	65.32 lbf.in (7.38 N.m) LXM05AD28M2, 200240 V, single phase							
	65.32 lbf.in (7.38 N.m) LXM05BD28F1, 110120 V, single phase							
	65.32 lbf.in (7.38 N.m) LXM05BD28M2, 200240 V, single phase							
	65.32 lbf.in (7.38 N.m) LXM05CD28F1, 110120 V, single phase							
	65.32 lbf.in (7.38 N.m) LXM05CD28M2, 200240 V, single phase							
	65.50 lbf.in (7.4 N.m) LXM32.D18M2 6 A, 230 V, single phase							
	65.32 lbf.in (7.38 N.m) LXM15LD28M3, 230 V, three phase							
	90.72 lbf.in (10.25 N.m) LXM05AD42M3X, 200240 V, three phase							
	90.72 lbf.in (10.25 N.m) LXM05BD42M3X, 200240 V, three phase							
	90.72 lbf.in (10.25 N.m) LXM05CD42M3X, 200240 V, three phase							
Nominal Output Power	750 W LXM05AD28M2, 200240 V, single phase							
	750 W LXM05BD28M2, 200240 V, single phase							
	750 W LXM05CD28M2, 200240 V, single phase							
	750 W LXM05AD28F1, 110120 V, single phase							
	750 W LXM05BD28F1, 110120 V, single phase							
	750 W LXM05CD28F1, 110120 V, single phase							
	900 W LXM32.D18M2 6 A, 230 V, single phase							
	1250 W LXM15LD28M3, 230 V, three phase							
	750 W LXM05AD42M3X, 200240 V, three phase							
	750 W LXM05BD42M3X, 200240 V, three phase							
	750 W LXM05CD42M3X, 200240 V, three phase							
Nominal Torque	21.24 lbf.in (2.4 N.m) LXM05AD28M2, 200240 V, single phase							
	21.24 lbf.in (2.4 N.m) LXM05BD28M2, 200240 V, single phase							
	21.24 lbf.in (2.4 N.m) LXM05CD28M2, 200240 V, single phase							
	21.24 lbf.in (2.4 N.m) LXM05AD28F1, 110120 V, single phase							
	21.24 lbf.in (2.4 N.m) LXM05BD28F1, 110120 V, single phase							
	21.24 lbf.in (2.4 N.m) LXM05CD28F1, 110120 V, single phase							
	18.59 lbf.in (2.1 N.m) LXM32.D18M2 6 A, 230 V, single phase							
	17.70 lbf.in (2 N.m) LXM15LD28M3, 230 V, three phase							
	21.24 lbf.in (2.4 N.m) LXM05AD42M3X, 200240 V, three phase							
	21.24 lbf.in (2.4 N.m) LXM05BD42M3X, 200240 V, three phase							
	21.24 lbf.in (2.4 N.m) LXM05CD42M3X, 200240 V, three phase							

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Nominal Speed	3000 rpm LXM05AD28M2, 200240 V, single phase 3000 rpm LXM05BD28M2, 200240 V, single phase 3000 rpm LXM05CD28M2, 200240 V, single phase 3000 rpm LXM05AD42M3X, 200240 V, three phase 3000 rpm LXM05BD42M3X, 200240 V, three phase 3000 rpm LXM05CD42M3X, 200240 V, three phase 3000 rpm LXM05CD42M3X, 200240 V, three phase 3000 rpm LXM05AD28F1, 110120 V, single phase 3000 rpm LXM05BD28F1, 110120 V, single phase 3000 rpm LXM05CD28F1, 110120 V, single phase 4000 rpm LXM32.D18M2 6 A, 230 V, single phase 6000 rpm LXM15LD28M3, 230 V, three phase
Product Compatibility	LXM05AD28F1 110120 V single phase LXM05AD28M2 200240 V single phase LXM05BD28F1 110120 V single phase LXM05BD28M2 200240 V single phase LXM05CD28F1 110120 V single phase LXM05CD28F1 110120 V single phase LXM05CD28M2 200240 V single phase LXM05CD18M2 230 V single phase LXM32.D18M2 230 V single phase LXM05AD42M3X 200240 V three phase LXM05BD42M3X 200240 V three phase LXM05CD42M3X 200240 V three phase LXM05CD42M3X 200240 V three phase
Shaft End	Untapped
Ip Degree Of Protection	IP65 standard IP67 with IP67 kit
Speed Feedback Resolution	131072 points/turn
Holding Brake	Without
Mounting Support	International standard flange
Electrical Connection	Rotatable right-angled connectors
Complementary Range Compatibility	Lexium 05 Lexium 15 Lexium 32
Supply Voltage Max	480 V
Phase	Three phase
Continuous Stall Current	7 A
Maximum Continuous Power	1.7 W
Maximum Current Irms	18 A LXM32.D18M2 30.9 A LXM15LD28M3 29.2 A LXM05AD28F1 29.2 A LXM05AD28M2 29.2 A LXM05AD42M3X 29.2 A LXM05BD28F1 29.2 A LXM05BD28M2 29.2 A LXM05BD42M3X 29.2 A LXM05BD42M3X 29.2 A LXM05CD28F1 29.2 A LXM05CD28F1 29.2 A LXM05CD28M2 29.2 A LXM05CD42M3X
Maximum Permanent Current	29.2 A
Switching Frequency	8 kHz
Second Shaft	Without second shaft end
Shaft Diameter	0.55 in (14 mm)
Shaft Length	1.18 in (30 mm)
Feedback Type	Single turn SinCos Hiperface
Motor Flange Size	2.76 in (70 mm)
Number Of Motor Stacks	3

Torque Constant	0.44 N.m/A 248 °F (120 °C)						
Back Emf Constant	29 V/krpm 248 °F (120 °C)						
Number Of Motor Poles	6						
Rotor Inertia	0.58 kg.cm ²						
Stator Resistance	0.91 Ohm 68 °F (20 °C)						
Stator Inductance	4.4 mH 68 °F (20 °C)						
Stator Electrical Time Constant	4.84 ms 68 °F (20 °C)						
Maximum Radial Force Fr	400 N 6000 rpm						
	430 N 5000 rpm						
	460 N 4000 rpm						
	510 N 3000 rpm						
	580 N 2000 rpm						
	730 N 1000 rpm						
Maximum Axial Force Fa	0.2 x Fr						
Type Of Cooling	Natural convection						
Length	8.66 in (220 mm)						
Centring Collar Diameter	2.36 in (60 mm)						
Centring Collar Depth	0.10 in (2.5 mm)						
Number Of Mounting Holes	4						
Mounting Holes Diameter	0.22 in (5.5 mm)						
Circle Diameter Of The Mounting Holes	3.23 in (82 mm)						
Net Weight	7.98 lb(US) (3.62 kg)						

Ordering and shipping details

Category	US1PC5318282
Discount Schedule	PC53
Gtin	3389118137615
Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.84 in (12.3 cm)
Package 1 Width	5.04 in (12.8 cm)
Package 1 Length	14.84 in (37.7 cm)
Package 1 Weight	7.94 lb(US) (3.6 kg)

Contractual warranty

Warranty 18 months

Sustainability Green Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

BSH0703T21A2A

Dimensions Drawings

Servo Motors Dimensions

Example with Straight Connectors



- a: Power supply for servo motor brake
- **b**: Power supply for servo motor encoder
- (1) M4 screw
- (2) Shaft end, keyed slot (optional)

Dimensions in mm

		Rotatable connector	•	c (without	c (with	c1	c2	сЗ	h	h1	Ø	Ø1 for
b1	b2	b1	b2	brake)	brake)							screws
39.5	25.5	39.5	39.5	220	254	30	20	5	5 N9	3 ^{+0.1} 0	14 k6	M5 x 12.5

Dimensions in in.

Straigh	ctors	angled	connectors (witho		c (with brake)	с1	c2	сЗ	h	h1	Ø	Ø1 for screws
b1	b2	b1	b2	2.0								
1.55	1.00	1.55	1.55	8.66	10.00	1.18	0.78	0.19	0.20 N9	0.12 ^{+0.004} 0	0.55 k6	M5 x 0.49

Product data sheet


BSH0703T21A2A

Performance Curves

230 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D18M2 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque