Product data sheet

Specification





IEC contactor, TeSys Deca, nonreversing, 18A, 10HP at 480VAC, up to 100kA SCCR, 3 phase, 3 NO, low consumption 24VDC coil

LC1D18BL

Product availability: Stock - Normally stocked in distribution facility

Price*: 204.00 USD

Main

Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Motor control Resistive load
Utilisation Category	AC-1 AC-3 AC-4 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC
[le] Rated Operational Current	18 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit 32 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit 18 A (at <140 °F (60 °C)) at <= 440 V AC AC-3e for power circuit
[Uc] Control Circuit Voltage	24 V DC

Complementary

Motor Power Kw	4 kW at 220230 V AC 50/60 Hz (AC-3)			
	7.5 kW at 380400 V AC 50/60 Hz (AC-3)			
	9 kW at 415440 V AC 50/60 Hz (AC-3)			
	10 kW at 500 V AC 50/60 Hz (AC-3)			
	10 kW at 660690 V AC 50/60 Hz (AC-3)			
	4 kW at 400 V AC 50/60 Hz (AC-4)			
	4 kW at 220230 V AC 50/60 Hz (AC-3e)			
	7.5 kW at 380400 V AC 50/60 Hz (AC-3e)			
	9 kW at 415440 V AC 50/60 Hz (AC-3e)			
	10 kW at 500 V AC 50/60 Hz (AC-3e)			
	10 kW at 660690 V AC 50/60 Hz (AC-3e)			
Maximum Horse Power Rating	1 hp at 115 V AC 50/60 Hz for 1 phase motors			
	3 hp at 230/240 V AC 50/60 Hz for 1 phase motors			
	5 hp at 200/208 V AC 50/60 Hz for 3 phase motors			
	5 hp at 230/240 V AC 50/60 Hz for 3 phase motors			
	10 hp at 460/480 V AC 50/60 Hz for 3 phase motors			
	15 hp at 575/600 V AC 50/60 Hz for 3 phase motors			
Compatibility Code	LC1D			
Pole Contact Composition	3 NO			
Protective Cover	With			

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[Ith] Conventional Free Air Thermal Current	10 A (at 140 °F (60 °C)) for signalling circuit 32 A (at 140 °F (60 °C)) for power circuit				
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 300 A at 440 V for power circuit conforming to IEC 60947				
Rated Breaking Capacity	300 A at 440 V for power circuit conforming to IEC 60947				
[Icw] Rated Short-Time Withstand Current	145 A 104 °F (40 °C) - 10 s for power circuit 240 A 104 °F (40 °C) - 1 s for power circuit 40 A 104 °F (40 °C) - 10 min for power circuit 84 A 104 °F (40 °C) - 1 min for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit				
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 50 A gG at <= 690 V coordination type 1 for power circuit 35 A gG at <= 690 V coordination type 2 for power circuit				
Average Impedance	2.5 mOhm - Ith 32 A 50 Hz for power circuit				
Power Dissipation Per Pole	2.5 W AC-1 0.8 W AC-3 0.8 W AC-3e				
[Ui] Rated Insulation Voltage	Power circuit 690 V IEC 60947-4-1 Power circuit 600 V CSA Power circuit 600 V UL Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA Signalling circuit 600 V UL				
Overvoltage Category	III				
Overvoltage Category Pollution Degree	3				
Pollution Degree [Uimp] Rated Impulse Withstand	3				
Pollution Degree [Uimp] Rated Impulse Withstand Voltage	3 6 kV IEC 60947 B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1				
Pollution Degree [Uimp] Rated Impulse Withstand Voltage Safety Reliability Level	3 6 kV IEC 60947 B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1				
Pollution Degree [Uimp] Rated Impulse Withstand Voltage Safety Reliability Level Mechanical Durability	3 6 kV IEC 60947 B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1 30 Mcycles 1.65 Mcycles 18 A AC-3 <= 440 V 1 Mcycles 32 A AC-1 <= 440 V				
Pollution Degree [Uimp] Rated Impulse Withstand Voltage Safety Reliability Level Mechanical Durability Electrical Durability	3 6 kV IEC 60947 B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1 30 Mcycles 1.65 Mcycles 18 A AC-3 <= 440 V 1 Mcycles 32 A AC-1 <= 440 V 1.65 Mcycles 18 A AC-3e <= 440 V				
Pollution Degree [Uimp] Rated Impulse Withstand Voltage Safety Reliability Level Mechanical Durability Electrical Durability Control Circuit Type	3 6 kV IEC 60947 B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1 30 Mcycles 1.65 Mcycles 18 A AC-3 <= 440 V 1 Mcycles 32 A AC-1 <= 440 V 1.65 Mcycles 18 A AC-3e <= 440 V DC low consumption				
Pollution Degree [Uimp] Rated Impulse Withstand Voltage Safety Reliability Level Mechanical Durability Electrical Durability Control Circuit Type Coil Technology	3 6 kV IEC 60947 B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1 30 Mcycles 1.65 Mcycles 18 A AC-3 <= 440 V 1 Mcycles 32 A AC-1 <= 440 V 1.65 Mcycles 18 A AC-3e <= 440 V DC low consumption Built-in bidirectional peak limiting diode suppressor 0.10.3 Uc -40158 °F (-4070 °C) drop-out DC 0.81.25 Uc -40140 °F (-4060 °C) operational DC				
Pollution Degree [Uimp] Rated Impulse Withstand Voltage Safety Reliability Level Mechanical Durability Electrical Durability Control Circuit Type Coil Technology Control Circuit Voltage Limits	3 6 kV IEC 60947 B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1 30 Mcycles 1.65 Mcycles 18 A AC-3 <= 440 V 1 Mcycles 32 A AC-1 <= 440 V 1.65 Mcycles 18 A AC-3e <= 440 V DC low consumption Built-in bidirectional peak limiting diode suppressor 0.10.3 Uc -40158 °F (-4070 °C) drop-out DC 0.81.25 Uc -40140 °F (-4060 °C) operational DC 11.25 Uc 140158 °F (6070 °C) operational DC				
Pollution Degree [Uimp] Rated Impulse Withstand Voltage Safety Reliability Level Mechanical Durability Electrical Durability Control Circuit Type Coil Technology Control Circuit Voltage Limits	3 6 kV IEC 60947 B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1 30 Mcycles 1.65 Mcycles 18 A AC-3 <= 440 V 1 Mcycles 32 A AC-1 <= 440 V 1.65 Mcycles 18 A AC-3e <= 440 V DC low consumption Built-in bidirectional peak limiting diode suppressor 0.10.3 Uc -40158 °F (-4070 °C) drop-out DC 0.81.25 Uc -40140 °F (-4060 °C) operational DC 11.25 Uc 140158 °F (6070 °C) operational DC 2.4 W 68 °F (20 °C))				
Pollution Degree [Uimp] Rated Impulse Withstand Voltage Safety Reliability Level Mechanical Durability Electrical Durability Control Circuit Type Coil Technology Control Circuit Voltage Limits Inrush Power In W Hold-In Power Consumption In W	3 6 kV IEC 60947 B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1 30 Mcycles 1.65 Mcycles 18 A AC-3 <= 440 V 1 Mcycles 32 A AC-1 <= 440 V 1.65 Mcycles 18 A AC-3e <= 440 V DC low consumption Built-in bidirectional peak limiting diode suppressor 0.10.3 Uc -40158 °F (-4070 °C) drop-out DC 0.81.25 Uc -40140 °F (-4060 °C) operational DC 11.25 Uc 140158 °F (6070 °C) operational DC 2.4 W 68 °F (20 °C) 2.4 W 68 °F (20 °C) 77 ±15 % ms closing				

Connections - Terminals	Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible without cable end	
	Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness:	
	flexible without cable end	
	Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible with cable end	
	Control circuit: screw clamp terminals 2 0.000.00 in² (12.5 mm²) - cable stiffness: flexible with cable end	
	Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: solid without cable end	
	Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: solid without cable end	
	Power circuit: screw clamp terminals 1 0.000.01 in² (1.56 mm²) - cable stiffness:	
	flexible without cable end Power circuit: screw clamp terminals 2 0.000.01 in² (1.56 mm²) - cable stiffness:	
	flexible without cable end Power circuit: screw clamp terminals 1 0.000.01 in² (16 mm²) - cable stiffness:	
	flexible with cable end	
	Power circuit: screw clamp terminals 2 0.000.01 in ² (14 mm ²) - cable stiffness: flexible with cable end	
	Power circuit: screw clamp terminals 1 0.000.01 in² (1.56 mm²) - cable stiffness:	
	solid without cable end Power circuit: screw clamp terminals 2 0.000.01 in² (1.56 mm²) - cable stiffness:	
	solid without cable end	
Tightening Torque	Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2	
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm	
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2	
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2 Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2	
Auxiliary Contact Composition	1 NO + 1 NC	
Auxiliary Contacts Type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1	
Signalling Circuit Frequency	25400 Hz	
Minimum Switching Voltage	17 V for signalling circuit	
Minimum Switching Current	5 mA for signalling circuit	
Insulation Resistance	> 10 MOhm for signalling circuit	
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact1.5 ms on energisation between NC and NO contact	
Mounting Support	Plate	
	Rail	
Environment		
Standards	CSA C22.2 No 14	
	EN 60947-4-1	
	EN 60947-5-1 IEC 60947-4-1	
	IEC 60947-5-1	
	UL 508	
	IEC 60335-1	
Product Certifications	GL BV	
	DNV	
	LROS (Lloyds register of shipping)	
	RINA	
	UL CCC	
	CSA	
	GOST	
	UKCA CB	
Ip Degree Of Protection	IP20 front face IEC 60529	
Protective Treatment	THIEC 60068-2-30	

Climatic Withstand	IACS E10 exposure to damp heat IEC 60947-1 Annex Q category D exposure to damp heat		
Permissible Ambient Air Temperature Around The Device	-40140 °F (-4060 °C) 140158 °F (6070 °C) with derating		
Operating Altitude	09842.52 ft (03000 m)		
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1		
Flame Retardance	V1 conforming to UL 94		
Mechanical Robustness	Vibrations contactor open 2 Gn, 5300 Hz) Vibrations contactor closed 4 Gn, 5300 Hz) Shocks contactor open 10 Gn for 11 ms) Shocks contactor closed 15 Gn for 11 ms)		
Height	3.03 in (77 mm)		
Width 1.77 in (45 mm)			
Depth 3.74 in (95 mm)			
Net Weight	1.08 lb(US) (0.49 kg)		

Ordering and shipping details

Category	US10l1222354
Discount Schedule	0112
Gtin	3389110361711
Returnability	Yes
Country Of Origin	ID

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	2.01 in (5.100 cm)	
Package 1 Width	3.43 in (8.700 cm)	
Package 1 Length	4.13 in (10.500 cm)	
Package 1 Weight	18.69 oz (530.000 g)	
Unit Type Of Package 2	S02	
Number Of Units In Package 2	15	
Package 2 Height	5.91 in (15.000 cm)	
Package 2 Width	11.81 in (30.000 cm)	
Package 2 Length	15.75 in (40.000 cm)	
Package 2 Weight	18.26 lb(US) (8.284 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
Ø	Rohs Exemption Information	Yes
②	Pvc Free	


Certifications & Standards

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Compliant with Exemptions		
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.		
Environmental Disclosure	Product Environmental Profile		
Circularity Profile	End of Life Information		
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov		

LC1D18BL

Dimensions Drawings

Dimensions



(1) Minimum electrical clearance

LC1		D09D18	D093D123	D099D129
b		77	99	80
	without cover or add-on blocks	93	93	93
С	with cover, without add-on blocks	95	95	95
с1	with LAD N or C (2 or 4 contacts)	126	126	126
c2	with LA6 DK10	138	138	138
с3	with LAD T, R, S	146	146	146
	with LAD T, R, S and sealing cover	150	150	150

Connections and Schema

Wiring

