Product data sheet

Specification





IEC contactor, TeSys Deca, nonreversing, 32A, 20HP at 480VAC, up to 100kA SCCR, 3 phase, 3 NO, 120VAC 50/60Hz coil, open

LC1D32G7

Product availability: Stock - Normally stocked in distribution facility

Price*: 206.40 USD

Main

Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-3 AC-1 AC-4 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC
[le] Rated Operational Current	32 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit 50 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit 32 A (at <140 °F (60 °C)) at <= 440 V AC AC-3e for power circuit
[Uc] Control Circuit Voltage	120 V AC 50/60 Hz

Complementary

Motor Power Kw	7.5 kW at 220230 V AC 50/60 Hz (AC-3)
	15 kW at 380400 V AC 50/60 Hz (AC-3)
	15 kW at 415440 V AC 50/60 Hz (AC-3)
	18.5 kW at 500 V AC 50/60 Hz (AC-3)
	18.5 kW at 660690 V AC 50/60 Hz (AC-3)
	7.5 kW at 400 V AC 50/60 Hz (AC-4)
	7.5 kW at 220230 V AC 50/60 Hz (AC-3e)
	15 kW at 380400 V AC 50/60 Hz (AC-3e)
	15 kW at 415440 V AC 50/60 Hz (AC-3e)
	18.5 kW at 500 V AC 50/60 Hz (AC-3e)
	18.5 kW at 660690 V AC 50/60 Hz (AC-3e)
Maximum Horse Power Rating	2 hp at 115 V AC 50/60 Hz for 1 phase motors
	5 hp at 230/240 V AC 50/60 Hz for 1 phase motors
	10 hp at 200/208 V AC 50/60 Hz for 3 phase motors
	10 hp at 230/240 V AC 50/60 Hz for 3 phase motors
	20 hp at 460/480 V AC 50/60 Hz for 3 phase motors
	25 hp at 575/600 V AC 50/60 Hz for 3 phase motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[Ith] Conventional Free Air Thermal Current	10 A (at 140 °F (60 °C)) for signalling circuit 50 A (at 140 °F (60 °C)) for power circuit
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 550 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	550 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	260 A 104 °F (40 °C) - 10 s for power circuit 430 A 104 °F (40 °C) - 1 s for power circuit 60 A 104 °F (40 °C) - 10 min for power circuit 138 A 104 °F (40 °C) - 1 min for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 63 A gG at <= 690 V coordination type 1 for power circuit 63 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2 mOhm - Ith 50 A 50 Hz for power circuit
Power Dissipation Per Pole	2 W AC-3 5 W AC-1 2 W AC-3e
[Ui] Rated Insulation Voltage	Power circuit 690 V IEC 60947-4-1 Power circuit 600 V CSA Power circuit 600 V UL Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA Signalling circuit 600 V UL
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	15 Mcycles
Electrical Durability	1.65 Mcycles 32 A AC-3 <= 440 V 1.4 Mcycles 50 A AC-1 <= 440 V 1.65 Mcycles 32 A AC-3e <= 440 V
Control Circuit Type	AC 50/60 Hz
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.30.6 Uc -40158 °F (-4070 °C) drop-out AC 50/60 Hz 0.81.1 Uc -40140 °F (-4060 °C) operational AC 50 Hz 0.851.1 Uc -40140 °F (-4060 °C) operational AC 60 Hz 11.1 Uc 140158 °F (6070 °C) operational AC 50/60 Hz
Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 68 °F (20 °C)) 70 VA 50 Hz cos phi 0.75 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C)) 7 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat Dissipation	23 W at 50/60 Hz
Operating Time	1222 ms closing 419 ms opening
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)

Connections - Terminals	Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness:
	flexible without cable end Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness:
	flexible without cable end
	Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible with cable end
	Control circuit: screw clamp terminals 2 0.000.00 in² (12.5 mm²) - cable stiffness: flexible with cable end
	Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness:
	solid without cable end Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness:
	solid without cable end
	Power circuit: screw clamp terminals 1 0.000.02 in² (2.510 mm²) - cable stiffness: flexible without cable end
	Power circuit: screw clamp terminals 2 0.000.02 in² (2.510 mm²) - cable
	stiffness: flexible without cable end Power circuit: screw clamp terminals 1 0.000.02 in² (110 mm²) - cable stiffness:
	flexible with cable end Power circuit: screw clamp terminals 2 0.000.01 in² (1.56 mm²) - cable stiffness:
	flexible with cable end Power circuit: screw clamp terminals 1 0.000.02 in² (1.510 mm²) - cable
	stiffness: solid without cable end
	Power circuit: screw clamp terminals 2 0.000.02 in² (2.510 mm²) - cable stiffness: solid without cable end
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm
3	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2
	Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals flat Ø 6 mm
	Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals Philips No 2 Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2
	Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals pozidriv No 2
Auxiliary Contact Composition	1 NO + 1 NC
Auxiliary Contacts Type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Voltage	17 V for signalling circuit
Minimum Switching Current	5 mA for signalling circuit
Insulation Resistance	> 10 MOhm for signalling circuit
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Mounting Support	Rail
	Plate
Environment	
Standards	CSA C22.2 No 14
	EN 60947-4-1
	EN 60947-5-1 IEC 60947-4-1
	IEC 60947-4-1
	UL 508
	IEC 60335-1
Product Certifications	GL BV
	DNV
	LROS (Lloyds register of shipping)
	RINA
	UL
	CCC CSA
	GOST
	UKCA
In Dograp Of Protoction	CB
Ip Degree Of Protection	IP20 front face IEC 60529
Protective Treatment	THIEC 60068-2-30

Climatic Withstand	IACS E10 exposure to damp heat IEC 60947-1 Annex Q category D exposure to damp heat	
Permissible Ambient Air Temperature Around The Device	-40140 °F (-4060 °C) 140158 °F (6070 °C) with derating	
Operating Altitude	09842.52 ft (03000 m)	
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Vibrations contactor open 2 Gn, 5300 Hz) Vibrations contactor closed 4 Gn, 5300 Hz) Shocks contactor closed 15 Gn for 11 ms) Shocks contactor open 8 Gn for 11 ms)	
Height	3.35 in (85 mm)	
Width	1.77 in (45 mm)	
Depth	3.62 in (92 mm)	
Net Weight	0.83 lb(US) (0.375 kg)	

Ordering and shipping details

Category	US10l1222354
Discount Schedule	0112
Gtin	3389110350814
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.41 in (11.2 cm)
Package 1 Width	2.01 in (5.1 cm)
Package 1 Length	3.54 in (9.0 cm)
Package 1 Weight	14.67 oz (416.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	20
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	19.11 lb(US) (8.67 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	320
Package 3 Height	30.31 in (77.0 cm)
Package 3 Width	23.62 in (60.0 cm)
Package 3 Length	31.50 in (80.0 cm)
Package 3 Weight	324.56 lb(US) (147.22 kg)

Contractual warranty

Warranty

May 27, 2024

18 months

Sustainability Green Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

May 27, 2024

Dimensions Drawings

Approximate Dimensions

