# **Product data sheet**

Specification





AC servo motor BSH, Lexium 32, 14.4N.m, 3000rpm, keyed shaft, with brake, IP65

BSH1402T31F1P

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 3,952.50 USD

#### Main

Product Or Component Type	Servo motor				
Device Short Name	BSH				
Maximum Mechanical Speed	4000 rpm				
Continuous Stall Torque	172.59 lbf.in (19.5 N.m) LXM32.D72N4 24 A, 400 V, three phase 172.59 lbf.in (19.5 N.m) LXM32.D72N4 24 A, 480 V, three phase 127.45 lbf.in (14.4 N.m) LXM05AD42M3X, 200240 V, three phase 127.45 lbf.in (14.4 N.m) LXM05BD42M3X, 200240 V, three phase 127.45 lbf.in (14.4 N.m) LXM05CD42M3X, 200240 V, three phase				
Peak Stall Torque	524.85 lbf.in (59.3 N.m) LXM32.D72N4 24 A, 400 V, three phase 524.85 lbf.in (59.3 N.m) LXM32.D72N4 24 A, 480 V, three phase 217.37 lbf.in (24.56 N.m) LXM05AD42M3X, 200240 V, three phase 217.37 lbf.in (24.56 N.m) LXM05BD42M3X, 200240 V, three phase				
Nominal Output Power	3900 W LXM32.D72N4 24 A, 400 V, three phase 3900 W LXM32.D72N4 24 A, 480 V, three phase 2900 W LXM05AD42M3X, 200240 V, three phase 2900 W LXM05BD42M3X, 200240 V, three phase 2900 W LXM05CD42M3X, 200240 V, three phase				
Nominal Torque	108.86 lbf.in (12.3 N.m) LXM32.D72N4 24 A, 400 V, three phase 108.86 lbf.in (12.3 N.m) LXM32.D72N4 24 A, 480 V, three phase 81.43 lbf.in (9.2 N.m) LXM05AD42M3X, 200240 V, three phase 81.43 lbf.in (9.2 N.m) LXM05BD42M3X, 200240 V, three phase 81.43 lbf.in (9.2 N.m) LXM05BD42M3X, 200240 V, three phase 81.43 lbf.in (9.2 N.m) LXM05CD42M3X, 200240 V, three phase				
Nominal Speed	3000 rpm LXM32.D72N4 24 A, 400 V, three phase 3000 rpm LXM32.D72N4 24 A, 480 V, three phase 3000 rpm LXM05AD42M3X, 200240 V, three phase 3000 rpm LXM05BD42M3X, 200240 V, three phase 3000 rpm LXM05CD42M3X, 200240 V, three phase				
Product Compatibility	LXM05AD42M3X 200240 V three phase LXM05BD42M3X 200240 V three phase LXM05CD42M3X 200240 V three phase				
Shaft End	Keyed				
Ip Degree Of Protection	IP65 standard IP67 with IP67 kit				
Speed Feedback Resolution	131072 points/turn				
Holding Brake	With				
Mounting Support	International standard flange				
Electrical Connection	Straight connectors				

#### Complementary

Range Compatibility Lexium 05 Lexium 32

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Apr 23, 2024 Life Is On Schneider

Supply Voltage Max	480 V					
Phase	Three phase					
Continuous Stall Current	22.5 A					
Maximum Continuous Power	4.2 W					
Maximum Current Irms	72 A LXM32.D72N4 75.2 A LXM05AD42M3X 75.2 A LXM05BD42M3X 75.2 A LXM05CD42M3X					
Maximum Permanent Current	75.2 A					
Switching Frequency	8 kHz					
Second Shaft	Without second shaft end					
Shaft Diameter	0.94 in (24 mm)					
Shaft Length	1.97 in (50 mm)					
Key Width	1.57 in (40 mm)					
Feedback Type	Single turn SinCos Hiperface					
Holding Torque	203.57 lbf.in (23 N.m) holding brake					
Motor Flange Size	5.51 in (140 mm)					
Number Of Motor Stacks	2					
Torque Constant	1.47 N.m/A 248 °F (120 °C)					
Back Emf Constant	101 V/krpm 248 °F (120 °C)					
Number Of Motor Poles	10					
Rotor Inertia	14.48 kg.cm²					
Stator Resistance	0.6 Ohm 68 °F (20 °C)					
Stator Inductance	7.4 mH 68 °F (20 °C)					
Stator Electrical Time Constant	12.1 ms 68 °F (20 °C)					
Maximum Radial Force Fr	1680 N 3000 rpm 1930 N 2000 rpm 2430 N 1000 rpm					
Maximum Axial Force Fa	0.2 x Fr					
Brake Pull-In Power	24 W					
Type Of Cooling	Natural convection					
Length	12.22 in (310.5 mm)					
Centring Collar Diameter	5.12 in (130 mm)					
Centring Collar Depth	0.14 in (3.5 mm)					
Number Of Mounting Holes	4					
Mounting Holes Diameter	0.43 in (11 mm)					
Circle Diameter Of The Mounting Holes	6.50 in (165 mm)					
Net Weight	39.02 lb(US) (17.7 kg)					

## Ordering and shipping details

Category	US1PC5318282
Discount Schedule	PC53
Gtin	3389118361331

Returnability	No	
Country Of Origin	DF	

# **Packing Units**

Unit Type Of Package 1	PCE		
Number Of Units In Package 1	1		
Package 1 Height	10.63 in (27.0 cm)		
Package 1 Width	10.63 in (27.0 cm)		
Package 1 Length	18.98 in (48.2 cm)		
Package 1 Weight	29.30 lb(US) (13.29 kg)		

### **Contractual warranty**

Warranty 18 months

### Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**


Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.				
Circularity Profile	No need of specific recycling operations				

#### BSH1402T31F1P

#### **Dimensions Drawings**

#### **Servo Motors Dimensions**

#### **Example with Straight Connectors**



- a: Power supply for servo motor brake
- **b**: Power supply for servo motor encoder
- (1) M4 screw
- (2) Shaft end, keyed slot (optional)
- (3) For screws M8 x 19 mm/M8 x 0.75 in.

#### Dimensions in mm

Straight connectors		Rotatable angled connectors		a (itha atha aadaa)	- (ith hards-)		
b	b1	b2	b	b1	b2	c (without brake)	c (with brake)
192.5	54	25.5	198.5	60	39.5	273	311

#### Dimensions in in.

Straig	ht conne	ectors	Rotatable angled connectors		a (itha atha aadaa)	( د ا د د ا داند د ا	
b	b1	b2	b	b1	b2	c (without brake)	c (with brake)
7.57	2.12	1.00	7.81	2.36	1.55	10.74	12.24


### BSH1402T31F1P

#### Performance Curves

### 400 V 3-Phase Supply Voltage

#### **Torque/Speed Curves**

Servo motor with LXM32•D72N4 servo drive




- **X** Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

#### 480 V 3-Phase Supply Voltage

#### **Torque/Speed Curves**

Servo motor with LXM32•D72N4 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque