# Product data sheet





IEC contactor, TeSys Deca, nonreversing, 80A resistive, 4 pole, 4 NO, 230VAC 50/60Hz coil, open style

LC1DT80AP7

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 540.96 USD

#### Main

waiii		
Range	TeSys TeSys Deca	
Range Of Product	TeSys Deca	
Product Or Component Type	Contactor	
Device Short Name	LC1D	
Contactor Application	Resistive load	
Utilisation Category	AC-1	
Poles Description	4P	
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC	
[le] Rated Operational Current	80 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit	
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz	
Complementary		
Compatibility Code	LC1D	

Compatibility Code	LC1D
Pole Contact Composition	4 NO
Protective Cover	With
[Ith] Conventional Free Air Thermal Current	10 A (at 140 °F (60 °C)) for signalling circuit 80 A (at 140 °F (60 °C)) for power circuit
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 1000 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	1000 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	640 A 104 °F (40 °C) - 10 s for power circuit 900 A 104 °F (40 °C) - 1 s for power circuit 110 A 104 °F (40 °C) - 10 min for power circuit 260 A 104 °F (40 °C) - 1 min for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 125 A gG at <= 690 V coordination type 1 for power circuit 125 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	1.6 mOhm - Ith 80 A 50 Hz for power circuit
Power Dissipation Per Pole	10.2 W AC-1

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

[Ui] Rated Insulation Voltage	Power circuit 600 V CSA
	Power circuit 600 V UL
	Signalling circuit 690 V IEC 60947-1
	Signalling circuit 600 V CSA Signalling circuit 600 V UL
	Power circuit 690 V IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	6 Mcycles
Electrical Durability	1.4 Mcycles 80 A AC-1 <= 440 V
Control Circuit Type	AC 50/60 Hz
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.30.6 Uc -40158 °F (-4070 °C) drop-out AC 50/60 Hz
	0.81.1 Uc -40140 °F (-4060 °C) operational AC 50 Hz
	0.851.1 Uc -40140 °F (-4060 °C) operational AC 60 Hz
	11.1 Uc 140158 °F (6070 °C) operational AC 50/60 Hz
Inrush Power In Va	140 VA 60 Hz cos phi 0.75 (at 68 °F (20 °C)) 160 VA 50 Hz cos phi 0.75 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	13 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C)) 15 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat Dissipation	45 W at 50/60 Hz
Operating Time	419 ms opening 1226 ms closing
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)
Connections - Terminals	Control circuit: screw clamp terminals 2 0.000.00 in² (12.5 mm²) - cable stiffness:
	flexible with cable end Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness:
	flexible without cable end
	Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness:
	flexible without cable end
	Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible with cable end
	Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness:
	solid without cable end
	Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness:
	solid without cable end Power circuit: EverLink BTR screw connectors 1 0.000.05 in² (135 mm²) - cable
	stiffness: flexible without cable end
	Power circuit: EverLink BTR screw connectors 2 0.000.04 in² (125 mm²) - cable
	stiffness: flexible without cable end
	Power circuit: EverLink BTR screw connectors 1 0.000.05 in <sup>2</sup> (135 mm <sup>2</sup> ) - cable stiffness: flexible with cable end
	Power circuit: EverLink BTR screw connectors 2 0.000.04 in² (125 mm²) - cable
	stiffness: flexible with cable end
	Power circuit: EverLink BTR screw connectors 1 0.000.05 in² (135 mm²) - cable
	stiffness: solid without cable end Power circuit: EverLink BTR screw connectors 2 0.000.04 in² (125 mm²) - cable
	stiffness: solid without cable end
Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat \$6 \text{ film}  Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2
	Power circuit 70.81 lbf.in (8 N.m) screw clamp terminals 0.040.05 in² (2535 mm²)
	hexagonal 0.16 in (4 mm)
	Power circuit 44.25 lbf.in (5 N.m) screw clamp terminals 0.000.04 in² (125 mm²) hexagonal 0.16 in (4 mm)
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2
	Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals pozidriv No 2
Auxiliary Contact Composition	4 NO + 4 NO
Auxiliary Contact Composition	1 NO + 1 NC

Auxiliary Contacts Type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1	
Signalling Circuit Frequency	25400 Hz	
Minimum Switching Voltage	17 V for signalling circuit	
Minimum Switching Current	5 mA for signalling circuit	
Insulation Resistance	> 10 MOhm for signalling circuit	
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact	
Mounting Support	Rail Plate	

### **Environment**

Standards	CSA C22.2 No 14
	EN 60947-4-1
	EN 60947-5-1
	IEC 60947-4-1
	IEC 60947-5-1
	UL 508
	IEC 60335-1
Product Certifications	DNV
	GL
	UL
	CSA
	BV
	GOST
	CCC
	LROS (Lloyds register of shipping)
	RINA
Ip Degree Of Protection IP20 front face IEC 60529	
Protective Treatment THIEC 60068-2-30	
Climatic Withstand	IACS E10 exposure to damp heat
	IEC 60947-1 Annex Q category D exposure to damp heat
Permissible Ambient Air	-40140 °F (-4060 °C)
Temperature Around The Device	140158 °F (6070 °C) with derating
	- Tolling Transfer of management
Operating Altitude	09842.52 ft (03000 m)
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1
Flame Retardance	MA conference to III OA
	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open 2 Gn, 5300 Hz)
	Vibrations contactor closed 4 Gn, 5300 Hz)
	Shocks contactor closed 15 Gn for 11 ms)
	Shocks contactor open 10 Gn for 11 ms)
	Shocks contactor open to on for 11 ms)
Height	4.80 in (122 mm)
Width	2.76 in (70 mm)
Depth	4.72 in (120 mm)
Net Weight	2.54 lb(US) (1.15 kg)

# Ordering and shipping details

Category	US10I1222357	
Discount Schedule	0112	
Gtin	3389119409445	
Returnability	No	
Country Of Origin	ID	

## **Packing Units**

9		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	3.15 in (8.0 cm)	
Package 1 Width	5.51 in (14.0 cm)	
Package 1 Length	5.91 in (15.0 cm)	
Package 1 Weight	2.39 lb(US) (1.086 kg)	
Unit Type Of Package 2	S02	
Number Of Units In Package 2	7	
Package 2 Height	5.91 in (15.0 cm)	
Package 2 Width	11.81 in (30.0 cm)	
Package 2 Length	15.75 in (40.0 cm)	
Package 2 Weight	18.14 lb(US) (8.226 kg)	

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>②</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information Yes	
<b>Ø</b>	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov