Product data sheet

Specification





TeSys SK mini contactor - 4P (4 NO) - AC-1 - 690 V 20 A - 230 V AC coil

LC1SKGC400P7

! Discontinued on: Oct 8, 2021

① Discontinued

Main

Range	TeSys
Product Name	TeSys SK
Product Or Component Type	Mini contactor
Device Short Name	LC1SKGC
Contactor Application	Resistive load
Utilisation Category	AC-1
Power Pole Contact Composition	4P
Pole Contact Composition	4 NO
[le] Rated Operational Current	20 A (at <122 °F (50 °C)) AC AC-1
[Ue] Rated Operational Voltage	Power circuit 690 V AC 50/60 Hz

Complementary

,	
Control Circuit Type	AC 50/60 Hz
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz
[Ith] Conventional Free Air Thermal Current	20 A (at 131 °F (55 °C)) for power circuit
Irms Rated Making Capacity	85 A AC conforming to NF C 63-110 85 A AC conforming to IEC 60947
Rated Breaking Capacity	68 A at <= 400 V conforming to NF C 63-110 68 A at <= 400 V conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	60 A 131 °F (55 °C) for power circuit
Associated Fuse Rating	20 A gl at <= 440 V for power circuit
Average Impedance	4 mOhm - Ith 20 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit 690 V BS 5424 Power circuit 690 V IEC 60947 Power circuit 690 V UL 508 Power circuit 690 V VDE 0110 group C Power circuit 690 V CSA C22.2 No 14
Mounting Support	Rail Panel
Standards	EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	CB Scheme CE UKCA EAC cULus
Connections - Terminals	connector 1 0.000.01 in² (1.56 mm²)solid connector 2 0.000.01 in² (1.54 mm²)solid connector 1 0.000.01 in² (0.56 mm²)flexible without cable end connector 2 0.000.00 in² (0.352.5 mm²)flexible without cable end connector 1 0.000.01 in² (0.356 mm²)flexible with cable end connector 2 0.000.00 in² (0.351.5 mm²)flexible with cable end
Tightening Torque	Power circuit 7.08 lbf.in (0.8 N.m) connector pozidriv No 1
Operating Time	68 ms coil de-energisation and NO opening 714 ms coil energisation and NO closing
Mechanical Durability	10 Mcycles
Maximum Operating Rate	1200 cyc/h
Control Circuit Voltage Limits	Operational: 0.851.1 Uc at 50/60 Hz (at <131 °F (55 °C)) Drop-out: 0.20.75 Uc at 50/60 Hz (at <131 °F (55 °C))
Inrush Power In Va	23 VA 50/60 Hz (at 68 °F (20 °C))
Hold-In Power Consumption In Va	4.9 VA 50/60 Hz (at 68 °F (20 °C))
Heat Dissipation	1.5 W 50/60 Hz

Environment

Ip Degree Of Protection	IP2X VDE 0106
Protective Treatment	TC IEC 60068 TC DIN 50015
Ambient Air Temperature For Operation	-4122 °F (-2050 °C)
Ambient Air Temperature For Storage	-58158 °F (-5070 °C)
Operating Altitude	6561.68 ft (2000 m) without derating
Height	2.28 in (58 mm)
Width	1.77 in (45 mm)
Depth	2.20 in (56 mm)
Net Weight	0.39 lb(US) (0.175 kg)

Ordering and shipping details

Category	18400-WORLD SERVICE PARTS(CONTACTORS)
Discount Schedule	CP10
Gtin	3389110563801
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.89 in (4.8 cm)
Package 1 Width	2.36 in (6 cm)
Package 1 Length	2.44 in (6.2 cm)
Package 1 Weight	6.03 oz (171 g)

Contractual warranty

Warranty

Apr 25, 2024

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.