Product data sheet

Specifications





Control relay, TeSys K, 4 NO, It or eq to 690V, 250VDC standard coil

CA3KN40UD

Discontinued on: Jul 12, 2021

! Discontinued

Main

Range	TeSys
Product Name	TeSys CAK
Product Or Component Type	Control relay
Device Short Name	CA3K
Contactor Application	Control circuit
Utilisation Category	AC-15 DC-13
Pole Contact Composition	4 NO
[Ue] Rated Operational Voltage	<= 690 V <= 400 Hz
Control Circuit Type	DC standard
[Uc] Control Circuit Voltage	250 V DC

Complementary

[Ith] Conventional Free Air	10 A (at 122 °F (50 °C))
Thermal Current	1077 (00.122 1 (00.07))
Irms Rated Making Capacity	110 A IEC 60947
Associated Fuse Rating	10 A gG conforming to IEC 60947 10 A gG conforming to VDE 0660
	10 A gG comorning to VDE 0000
[Ui] Rated Insulation Voltage	690 V IEC 60947
	750 V VDE 0110 group C
	690 V BS 5424
	600 V CSA C22.2 No 14
Mounting Support	Plate
	Rail
Connections - Terminals	screw clamp terminals 1 0.000.01 in² (1.54 mm²)solid
	screw clamp terminals 2 0.000.01 in ² (1.54 mm ²)solid
	screw clamp terminals 1 0.000.01 in ² (0.754 mm ²)flexible with cable end
	screw clamp terminals 2 0.000.01 in ² (0.754 mm ²)flexible without cable end
	screw clamp terminals 1 0.000.00 in ² (0.341.5 mm ²)flexible with cable end
	screw clamp terminals 2 $0.000.00~\text{in}^2~(0.341.5~\text{mm}^2)$ flexible without cable end
Tightening Torque	11.51 lbf.in (1.3 N.m) screw clamp terminals flat Ø 6 mm
	11.51 lbf.in (1.3 N.m) screw clamp terminals Philips No 2 0.24 in (6 mm)
Control Circuit Voltage Limits	Operational: 0.81.15 Uc (at <122 °F (50 °C))
	Drop-out: 0.10.75 Uc (at <122 °F (50 °C))
Operating Time	10 ms coil de-energisation and NO opening
	3040 ms coil energisation and NO closing
Mechanical Durability	20 Mcycles
Maximum Operating Rate	10000 cyc/h

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Immunity To Microbreaks	2 ms
Inrush Power In W	3 W 68 °F (20 °C))
Hold-In Power Consumption In W	3 W 68 °F (20 °C)
Heat Dissipation	3 W
Minimum Switching Voltage	17 V
Minimum Switching Current	5 mA
Non Overlap Distance	0.02 in (0.5 mm)
Insulation Resistance	> 10 MOhm
Height	2.28 in (58 mm)
Width	1.77 in (45 mm)
Depth	2.24 in (57 mm)
Net Weight	0.50 lb(US) (0.225 kg)

Environment

Standards	EN/IEC 60947-4-1 GB/T 14048.4 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1
Product Certifications	CB Scheme CCC UL CSA EAC CE UKCA
Ip Degree Of Protection	IP2X
Protective Treatment	TC IEC 60068
Ambient Air Temperature For Operation	-13122 °F (-2550 °C)
Ambient Air Temperature For Storage	-58176 °F (-5080 °C)
Operating Altitude	6561.68 ft (2000 m) without derating
Flame Retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102
Mechanical Robustness	Vibrations contactor open2 Gn, 5300 Hz IEC 60068-2-6 Vibrations contactor closed4 Gn, 5300 Hz IEC 60068-2-6 Shocks contactor open10 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed15 Gn for 11 ms IEC 60068-2-27

Ordering and shipping details

Category	22371-RELAYS, CONTROL	
Discount Schedule	l12	
Gtin	3389110484816	
Returnability	No	
Country Of Origin	FR	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	1.89 in (4.8 cm)	
Package 1 Width	2.44 in (6.2 cm)	
Package 1 Length	2.60 in (6.6 cm)	
Package 1 Weight	7.94 oz (225 g)	

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov