# **Product data sheet**

Specification





# TeSys Deca reversing contactor - 3P(3 NO) - AC-3 - <= 440 V 32 A - 24 V DC coil

LC2D32BDV

! Discontinued on: Jan 23, 2021

#### ① Discontinued

	_
ΝЛ	-:
IVI	ain
	anı

Range	TeSys TeSys Deca
Product Name	TeSys D TeSys Deca
Product Or Component Type	Reversing contactor
Device Short Name	LC2D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-3 AC-1
Device Presentation	Preassembled with reversing power busbar
Poles Description	3P
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC
[le] Rated Operational Current	32 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit 50 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit
Motor Power Kw	7.5 kW at 220230 V AC 50 Hz 15 kW at 380400 V AC 50 Hz 15 kW at 415440 V AC 50 Hz 18.5 kW at 500 V AC 50 Hz 18.5 kW at 660690 V AC 50 Hz
Motor Power Hp (UI / Csa)	2 hp at 115 V AC 60 Hz for 1 phase motors 5 hp at 230/240 V AC 60 Hz for 1 phase motors 7.5 hp at 230/240 V AC 60 Hz for 3 phase motors 10 hp at 230/240 V AC 60 Hz for 3 phase motors 20 hp at 460/480 V AC 60 Hz for 3 phase motors 30 hp at 575/600 V AC 60 Hz for 3 phase motors
Control Circuit Type	DC standard
[Uc] Control Circuit Voltage	24 V DC
Auxiliary Contact Composition	1 NO + 1 NC
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947
Overvoltage Category	III
[Ith] Conventional Free Air Thermal Current	10 A (at 140 °F (60 °C)) for signalling circuit 50 A (at 140 °F (60 °C)) for power circuit
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 550 A at 440 V for power circuit conforming to IEC 60947

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Rated Breaking Capacity	550 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	60 A 104 °F (40 °C) - 10 min for power circuit 138 A 104 °F (40 °C) - 1 min for power circuit
	260 A 104 °F (40 °C) - 10 s for power circuit
	430 A 104 °F (40 °C) - 1 s for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
	63 A gG at <= 690 V coordination type 1 for power circuit
	63 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2 mOhm - Ith 50 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit 690 V IEC 60947-4-1
	Power circuit 600 V CSA
	Power circuit 600 V UL
	Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA
	Signalling circuit 600 V UL
	organism of the control of the contr
Electrical Durability	1.65 Mcycles 32 A AC-3 <= 440 V
	1.4 Mcycles 50 A AC-1 <= 440 V
Power Dissipation Per Pole	2 W AC-3
	5 W AC-1
Front Cover	With
Interlocking Type	Electrical and mechanical
Mounting Support	Plate
	Rail
Standards	CSA C22.2 No 14
	EN 60947-4-1
	EN 60947-5-1
	IEC 60947-4-1
	IEC 60947-5-1
	UL 508 IEC 60335-1
Donadonak Oradifirationa	
Product Certifications	UL CSA
	RINA
	GOST
	CCC
	DNV
	LROS (Lloyds register of shipping)
	GL
	BV
	UKCA
	CB
Connections - Terminals	Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)flexible without
	cable end Control circuit screw clamp terminals 2 0.000.01 in² (14 mm²)flexible without
	cable end
	Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)flexible with cable end
	Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²)flexible with cable
	end Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)solid
	Control circuit screw clamp terminals 1 0.000.01 in (14 min )solid
	Power circuit screw clamp terminals 2 0.000.02 in² (2.510 mm²)flexible without
	cable end Power circuit screw clamp terminals 2 0.000.02 in² (2.510 mm²)flexible without
	cable end Power circuit screw clamp terminals 1 0.000.02 in² (110 mm²)flexible with cable
	end
	Power circuit screw clamp terminals 2 0.000.01 in² (1.56 mm²)flexible with cable end
	Power circuit screw clamp terminals 1 0.000.02 in² (1.510 mm²)solid
	Power circuit screw clamp terminals 2 0.000.02 in² (2.510 mm²)solid

Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm	
3	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2	
	Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals flat Ø 6 mm	
	Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals Philips No 2	
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2	
	Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals pozidriv No 2	
Operating Time	53.5572.45 ms closing	
	1624 ms opening	
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1	
	B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1	
Mechanical Durability	30 Mcycles	
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)	

# Complementary

•	
Coil Technology	Built-in bidirectional peak limiting diode suppressor
Control Circuit Voltage Limits	0.10.25 Uc -40158 °F (-4070 °C) drop-out DC 0.71.25 Uc -40140 °F (-4060 °C) operational DC 11.25 Uc 140158 °F (6070 °C) operational DC
Time Constant	28 ms
Inrush Power In W	5.4 W 68 °F (20 °C))
Hold-In Power Consumption In W	5.4 W 68 °F (20 °C)
Auxiliary Contacts Type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Current	5 mA for signalling circuit
Minimum Switching Voltage	17 V for signalling circuit
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Insulation Resistance	> 10 MOhm for signalling circuit

## **Environment**

Ip Degree Of Protection	IP20 front face IEC 60529
Climatic Withstand	IACS E10 IEC 60947-1 Annex Q category D
Protective Treatment	TH IEC 60068-2-30
Pollution Degree	3
Ambient Air Temperature For Operation	-40140 °F (-4060 °C) 140158 °F (6070 °C) with derating
Ambient Air Temperature For Storage	-76176 °F (-6080 °C)
Operating Altitude	09842.52 ft (03000 m)
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open2 Gn, 5300 Hz Vibrations contactor closed4 Gn, 5300 Hz Shocks contactor closed15 Gn for 11 ms Shocks contactor open8 Gn for 11 ms
Height	3.35 in (85 mm)
Width	3.54 in (90 mm)
Depth	3.98 in (101 mm)

## Ordering and shipping details

Category	22355-CTR,TESYS D,OPEN,9-38A DC
Discount Schedule	112
Gtin	3389110414691
Returnability	No
Country Of Origin	FR

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.29 in (10.9 cm)
Package 1 Width	4.49 in (11.4 cm)
Package 1 Length	4.65 in (11.8 cm)
Package 1 Weight	2.58 lb(US) (1.17 kg)

## **Contractual warranty**

Warranty 18 months



Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov