Product data sheet

Specifications





TeSys F magnetic latching contactor - 4P(4 NO) - 630 A - 220...230 V AC/DC coil

CR1F6304M7

! Discontinued on: Jul 12, 2021

(!) Discontinued

Main

Range	TeSys
Product Name	TeSys F
Product Or Component Type	Magnetic latching contactor
Device Short Name	CR1F
Device Application	Control
Contactor Application	Resistive load Motor control
Utilisation Category	AC-3 AC-4 AC-1
Poles Description	4P
Power Pole Contact Composition	4 NO
[Ue] Rated Operational Voltage	1000 V AC 25200 Hz
[le] Rated Operational Current	630 A (at <104 °F (40 °C)) at <= 440 V AC AC-3 1000 A (at <104 °F (40 °C)) at <= 440 V AC AC-1 560 A (at <104 °F (40 °C)) at <= 440 V AC AC-4
Control Circuit Type	AC 50400 Hz DC standard
[Uc] Control Circuit Voltage	220230 V AC 50400 Hz 220230 V DC
Irms Rated Making Capacity	6740 A
Rated Breaking Capacity	6300 A at 220440 V 5400 A at 500 V 3200 A at 1000 V 4600 A at 660/690 V
[Icw] Rated Short-Time Withstand Current	5.05 kA 104 °F (40 °C) - 1 s 5.05 kA 104 °F (40 °C) - 5 s 5.05 kA 104 °F (40 °C) - 10 s 4400 A 104 °F (40 °C) - 30 s 3400 A 104 °F (40 °C) - 1 min 2200 A 104 °F (40 °C) - 3 min 1600 A 104 °F (40 °C) - 10 min
Associated Fuse Rating	630 A aM at <= 440 V 1000 A BS88 at <= 440 V 1000 A gG at <= 440 V
Average Impedance	0.12 mOhm - Ith 1000 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V IEC 60158-1 1000 V IEC 60947-4 1000 V BS 775 1500 V VDE 0110 group C

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Apr 20, 2024 Life Is On Schneider 1

Power Dissipation Per Pole	48 W AC-3 120 W AC-1
Connections - Terminals	bars 2 60 x 5 mm Power circuit bolted connection
Tightening Torque	513.34 lbf.in (58 N.m)
Operating Time	4080 ms latching 50100 ms unlatching
Mechanical Durability	1 Mcycles
Maximum Operating Rate	120 cyc/h 104 °F (40 °C)

Complementary

Control Circuit Voltage Limits	Latching: 0.851.1 Uc Unlatching: 0.851.1 Uc
Average Consumption	11 VA AC 50400 Hz unlatching 2300 VA AC 50400 Hz latching 11 VA DC unlatching 2300 VA DC latching

Environment

Protective Treatment	тс
Ambient Air Temperature For Operation	5158 °F (-1570 °C)
Ambient Air Temperature For Storage	-76176 °F (-6080 °C)
Operating Altitude	9842.52 ft (3000 m) without derating
Height	11.97 in (304 mm)
Width	15.31 in (389 mm)
Depth	10.04 in (255 mm)
Net Weight	47.40 lb(US) (21.5 kg)

Ordering and shipping details

Category	22331-CTR,F-LINE,DC,OPEN,NONREV
Discount Schedule	112
Gtin	3389110549010
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.83 in (27.5 cm)
Package 1 Width	13.39 in (34 cm)
Package 1 Length	16.93 in (43 cm)
Package 1 Weight	44.33 lb(US) (20.11 kg)

Contractual warranty

Warranty	18 months	
----------	-----------	--



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Compliant	
	EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	