Product data sheet

Specifications





Fuse carrier, TeSys DF, 3P+N, 32A, 690VAC, fuse size 10x38mm

DF103N

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 43.40 USD

Main

| Range | TeSys |
|--|--|
| Product Name | TeSys DF |
| Product Or Component Type | Fuse carrier |
| Device Short Name | DF10 |
| Device Composition | tubular link locked in Neutral pole |
| Product Compatibility | DF2CA fuse cartridge DF2CN fuse cartridge |
| Poles Description | 3P + N |
| Fuse Size | 10 x 38 mm |
| Fuse Type | , gG , aM |
| Control Type | Toggle padlockable |
| Utilisation Category | AC-20B IEC 60947-3 DC-20B IEC 60947-3 |
| [Ue] Rated Operational Voltage | 690 V AC 690 V DC |
| [le] Rated Operational Current | 32 A 400 V AC |
| [Ith] Conventional Free Air Thermal Current | 32 A 68 °F (20 °C) |
| [Ui] Rated Insulation Voltage | 690 V AC |
| [Uimp] Rated Impulse Withstand Voltage | 6 kV |
| Overvoltage Category | III |
| Short-Circuit Withstand | 120 kA 400 V IEC 60947-3 120 kA 500 V IEC 60947-3 |
| Power Dissipation In W | 3 W maximum power dissipation by fuse |

Complementary

| Standards | EN/IEC 60947-3 EN/IEC 60269-2 UL 4248-1 CSA C22.2 No 4248-1 EN 45545-2: R22 HL2 |
|------------------------|---|
| Product Certifications | IEC UL Recognized CSA CCC EAC DNV-GL |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Mounting Support | 35 mm symmetrical DIN rail |
|-------------------------|--|
| Mounting Position | Vertical +/- 23°) |
| Connections - Terminals | screw clamp terminals 1 0.000.02 in ² (116 mm ²)rigid screw clamp terminals 2 0.000.01 in ² (16 mm ²)rigid screw clamp terminals 1 0.000.02 in ² (116 mm ²)flexible with or without screw clamp terminals 2 0.000.01 in ² (16 mm ²)flexible with or without |
| Tightening Torque | 19.47 lbf.in (2.2 N.m) PZ2 19.47 lbf.in (2.2 N.m) flat Ø 5.5 mm |
| Height | 3.13 in (79.5 mm) |
| Width | 2.76 in (70 mm) |
| Depth | 2.40 in (61 mm) |
| Net Weight | 0.38 lb(US) (0.171 kg) |
| Quantity Per Set | Set of 3 |

Environment

| Ambient Air Temperature For Storage | -40158 °F (-4070 °C) |
|--|---|
| Ambient Air Temperature For Operation | -40158 °F (-4070 °C) with derating above 20°C |
| Operating Altitude | 06561.68 ft (02000 m) |
| Ip Degree Of Protection | IP20 |
| Pollution Degree | 3 |
| Fire Resistance | 1760 °F (960 °C) IEC 60695-2-1 |
| Compatibility Code | DF10 |

Ordering and shipping details

| Category | US10CP121714 |
|-------------------|---------------|
| Discount Schedule | 0CP1 |
| Gtin | 3389119407250 |
| Returnability | No |
| Country Of Origin | TN |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.44 in (6.2 cm) |
| Package 1 Width | 2.76 in (7 cm) |
| Package 1 Length | 3.15 in (8 cm) |
| Package 1 Weight | 6.35 oz (180 g) |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 3 |
| Package 2 Height | 2.68 in (6.8 cm) |
| Package 2 Width | 3.35 in (8.5 cm) |
| Package 2 Length | 8.74 in (22.2 cm) |
| Package 2 Weight | 20.35 oz (577 g) |

| Unit Type Of Package 3 | S03 |
|------------------------------|-------------------------|
| Number Of Units In Package 3 | 48 |
| Package 3 Height | 11.81 in (30 cm) |
| Package 3 Width | 11.81 in (30 cm) |
| Package 3 Length | 15.75 in (40 cm) |
| Package 3 Weight | 21.59 lb(US) (9.791 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

| \checkmark | Toxic Heavy Metal Free | |
|--------------|----------------------------|-----|
| | Mercury Free | |
| | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Compliant |
| | EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| | Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | No need of specific recycling operations |
| | Circularity Profile |
| California Proposition 65 | WARNING: Cancer - www.P65Warnings.ca.gov |