Product data sheet

Specification





Fuse carrier, TeSys DF, 2P, 25A, 400VAC, fuse size 8.5x31.5mm

DF82

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 30.60 USD

Main

Range	TeSys
Product Name	TeSys DF
Product Or Component Type	Fuse carrier
Device Short Name	DF8
Product Compatibility	DF2BA fuse cartridge DF2BN fuse cartridge
Poles Description	2P
Fuse Size	8.3 x 31.5 mm
Fuse Type	, gG , aM
Control Type	Toggle padlockable
Utilisation Category	AC-20B IEC 60947-3
[Ue] Rated Operational Voltage	400 V AC
[le] Rated Operational Current	25 A 400 V AC
[Ith] Conventional Free Air Thermal Current	25 A 68 °F (20 °C)
[Ui] Rated Insulation Voltage	500 V AC
[Uimp] Rated Impulse Withstand Voltage	6 kV
Overvoltage Category	III
Short-Circuit Withstand	20 kA 400 V IEC 60947-3
Power Dissipation In W	2.5 W maximum power dissipation by fuse

Complementary

Standards	EN/IEC 60947-3 EN/IEC 60269-2
Product Certifications	IEC EAC DNV-GL
Mounting Support	35 mm symmetrical DIN rail
Mounting Position	Vertical +/- 23°)
Connections - Terminals	screw clamp terminals 1 0.000.02 in² (116 mm²)rigid screw clamp terminals 2 0.000.01 in² (16 mm²)rigid screw clamp terminals 1 0.000.02 in² (116 mm²)flexible with or without screw clamp terminals 2 0.000.01 in² (16 mm²)flexible with or without
Tightening Torque	19.47 lbf.in (2.2 N.m) PZ2 19.47 lbf.in (2.2 N.m) flat Ø 5.5 mm

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Height	3.13 in (79.5 mm)
Width	1.38 in (35 mm)
Depth	2.40 in (61 mm)
Net Weight	0.19 lb(US) (0.085 kg)
Quantity Per Set	Set of 6

Environment

Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C) with derating above 20°C
Operating Altitude	06561.68 ft (02000 m) without derating
Ip Degree Of Protection	IP20
Pollution Degree	3
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1
Compatibility Code	DF8

Ordering and shipping details

Category	US10CP121714
Discount Schedule	0CP1
Gtin	3389119407120
Returnability	No
Country Of Origin	FR

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.15 in (8.000 cm)
Package 1 Width	1.38 in (3.500 cm)
Package 1 Length	2.40 in (6.100 cm)
Package 1 Weight	3.10 oz (88.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	2.68 in (6.800 cm)
Package 2 Width	3.35 in (8.500 cm)
Package 2 Length	8.74 in (22.200 cm)
Package 2 Weight	19.93 oz (565.000 g)
Unit Type Of Package 3	S03
Number Of Units In Package 3	96
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	20.94 lb(US) (9.499 kg)

Contractual warranty

Warranty

18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations Circularity Profile
California Proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov