





# Mini circuit breaker, E-Frame, 15A, 1 pole, 277 VAC, 25 kA max, bolt on, shunt trip

EDB14015SA

! Discontinued on: Jan 11, 2023

### ① Discontinued

#### Main

Range Of Product	125 A Frame EDB-EGB-EJB	
Product Or Component Type	Miniature circuit-breaker	
Device Short Name	EDB	
Module Type	E-Frame	
Trip Unit Rating	875 A	

## Complementary

o o impromontary	
Line Rated Current	15 A
Maximum Operating Voltage	277 V AC
Awg Gauge	AWG 12AWG 6 aluminium AWG 14AWG 6 copper
Breaking Capacity	18 kA 277 V AC 18 kA 240 V AC 25 kA 120 V AC 18 kA 120/240 V AC
Circuit Breaker Application	Switching Duty rated HID rated HACR rated
Electrical Connection	Lugs aluminium
Holding Current	270 A
Local Signalling	Trip indicator
Mounting Mode	Bolt-on
Number Of Poles	1
Number Of Spaces	2
Number Of Spaces Required	2
Product Destination	NF panelboard
Protection Type	Overload Short-circuit
Device Composition	Shunt trip
Trip Unit Technology	Thermal-magnetic
Breaking Capacity Code	D
Tightening Torque	30.09 lbf.in (3.4 N.m) 0.000.02 in² (2.516 mm²) (AWG 14AWG 6)
Height	5.66 in (143.76 mm)
Width	1.96 in (49.78 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Depth	4.05 in (102.87 mm)
Net Weight	2 lb(US) (0.91 kg)

## **Environment**

Product Certifications	IEC cULus
Ambient Air Temperature For Operation	104 °F (40 °C)

# Ordering and shipping details

Category	00931-EDB CIRCUIT BREAKERS
Discount Schedule	DE2
Gtin	00785901691372
Returnability	No
Country Of Origin	MX

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.06 in (7.772 cm)
Package 1 Width	5.81 in (14.757 cm)
Package 1 Length	9.56 in (24.282 cm)
Package 1 Weight	32.98 oz (934.99 g)

## **Contractual warranty**

Warranty 18 months

Apr 25, 2024



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.