

Product data sheet

Specifications

SQUARE D



Transformer Dry Type 112.5kVA 480D208Y

EE112T3HFISCUNLP

Discontinued on: Oct 11, 2022

Discontinued

Main

Product	Non-Linear Transformer
Enclosure Code	22D
Enclosure Type	NEMA 2
Insulation Temperature	428 °F (220 °C)
K-Factor	K-13
Phase	3 phase
Primary Voltage	480 V delta
Power Rating	112.5 kVA
Secondary Voltage	208Y/120 V
Full Capacity Taps	6 2.5 % 2+ 4-
Temperature Rise	115 °C
Winding Material	Copper

Ordering and shipping details

Category	16278-EE K RATED LVGP XFMR
Discount Schedule	PE2E
Gtin	785901435761
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	48.31 in (122.7 cm)
Package 1 Width	28.70 in (72.9 cm)
Package 1 Length	32.99 in (83.8 cm)
Package 1 Weight	954.00 lb(US) (432.727 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)