

# Product data sheet

Specifications

SQUARE D



## TRFMR DRY 3PH 75KVA 480DELTA 208Y/120

EE75T3HISNLP

 Discontinued on: Nov 1, 2022

 Discontinued

### Main

Product	Non-Linear Transformer
Enclosure Code	21D
Enclosure Type	NEMA 2
Insulation Temperature	428 °F (220 °C)
K-Factor	K-13
Phase	3 phase
Primary Voltage	480 V delta
Power Rating	75 kVA
Secondary Voltage	208Y/120 V
Full Capacity Taps	6 2.5 % 2+ 4-
Temperature Rise	150 °C
Winding Material	Aluminium

### Ordering and shipping details

Category	16278-EE K RATED LVGP XFMR
Discount Schedule	PE2E
Gtin	785901430483
Returnability	No
Country Of Origin	MX

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	41.89 in (106.4 cm)
Package 1 Width	28.19 in (71.6 cm)
Package 1 Length	32.99 in (83.8 cm)
Package 1 Weight	544.00 lb(US) (246.754 kg)

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

**Eu Rohs Directive**

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

**Environmental Disclosure**

[Product Environmental Profile](#)