# **Product data sheet**

Specifications





IEC contactor, TeSys Deca, nonreversing, 125A resistive, 4 pole, 2 NO and 2 NC, 48VDC coil, open style

LP1D80008ED

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 599.00 USD

#### Main

Range	TeSys
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LP1D
Contactor Application	Resistive load
Utilisation Category	AC-1
Poles Description	4P
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz
[le] Rated Operational Current	125 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit
[Uc] Control Circuit Voltage	48 V DC

### Complementary

Compatibility Code	LP1D
Pole Contact Composition	2 NO + 2 NC
Protective Cover	Without
[Ith] Conventional Free Air Thermal Current	125 A (at 140 °F (60 °C)) for power circuit
Irms Rated Making Capacity	1100 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	1100 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	135 A 104 °F (40 °C) - 10 min for power circuit 320 A 104 °F (40 °C) - 1 min for power circuit 640 A 104 °F (40 °C) - 10 s for power circuit 990 A 104 °F (40 °C) - 1 s for power circuit
Associated Fuse Rating	200 A gG at <= 690 V coordination type 1 for power circuit 160 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	0.8 mOhm - Ith 125 A 50 Hz for power circuit
Power Dissipation Per Pole	12.5 W AC-1
[Ui] Rated Insulation Voltage	Power circuit 600 V CSA Power circuit 600 V UL Power circuit 1000 V IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	10 Mcycles
Electrical Durability	0.8 Mcycles 125 A AC-1 <= 440 V
Control Circuit Type	DC DC standard
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.10.3 Uc -40131 °F (-4055 °C) drop-out DC 0.851.1 Uc -40131 °F (-4055 °C) operational DC
Inrush Power In W	22 W 68 °F (20 °C))
Hold-In Power Consumption In W	22 W 68 °F (20 °C)
Operating Time	620 ms opening 2035 ms closing
Time Constant	75 ms
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)
Connections - Terminals  Tightening Torque	Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 0.000.00 in² (12.5 mm²) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: solid Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: solid Power circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: solid Power circuit: connector 1 0.010.08 in² (450 mm²) - cable stiffness: flexible without cable end Power circuit: connector 2 0.010.04 in² (450 mm²) - cable stiffness: flexible with cable end Power circuit: connector 2 0.010.08 in² (450 mm²) - cable stiffness: flexible with cable end Power circuit: connector 2 0.010.08 in² (450 mm²) - cable stiffness: solid Power circuit: connector 1 0.010.08 in² (450 mm²) - cable stiffness: solid Power circuit: connector 2 0.010.04 in² (425 mm²) - cable stiffness: solid Control circuit: screw clamp terminals 1 0.000.00 in² (12.5 mm²) - cable stiffness: flexible with cable end  Control circuit: 10.62 lbf.in (1.2 N.m) screw clamp terminals flat Ø 6 mm Control circuit 10.62 lbf.in (1.2 N.m) screw clamp terminals Philips No 2 Power circuit 106.21 lbf.in (12 N.m) connector flat Ø 6 to Ø 8 mm Power circuit 106.21 lbf.in (12 N.m) connector flat Ø 6 to Ø 8 mm
Mounting Support	Control circuit 10.62 lbf.in (1.2 N.m) screw clamp terminals pozidriv No 2  Plate Rail
Environment	
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508
Product Certifications	UL CSA CCC EAC UKCA CB DNV-GL RINA

LROS (Lloyds register of shipping)

Ip Degree Of Protection	IP20 front face IEC 60529
Permissible Ambient Air Temperature Around The Device	-40140 °F (-4060 °C) 140158 °F (6070 °C) with derating
Operating Altitude	09842.52 ft (03000 m)
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open 2 Gn, 5300 Hz) Vibrations contactor closed 3 Gn, 5300 Hz) Shocks contactor open 8 Gn for 11 ms) Shocks contactor closed 10 Gn for 11 ms)
Height	5.00 in (127 mm)
Width	3.78 in (96 mm)
Depth	7.72 in (196 mm)
Net Weight	6.42 lb(US) (2.91 kg)

### Ordering and shipping details

Category	US10I1222359
Discount Schedule	0112
Gtin	3389110203639
Returnability	No
Country Of Origin	CZ

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.27 in (21.0 cm)
Package 1 Width	4.33 in (11.0 cm)
Package 1 Length	5.51 in (14.0 cm)
Package 1 Weight	6.12 lb(US) (2.777 kg)

### **Contractual warranty**

Warranty 18 months

## Sustainability Screen Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Environmental Disclosure</b>	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov