





Transformer, dry type, DOE 2016, 112.5kVA, 3 phase, 208V delta primary, 208Y/120V secondary, 21K, 150C rise

EX112T211H



(!) Discontinued on: Oct 20, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Square D
Product Or Component Type	Transformer
Device Short Name	DOE 2016
Transformer Type	Energy efficient
Device Application	Low voltage electrical distribution

Complementary

Box Number	21K
Phase	3 phase
Rated Operational Power In Va	112.5 kVA
Network Frequency	60 Hz
Type Of Cooling	Natural convection
Primary Voltage	208 V delta
Number Of Tap-Offs	1 5 % FCAN 2 5 % FCBN
Secondary Voltage	208Y/120 V
Coil Material	Aluminium
Basic Imp Level (Bil)	10 kV
Temperature Rise	150 °C 220 °C insulated
Doe Efficiency	98.85 % at 35 % load factor , 167 °F (75.0 °C)
Sound Level	47 dB 6 dB NEMA ST-20
%lz	4.20 %
%lx	0.0351 %
X/R Ratio	1.53
Let Through Current	7.5 kA
Transformer Losses	201.0 no load (core loss) 2578.0 load loss (coil loss)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Transformer Btu/Hr	928.2 16.6 %	
	1235.6 25 %	
	2885.0 50 %	
	5633.9 75 %	
	9482.3 100 %	
Height	45.98 in (1168 mm)	
Depth	24.02 in (610 mm)	
Width	31.30 in (795 mm)	
Net Weight	865.01 lb(US) (392.36 kg)	
Mounting Support	Floor	
	Floor, with 7400FMB	
	Ceiling, with 7400CMB21K	
Degree Of Protection	UL type 1	
	UL type 2, with 7400DS21K	
	UL type 3R, with 7400WS21K	
Electrical Connection	4 Hole Nema Pad primary 0.44 in (11.1 mm)	
	4 Hole Nema Pad secondary 0.44 in (11.1 mm)	
	6 Hole Nema Pad sec - XO 0.44 in (11.1 mm)	

Environment

Ambient Air Temperature For Operation	104 °F (40 °C)
Average Ambient Air Temperature For Operation	30 °C
Standards	UL 1561 CSA C22.2 No 47 NEMA ST-20

Ordering and shipping details

Category	US1PE2X16500
Discount Schedule	PE2X
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	965.00 lb(US) (437.717 kg)



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
Ø	Toxic Heavy Metal Free
②	Mercury Free
②	Rohs Exemption Information Yes
⊘	Pvc Free
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Approximate Dimensions



