

Product data sheet

Specifications

SQUARE D

Green Premium™



Transformer, dry type, DOE 2016, 150kVA, 3 phase, 480V delta primary, 208Y/120V secondary, 22K, 150C rise

EX150T3H

! Discontinued

! Discontinued on: Nov 22, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Square D
Product Or Component Type	Transformer
Device Short Name	DOE 2016
Transformer Type	Energy efficient
Device Application	Low voltage electrical distribution

Complementary

Box Number	22K
Phase	3 phase
Rated Operational Power In Va	150 kVA
Network Frequency	60 Hz
Type Of Cooling	Natural convection
Primary Voltage	480 V delta
Number Of Tap-Offs	2 2.5 % FCAN 4 2.5 % FCBN
Secondary Voltage	208Y/120 V
Coil Material	Aluminium
Basic Imp Level (Bil)	10 kV
Temperature Rise	150 °C 220 °C insulated
Doe Efficiency	99 % at 35 % load factor , 167 °F (75.0 °C)
Sound Level	47 dB 3 dB NEMA ST-20
%Iz	4.20 %
%Ix	0.036 %
X/R Ratio	1.69
Let Through Current	10.0 kA
Transformer Losses	210.0 no load (core loss) 3192.0 load loss (coil loss)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Transformer Btu/Hr	1016.677571966784 16.6 % 1397.272149 25 % 3439.439136 50 % 6843.050781 75 % 11608.107084 100 %
Height	49.09 in (1247 mm)
Depth	28.46 in (723 mm)
Width	33.66 in (855 mm)
Net Weight	1100.00 lb(US) (498.95 kg)
Mounting Support	Floor Floor, with 7400FMB Ceiling, with 7400CMB22K
Degree Of Protection	UL type 1 UL type 2, with 7400DS22K UL type 3R, with 7400WS22K
Electrical Connection	4 Hole Nema Pad primary 0.44 in (11.1 mm) 4 Hole Nema Pad secondary 0.44 in (11.1 mm) 6 Hole Nema Pad sec - XO 0.44 in (11.1 mm)

Environment

Ambient Air Temperature For Operation	104 °F (40 °C)
Average Ambient Air Temperature For Operation	30 °C
Standards	UL 1561 CSA C22.2 No 47 NEMA ST-20

Ordering and shipping details

Category	US1PE2X16250
Discount Schedule	PE2X
Gtin	785901974598
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	54.80 in (139.19 cm)
Package 1 Width	32.40 in (82.3 cm)
Package 1 Length	38.50 in (97.79 cm)
Package 1 Weight	1198.01 lb(US) (543.41 kg)

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Approximate Dimensions

