Product data sheet

Specifications





TeSys Deca thermal overload relays - 0.25...0.4 A - class 10A

LR3D03

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 60.00 USD

Main

| Range | TeSys TeSys Deca |
|--|--|
| Product Name | TeSys LRD TeSys Deca |
| Product Or Component Type | Non differential thermal overload relay |
| Device Short Name | LR3D |
| Relay Application | Motor protection |
| Product Compatibility | LC1D32 LC1D12 LC1D38 LC1D18 LC1D25 LC1D09 |
| Network Type | DC AC |
| Thermal Overload Class | Class 10A IEC 60947-4-1 |
| Thermal Protection Adjustment Range | 0.250.4 A |
| [Ui] Rated Insulation Voltage | Power circuit 600 V CSA Power circuit 600 V UL Power circuit 690 V IEC 60947-4-1 |

Complementary

| Network Frequency | 0400 Hz |
|--|--|
| Mounting Support | Plate, with specific accessories Rail, with specific accessories Under contactor |
| Tripping Threshold | 1.14 +/- 0.06 Ir IEC 60947-4-1 |
| Auxiliary Contact Composition | 1 NO + 1 NC |
| [Ith] Conventional Free Air Thermal Current | 5 A signalling circuit |
| Permissible Current | 3 A 120 V AC-15 signalling circuit 0.22 A 125 V DC-13 signalling circuit |
| [Ue] Rated Operational Voltage | 690 V AC 0400 Hz power circuit IEC 60947-4-1 |
| Associated Fuse Rating | 4 A gG for signalling circuit 4 A BS for signalling circuit |
| [Uimp] Rated Impulse Withstand Voltage | 6 kV |
| Phase Failure Sensitivity | Tripping current 130 % of Ir on two phase, the last one at 0 |
| Control Type | Red push-button stop Blue push-button reset |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Temperature Compensation | -4140 °F (-2060 °C) |
|--------------------------|--|
| Connections - Terminals | Control circuit screw clamp terminals 2 0.000.00 in ² (12.5 mm ²) flexible without cable end |
| | Control circuit screw clamp terminals 2 0.000.00 in ² (12.5 mm ²) flexible with cable end |
| | Control circuit screw clamp terminals 2 0.000.00 in ² (12.5 mm ²) solid without cable end |
| | Power circuit screw clamp terminals 1 0.000.02 in ² (1.510 mm ²) flexible without cable end |
| | Power circuit screw clamp terminals 1 0.000.01 in ² (14 mm ²) flexible with cable end |
| | Power circuit screw clamp terminals 1 0.000.01 in ² (16 mm ²) solid without cable end |
| Tightening Torque | Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals |
| Height | 2.60 in (66 mm) |
| Width | 1.77 in (45 mm) |
| Depth | 2.76 in (70 mm) |
| Net Weight | 0.27 lb(US) (0.124 kg) |

Environment

| Climatic Withstand | IACS E10 |
|--|--|
| Ip Degree Of Protection | IP20 conforming to IEC 60529 |
| Ambient Air Temperature For Operation | -4140 °F (-2060 °C) without derating IEC 60947-4-1 |
| Ambient Air Temperature For Storage | -76158 °F (-6070 °C) |
| Flame Retardance | V1 conforming to UL 94 |
| Mechanical Robustness | Vibrations6 Gn IEC 60068-2-6 Shocks15 Gn for 11 ms IEC 60068-2-7 |
| Dielectric Strength | 1.89 kV 50 Hz IEC 60947-1 |
| Standards | EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-5-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5 EN 50495 |
| Product Certifications | IEC UL CSA CCC EAC BV RINA DNV-GL LROS (Lloyds register of shipping) ATEX INERIS UKCA |

Ordering and shipping details

| Category | US10I1222347 |
|-------------------|---------------|
| Discount Schedule | 0112 |
| Gtin | 3389110346893 |
| Returnability | No |
| Country Of Origin | FR |

Packing Units

| · | |
|------------------------------|------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.97 in (5 cm) |
| Package 1 Width | 3.54 in (9 cm) |
| Package 1 Length | 3.15 in (8 cm) |
| Package 1 Weight | 4.73 oz (134 g) |
| Unit Type Of Package 2 | S02 |
| Number Of Units In Package 2 | 24 |
| Package 2 Height | 5.91 in (15 cm) |
| Package 2 Width | 11.81 in (30 cm) |
| Package 2 Length | 15.75 in (40 cm) |
| Package 2 Weight | 7.82 lb(US) (3.548 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |