Product data sheet

Specifications





Auxiliary contact, TeSys GS, 1 C/O, 4P, 250 to 400A, fuse type DIN, size 1-2, for GS1 GS2 Blown fuse

GS1AF44

! Discontinued on: Jan 31, 2024

① Discontinued

Main

Range Of Product	TeSys	
Device Short Name	GS1AF	
Product Or Component Type	Auxiliary contact	
Contact Application	Blown fuse signalling	
Contacts Type And Composition	1 C/O	
Contact Operation	Instantaneous	
[Ith] Conventional Free Air Thermal Current	e Air 16 A (at 104 °F (40 °C))	
[le] Rated Operational Current	12 A 24 V DC-13	
	2 A 48 V DC-13	
	3 A 400 V AC-15	
	4 A 230 V AC-15	
	0.4 A 220 V DC-13	
	0.6 A 110 V DC-13	

Complementary

Range Compatibility	TeSys TeSys GS fuse-switch disconnector	
Mechanical Durability	30000 cycles	
Electrical Durability	30000 cycles AC-15	
Product Compatibility	GS	
Poles Description	4P	
Switch Rated Current	400 A 250 A	
Fuse Type	DIN NFC	
Fuse Size	2 1	
Net Weight	0.07 lb(US) (0.032 kg)	

Ordering and shipping details

Category	18402-WORLD SERVICE PARTS(CONTROL ACCESS)	
Discount Schedule	CP10	
Gtin	3389110563351	
Returnability	No	
Country Of Origin	FR	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.18 in (3.0 cm)	
Package 1 Width	5.51 in (14.0 cm)	
Package 1 Length	ngth 9.84 in (25.0 cm)	
Package 1 Weight	1.59 oz (45.0 g)	
Unit Type Of Package 2	S01	
Number Of Units In Package 2	4	
Package 2 Height	5.91 in (15.0 cm)	
Package 2 Width	2 Width 5.91 in (15.0 cm)	
Package 2 Length	15.75 in (40.0 cm)	
Package 2 Weight	9.88 oz (280.0 g)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov