

Product data sheet

Specifications



TeSys Deca thermal overload relays , 4...6A , class 20

LRD1510

Product availability: Stock - Normally stocked in distribution facility

Price*: 60.00 USD

Main

Range	TeSys
Product Name	TeSys LRD TeSys Deca
Product Or Component Type	Differential thermal overload relay
Device Short Name	LRD
Relay Application	Motor protection
Product Compatibility	LC1D18 LC1D32 LC1D12 LC1D25 LC1D09
Network Type	AC DC
Thermal Overload Class	Class 20 IEC 60947-4-1
Thermal Protection Adjustment Range	4...6 A
[Ui] Rated Insulation Voltage	Power circuit 600 V CSA Power circuit 600 V UL Power circuit 690 V IEC 60947-4-1

Complementary

Network Frequency	0...400 Hz
Mounting Support	Plate, with specific accessories Rail, with specific accessories Under contactor
Tripping Threshold	1.14 +/- 0.06 Ir IEC 60947-4-1
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A signalling circuit
Permissible Current	1.5 A 240 V AC-15 signalling circuit 0.1 A 250 V DC-13 signalling circuit
[Ue] Rated Operational Voltage	690 V AC 0...400 Hz power circuit IEC 60947-4-1
Associated Fuse Rating	4 A gG for signalling circuit 4 A BS for signalling circuit
[Uimp] Rated Impulse Withstand Voltage	6 kV
Phase Failure Sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0
Control Type	Red push-button stop Blue push-button reset
Temperature Compensation	-4...140 °F (-20...60 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Control circuit screw clamp terminals 2 0.00...0.00 in² (1...2.5 mm²) flexible without cable end Control circuit screw clamp terminals 2 0.00...0.00 in² (1...2.5 mm²) flexible with cable end Control circuit screw clamp terminals 2 0.00...0.00 in² (1...2.5 mm²) solid without cable end Power circuit screw clamp terminals 1 0.00...0.02 in² (1.5...10 mm²) flexible without cable end Power circuit screw clamp terminals 1 0.00...0.01 in² (1...4 mm²) flexible with cable end Power circuit screw clamp terminals 1 0.00...0.01 in² (1...6 mm²) solid without cable end
Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Power circuit 16.37 lbf.in (1.85 N.m) screw clamp terminals
Width	1.77 in (45 mm)
Depth	3.62 in (92 mm)
Net Weight	0.42 lb(US) (0.19 kg)

Environment

Climatic Withstand	IACS E10
Ip Degree Of Protection	IP20 conforming to IEC 60529
Ambient Air Temperature For Operation	-4...140 °F (-20...60 °C) without derating IEC 60947-4-1
Ambient Air Temperature For Storage	-76...158 °F (-60...70 °C)
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations6 Gn IEC 60068-2-6 Shocks15 Gn for 11 ms IEC 60068-2-7
Dielectric Strength	1.89 kV 50 Hz IEC 60947-1
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1
Product Certifications	IEC UL CSA EAC DNV-GL LROS (Lloyds register of shipping) UKCA

Ordering and shipping details

Category	US10I1222347
Discount Schedule	0I12
Gtin	3389110146691
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.07 in (7.800 cm)

Package 1 Width	3.78 in (9.600 cm)
Package 1 Length	2.09 in (5.300 cm)
Package 1 Weight	7.94 oz (225.000 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	25
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	13.39 lb(US) (6.075 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Reach Free Of Svhc

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information.

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)