


Product data sheet

Specifications



Function module, thermal overload signalling, TeSys Ultra, 1 NO + 1 NC

LUFDH11

Product availability: Stock - Normally stocked in distribution facility

Price*: 156.00 USD

Main

Range	TeSys
Device Short Name	LUF
Product Or Component Type	Function module
Product Compatibility	LUCC LUCB LUCD

Complementary

Mounting Mode	Plug-in
Mounting Location	Front side
Main Function Available	Thermal overload signalling and manual reset
Auxiliary Contact Composition	1 NO + 1 NC
Communication Of Faults	LED front panel
[Us] Rated Supply Voltage	24...240 V DC 24...240 V AC
Current Consumption	7 mA 24 V DC 1.1 mA 240 V AC
Discrete Output Function	1 NO + 1 NC AC-15) 230 V 400 VA 100000 cycles 1 NO + 1 NC DC-13) 24 V 50 W 100000 cycles
[Ith] Conventional Free Air Thermal Current	2 A 158 °F (70 °C)
Short-Circuit Protection	2 A fuse gG IEC 60947-5-1
Input Type	Remote reset 0.00...0.00 in² (0.2...1.5 mm²) <1640.42 ft (500 m) 50 Ohm 52.8 mH 0.093 nF
Connection Pitch	0.20 in (5.08 mm)
Connections - Terminals	screw clamp terminals 2 0.00...0.00 in² (0.2...1 mm²) rigid without cable end screw clamp terminals 2 0.00...0.00 in² (0.25...1 mm²) flexible with cable end screw clamp terminals 2 0.00...0.00 in² (0.5...1 mm²) flexible with cable end
Tightening Torque	4.43...5.31 lbf.in (0.5...0.6 N.m) 0.14 in (3.5 mm) flat
Net Weight	0.13 lb(US) (0.06 kg)

Ordering and shipping details

Category	US10I1122399
Discount Schedule	0I11
Gtin	3389119200356

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.30 in (3.3 cm)
Package 1 Width	1.85 in (4.7 cm)
Package 1 Length	4.13 in (10.5 cm)
Package 1 Weight	2.65 oz (75.0 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	15
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	2.97 lb(US) (1.346 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.