

Product data sheet

Specifications



Motor circuit breaker, TeSys Deca, 3P, 80A, Icu 100kA, thermal magnetic, multifunction, UL489

GV4PB80S

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 636.00 USD

Main

Range Of Product	TeSys GV4
Range	TeSys Deca TeSys Deca
Device Short Name	GV4PB
Product Name	TeSys GV4 TeSys Deca
Product Or Component Type	Motor circuit breaker
Device Application	Motor protection
Trip Unit Technology	Thermal-magnetic Electronic

Complementary

Poles Description	3P
Utilisation Category	Category A IEC 60947-2 AC-3 IEC 60947-4-1
Operating Position	Any position
Breaking Capacity	100 kA SCCR 240 V AC 60 Hz UL 489 65 kA SCCR 480Y/277 V AC 60 Hz UL 489 25 kA SCCR 600Y/347 V AC 60 Hz UL 489 120 kA Icu 220/240 V AC 50/60 Hz IEC 60947-2 100 kA Icu 380/415 V AC 50/60 Hz IEC 60947-2 70 kA Icu 440 V AC 50/60 Hz IEC 60947-2 30 kA Icu 500 V AC 50/60 Hz IEC 60947-2 18 kA Icu 525 V AC 50/60 Hz IEC 60947-2 10 kA Icu 660/690 V AC 50/60 Hz IEC 60947-2
[Ics] Rated Service Short-Circuit Breaking Capacity	100 % 220/240 V AC 50/60 Hz IEC 60947-2 100 % 380/415 V AC 50/60 Hz IEC 60947-2 100 % 440 V AC 50/60 Hz IEC 60947-2 100 % 500 V AC 50/60 Hz IEC 60947-2 100 % 525 V AC 50/60 Hz IEC 60947-2 25 % 660/690 V AC 50/60 Hz IEC 60947-2
Control Type	Toggle
Line Rated Current	80 A
Magnetic Tripping Current	1360 A
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz IEC 60947-2 600Y/347 V AC 60 Hz UL 489
[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz IEC 60947-2
[Ith] Conventional Free Air Thermal Current	115 A IEC 60947-4-1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2
Power Dissipation Per Pole	4.6 W
Mechanical Durability	40000 cycles
Electrical Durability	14000 cycles AC-3 440 V In/2 7000 cycles AC-3 440 V In
Maximum Operating Rate	25 cyc/h
Rated Duty	Continuous IEC 60947-4-1
Connections - Terminals	EverLink BTR screw connectors top) 1 0.00...0.11 in² (1.5...70 mm²) - rigid EverLink BTR screw connectors top) 1 0.00...0.08 in² (1.5...50 mm²) - flexible EverLink BTR screw connectors bottom) 1 0.00...0.15 in² (2.5...95 mm²) - rigid EverLink BTR screw connectors bottom) 1 0.00...0.11 in² (2.5...70 mm²) - flexible
Tightening Torque	79.66 lbf.in (9 N.m) 0.02...0.15 in² (16...95 mm²) 44.25 lbf.in (5 N.m) 0.00...0.02 in² (1.5...10 mm²)
Mechanical Robustness	Vibrations +/- 1 mm 2...13.2 Hz IEC 60068-2-6 Vibrations 0.7 gn 13.2...100 Hz IEC 60068-2-6 Shocks 15 gn 11 ms IEC 60068-2-27
Phase Failure Sensitivity	Yes IEC 60947-4-1
Height	6.73 in (171 mm)
Width	3.19 in (81 mm)
Depth	4.57 in (116 mm)
Net Weight	3.20 lb(US) (1.45 kg)
Color	Gray RAL 7016)
Suitability For Isolation	Yes IEC 60947-1

Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-2 EN/IEC 60947-4-1 UL 489 CSA C22.2 No 5
Product Certifications	IEC UL CSA
Climatic Withstand	IACS E10
Ik Degree Of Protection	IK07 IEC 62262
Pollution Degree	3
Ip Degree Of Protection	IP40 IEC 60529
Ambient Air Temperature For Storage	-58...185 °F (-50...85 °C)
Fire Resistance	1760 °F (960 °C) IEC 60695-2-11
Operating Altitude	5000 m
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)

Ordering and shipping details

Category	US10I1122365
Discount Schedule	0I11
Gtin	3606489868697
Returnability	Yes

Country Of Origin	US
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.92 in (12.5 cm)
Package 1 Width	3.54 in (9.0 cm)
Package 1 Length	8.88 in (22.55 cm)
Package 1 Weight	3.82 lb(US) (1.733 kg)
Unit Type Of Package 2	S03
Number Of Units In Package 2	5
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	20.94 lb(US) (9.5 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information