# **Product data sheet**

Specifications





# Circuit breaker frame, MasterPact MTZ2 08H10 drawout for MicroLogic X, 800A, 50kA/1150VAC (Icu), 4P

LV848735

#### Main

Range	MasterPacT	
Product Name	MasterPact MTZ2	
Device Short Name	MTZ2 08 H10	
Product Or Component Type	Circuit breaker	
Device Application	Power distribution protection	
Poles Description	4P	
Neutral Position	Left	
Control Unit	Without control unit	
Product Compatibility	control unit MicroLogic 2.0 X control unit MicroLogic 5.0 X control unit MicroLogic 6.0 X control unit MicroLogic 7.0 X control unit MicroLogic 2.0 Xi control unit MicroLogic 5.0 Xi control unit MicroLogic 6.0 Xi control unit MicroLogic 6.0 Xi control unit MicroLogic 7.0 Xi	
Line Rated Current	800 A 104 °F (40 °C)	
Performance Type	H10 50 kA 1150 V AC	
[Ue] Rated Operational Voltage	1150 V AC 50/60 Hz	
Suitability For Isolation	Yes EN/IEC 60947-2	
Selectivity Category	Category B	
Control Type	Push-button	
Mounting Mode	Drawout	

#### **Complementary**

,	
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	50 kA 1150 V AC 50/60 Hz
[Ics] Rated Service Breaking Capacity	50 kA 1150 V AC 50/60 Hz
[Icw] Rated Short-Time Withstand Current	50 kA 1 s 50 kA 0.5 s 50 kA 3 s
[Icm] Rated Short-Circuit Making Capacity	105 kA 1150 V AC 50/60 Hz
Sensor Rating	400 A 630 A 800 A
[Ui] Rated Insulation Voltage	1250 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	12 kV

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Power Dissipation In W	100 W
Maximum Breaking Time	25 ms
Maximum Closing Response Time	70 ms
Mounting Support	Rails Base plate
Upside Connection	Rear
Downside Connection	Rear
Connection Pitch	4.53 in (115 mm)
Mechanical Durability	25000 cycles with periodic preventive maintenance
Electrical Durability	500 cycles 1150 V AC 50/60 Hz EN/IEC 60947-2
Height	Drawout circuit breaker with chassis 17.28 in (439 mm) Drawout circuit breaker without chassis 11.81 in (300 mm)
Width	Drawout circuit breaker with chassis 21.89 in (556 mm) Drawout circuit breaker without chassis 19.41 in (493 mm)
Depth	Drawout circuit breaker with chassis 15.87 in (403 mm) Drawout circuit breaker without chassis 11.81 in (300 mm)
Net Weight	264.55 lb(US) (120 kg)
Standards	EN/IEC 60947-1 EN/IEC 60947-2 EN/IEC 60947-2 Annex H IEC 61557-12
Product Certifications	CE IECEE CB Scheme

#### **Environment**

Ip Degree Of Protection	IP30 conforming to EN 60529
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Operating Altitude	06561.68 ft (02000 m) without derating

## Ordering and shipping details

Gtin 3606480809392

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.04 in (0.1 cm)
Package 1 Width	0.04 in (0.1 cm)
Package 1 Length	0.08 in (0.2 cm)
Package 1 Weight	0.04 oz (1.0 g)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov