


# Product data sheet

Specifications



## TeSys F - contactor coil - LX0FK - 220 V latching - 24 V unlatching AC/ DC

LX0FK224

⚠ Discontinued

### Main

|                              |  |
|------------------------------|--|
| Range                        | TeSys  |
| Product Or Component Type    | Contactor coil   |
| Device Short Name            | LX0FK  |
| Control Circuit Type         | AC 50...400 Hz<br>DC standard  |
| [Uc] Control Circuit Voltage | 220 V AC 50...400 Hz latching<br>24 V AC 50...400 Hz unlatching<br>220 V DC latching<br>24 V DC unlatching |
| Average Resistance           | 29 Ohm latching 68 °F (20 °C)<br>26 Ohm unlatching 68 °F (20 °C)   |
| Product Compatibility        | CR1F500  |
| Operating Time               | 50...100 ms unlatching<br>40...80 ms latching  |
| Mechanical Durability        | 1 Mcycles  |
| Maximum Operating Rate       | 120 cyc/h 104 °F (40 °C)   |

### Complementary

|                                |  |
|--------------------------------|--|
| Control Circuit Voltage Limits | Latching: 0.85...1.1 Uc<br>Unlatching: 0.85...1.1 Uc |
|--------------------------------|--|

### Environment

|            |                       |
|------------|-----------------------|
| Net Weight | 2.69 lb(US) (1.22 kg) |
|------------|-----------------------|

### Ordering and shipping details

|                   |                                       |
|-------------------|---------------------------------------|
| Category          | 18401-WORLD SERVICE PARTS(CTR ACCESS) |
| Discount Schedule | CP10                                  |
| Gtin              | 3389110207156                         |
| Returnability     | No                                    |

### Packing Units

|                              |     |
|------------------------------|-----|
| Unit Type Of Package 1       | PCE |
| Number Of Units In Package 1 | 1   |

### Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months