

Product data sheet

Specifications



TeSys Deca - contactor coil - LX1D2 - 380...400 V AC 50 Hz for 9 to 18 A contactor

LX1D2Q5

⚠ Discontinued

Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX1D2
Control Circuit Type	AC 50 Hz
[Uc] Control Circuit Voltage	380...400 V AC 50 Hz
Average Resistance	1848 Ohm 68 °F (20 °C)
Inductance Of Closed Circuit	67 H
Product Compatibility	LC1D09...D18

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Operational: 0.8...1.1 Uc at 50 Hz (at <131 °F (55 °C))
Inrush Power In Va	60 VA 50 Hz cos phi 0.75 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	7 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))

Environment

Net Weight	1.54 lb(US) (0.7 kg)
------------	----------------------

Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
Gtin	00785901260660
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications