

Product data sheet

Specifications



TeSys Deca - contactor coil - LX1D2 - 440 V AC 50/60 Hz for 9 to 18 A contactor

LX1D2R7

⚠ Discontinued on: Jul 12, 2021

⚠ Discontinued

Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX1D2
Control Circuit Type	AC 50/60 Hz
[Uc] Control Circuit Voltage	440 V AC 50/60 Hz
Average Resistance	2242 Ohm 68 °F (20 °C)
Inductance Of Closed Circuit	79 H
Product Compatibility	LC1D09...D18

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Operational: 0.8...1.1 Uc at 50/60 Hz (at <131 °F (55 °C))
Inrush Power In Va	70 VA 50/60 Hz cos phi 0.75 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	8 VA 50/60 Hz cos phi 0.3 (at 68 °F (20 °C))

Environment

Net Weight	1.54 lb(US) (0.7 kg)
------------	----------------------

Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
Gtin	3389110207637
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7 cm)
Package 1 Width	1.77 in (4.5 cm)
Package 1 Length	1.38 in (3.5 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	2.79 oz (79 g)
------------------	----------------

Contractual warranty

Warranty	18 months
----------	-----------