


Product data sheet

Specifications



contactor coil - TeSys F - LX1FG - 84 V AC - 50 Hz

LX1FG084

⚠ Discontinued on: Jul 12, 2021

⚠ Discontinued

Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX1FG
Range Compatibility	TeSys TeSys F LC1F contactor
Product Compatibility	LC1F225 LC1F185
Control Circuit Type	AC 50 Hz
[Uc] Control Circuit Voltage	84 V AC 50 Hz 100 V AC 60 Hz
Inductance Of Closed Circuit	0.37 H
Average Resistance	2.22 Ohm 68 °F (20 °C)
Operating Time	20...35 ms closing 7...15 ms opening
Mechanical Durability	10 Mcycles
Maximum Operating Rate	2400 cyc/h 131 °F (55 °C)

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Drop-out 0.35...0.55 Uc 50/60 Hz 131 °F (55 °C) Operational 0.85...1.1 Uc 50/60 Hz 131 °F (55 °C))
Inrush Power In Va	805 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C)) 970 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	55 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C)) 66 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat Dissipation	18...24 W 50 Hz

Environment

Ambient Air Temperature For Operation	23...131 °F (-5...55 °C)
Net Weight	1.21 lb(US) (0.55 kg)

Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
Gtin	3389118109148

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
---------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.44 in (6.2 cm)
Package 1 Width	3.11 in (7.9 cm)
Package 1 Length	6.54 in (16.6 cm)
Package 1 Weight	19.40 oz (550 g)

Contractual warranty

Warranty	18 months
----------	-----------