

Product data sheet

Specifications



TeSys Integral - coil - 24 V AC 50 Hz

LX1LD0249

⚠ Discontinued on: Dec 23, 2020

⚠ Discontinued

Main

Range	TeSys
Product Or Component Type	Coil
Range Compatibility	TeSys TeSys Integral contactor breaker
Product Compatibility	LD.LD...BD
Device Short Name	LX1
Control Circuit Type	AC 50 Hz
[Uc] Control Circuit Voltage	24 V AC 50 Hz
Average Resistance	0.323 Ohm 68 °F (20 °C)
Inductance Of Closed Circuit	0.071 H

Complementary

Control Circuit Voltage Limits	Operational: 0.85...1.1 Uc (at <131 °F (55 °C)) Drop-out: 0.25...0.7 Uc (at <131 °F (55 °C))
Inrush Power In Va	350...400 VA 50 Hz cos phi 0.55
Hold-In Power Consumption In Va	20...30 VA 50 Hz cos phi 0.28

Environment

Net Weight	0.66 lb(US) (0.3 kg)
------------	----------------------

Ordering and shipping details

Category	22384-STARTERS,INTEGRAL,ACCESS
Discount Schedule	I11
Gtin	3389110246421
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.15 in (8 cm)
Package 1 Width	2.95 in (7.5 cm)
Package 1 Length	4.13 in (10.5 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	12.13 oz (344 g)
------------------	------------------

Contractual warranty

Warranty	18 months
----------	-----------