## Product data sheet

Specifications





# TeSys F - contactor coil - LX4FG - 24 V DC wide range

LX4FG020

() Discontinued on: Feb 17, 2021



#### Main

Range	TeSys	
Product Or Component Type	Contactor coil	
Device Short Name	LX4FG	
Range Compatibility	TeSys TeSys F LC1F contactor	
Product Compatibility	LC1F225 LC1F185	
Control Circuit Type	DC wide range	
[Uc] Control Circuit Voltage	24 V DC	
Inductance Of Closed Circuit	9.3 H	
Average Resistance	0.52 Ohm inrush 68 °F (20 °C) 112 Ohm holding 68 °F (20 °C)	
Operating Time	3040 ms closing 3050 ms opening	
Mechanical Durability	1 Mcycles	
Maximum Operating Rate	60 cyc/h 158 °F (70 °C)	

#### Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Operational 0.71.25 Uc 158 °F (70 °C)) Drop-out 0.20.45 Uc 158 °F (70 °C))
Inrush Power In W	800 W 68 °F (20 °C))
Hold-In Power Consumption In W	5 W 68 °F (20 °C)

#### Environment

Ambient Air Temperature For Operation	-67158 °F (-5570 °C)
Net Weight	1.21 lb(US) (0.55 kg)

## Ordering and shipping details

Category	18401-WORLD SERVICE PARTS(CTR ACCESS)
Discount Schedule	CP10
Gtin	3389110190571
Returnability	No
Country Of Origin	CZ

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.44 in (6.2 cm)
Package 1 Width	3.11 in (7.9 cm)
Package 1 Length	6.54 in (16.6 cm)
Package 1 Weight	19.40 oz (550.0 g)

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information