# **Product data sheet**

Specifications





# integrated drive ILS with stepper motor - 24..48 V - EtherCAT - 3.5 A

ILS2E573PB1A0

! Discontinued on: Oct 9, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range Of Product	Lexium integrated drive
Product Or Component Type	Motion integrated drive
Device Short Name	ILS
Motor Type	3-phase stepper motor
Number Of Motor Poles	6
Phase	Single phase
[Us] Rated Supply Voltage	48 V 24 V
Network Type	DC
Communication Interface	EtherCAT, Integrated
Length	5.47 in (138.9 mm)
Winding Type	Medium speed of rotation and medium torque
Electrical Connection	Printed circuit board connector
Holding Brake	Without
Gear Box Type	Without
Nominal Speed	300 rpm 24 V 600 rpm 48 V
Nominal Torque	13.28 lbf.in (1.5 N.m)
Holding Torque	13.28 lbf.in (1.5 N.m)

# Complementary

Transmission Rate	100 Mbits
Mounting Support	Flange
Motor Flange Size	2.24 in (57 mm)
Number Of Motor Stacks	3
Centring Collar Diameter	1.50 in (38.1 mm)
Centring Collar Depth	0.06 in (1.6 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.20 in (5.2 mm)
Circle Diameter Of The Mounting Holes	2.62 in (66.6 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Feedback Type	Index pulse
Shaft End	Untapped
Second Shaft	Without second shaft end
Shaft Diameter	0.31 in (8 mm)
Shaft Length	0.83 in (21 mm)
Supply Voltage Limits	1855 V
Current Consumption	3500 mA maximum continuous
Associated Fuse Rating	16 A
Commissioning Interface	RS485 Modbus TCP 9.6, 19.2 and 38.4 kbauds)
Input/Output Type	4 signals (each be used as input or output)
Voltage State 0 Guaranteed	-34.5 V
Voltage State 1 Guaranteed	1530 V
Discrete Input Current	10 mA at 24 V safety input 2 mA at 24 V 24 V signal interface
Discrete Output Voltage	2325 V
Maximum Switching Current	100 mA per output 200 mA total
Protection Type	Safe torque off Short circuit of the output voltage Overload of output voltage
Peak Stall Torque	13.28 lbf.in (1.5 N.m)
Continuous Stall Torque	13.28 lbf.in (1.5 N.m)
Speed Feedback Resolution	20000 points/turn
Accuracy Error	+/- 6 arc min
Rotor Inertia	0.38 kg.cm²
Maximum Mechanical Speed	3000 rpm
Maximum Radial Force Fr	50 N
Maximum Axial Force Fa	100 N tensile force) 8.4 N force pressure)
Service Life In Hours	20000 h bearing
Marking	CE
Type Of Cooling	Natural convection
Net Weight	4.41 lb(US) (2 kg)
Environment	
	FN 64000 2:2004
Standards	EN 61800-3:2001, second environment IEC 60072-1 EN 61800-3: 2001-02 EN/IEC 50178 IEC 61800-3, Ed 2 EN 50347 EN/IEC 61800-3

Standards	EN 61800-3:2001, second environment
	IEC 60072-1
	EN 61800-3 : 2001-02
	EN/IEC 50178
	IEC 61800-3, Ed 2
	EN 50347
	EN/IEC 61800-3
Product Certifications	cUL
	UL
	TÜV
Ambient Air Temperature For Operation	104131 °F (4055 °C) with power derating of 2 % per °C) 32104 °F (040 °C) without derating)

Permissible Ambient Air Temperature Around The Device	221 °F (105 °C) power amplifier 230 °F (110 °C) motor	
Ambient Air Temperature For Storage	-13158 °F (-2570 °C)	
Operating Altitude	<= 3280.84 ft (1000 m) without derating	
Relative Humidity	1585 % without condensation	
Vibration Resistance	20 m/s² 10500 Hz) 10 cycles EN/IEC 60068-2-6	
Shock Resistance	150 m/s <sup>2</sup> 1000 shocks EN/IEC 60068-2-29	
Ip Degree Of Protection	IP41 shaft bushing: conforming to EN/IEC 60034-5 IP54 total except shaft bushing: conforming to EN/IEC 60034-5	

# Ordering and shipping details

Category	US1PC5618288
Discount Schedule	PC56
Gtin	3606485189437
Returnability	No
Country Of Origin	DE

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.33 in (11 cm)
Package 1 Width	6.69 in (17 cm)
Package 1 Length	9.45 in (24 cm)
Package 1 Weight	5.09 lb(US) (2.309 kg)
Unit Type Of Package 2	S04
Number Of Units In Package 2	5
Package 2 Height	11.81 in (30 cm)
Package 2 Width	15.75 in (40 cm)
Package 2 Length	23.62 in (60 cm)
Package 2 Weight	28.21 lb(US) (12.797 kg)
Package 3 Height	11.81 in (30.0 cm)

# **Contractual warranty**

Warranty 18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes
	Pvc Free	


#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information

#### **Dimensions Drawings**

#### **Integrated Drive**


#### **Dimensions**



- 1 Accessories: I/O signal insert with industrial connectors
- 2 Option: industrial connectors
- 3 Earth (ground) terminal
- 4 Accessories: cable entries  $\emptyset = 3 \dots 9 \text{ mm}/0.12 \dots 0.35 \text{ in.}$
- L 138.9 mm/5.47 in.
- D 8.00 mm/0.31 in.

Connections and Schema

## Connection Example with 4 I/O Signals




# **Product data sheet**

## ILS2E573PB1A0

#### Performance Curves

#### **Torque Characteristics**



- X Speed of rotation in rpm
- Y Torque in Nm
- 1.1 Max. torque at 24 V
- 1.2 Max. torque at 48 V