Product data sheet





integrated drive ILS with stepper motor - 24..48 V - Modbus TCP -3.5 A

ILS2T571PB1A0

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,170.00 USD

Main

| Range Of Product | Lexium integrated drive |
|---------------------------|--|
| Product Or Component Type | Motion integrated drive |
| Device Short Name | ILS |
| Motor Type | 3-phase stepper motor |
| Number Of Motor Poles | 6 |
| Phase | Single phase |
| [Us] Rated Supply Voltage | 24 V 48 V |
| Network Type | DC |
| Communication Interface | Modbus TCP, Integrated |
| Length | 4.01 in (101.9 mm) |
| Winding Type | Medium speed of rotation and medium torque |
| Electrical Connection | Printed circuit board connector |
| Holding Brake | Without |
| Gear Box Type | Without |
| Nominal Speed | 1000 rpm 24 V 2000 rpm 48 V |
| Nominal Torque | 3.98 lbf.in (0.45 N.m) |
| Holding Torque | 3.98 lbf.in (0.45 N.m) |

Complementary

| Transmission Rate | 10, 100 Mbits |
|---------------------------------------|-------------------|
| Mounting Support | Flange |
| Motor Flange Size | 2.24 in (57 mm) |
| Number Of Motor Stacks | 1 |
| Centring Collar Diameter | 1.50 in (38.1 mm) |
| Centring Collar Depth | 0.06 in (1.6 mm) |
| Number Of Mounting Holes | 4 |
| Mounting Holes Diameter | 0.20 in (5.2 mm) |
| Circle Diameter Of The Mounting Holes | 2.62 in (66.6 mm) |
| Feedback Type | Index pulse |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Shaft End | Untapped |
|----------------------------|--|
| Second Shaft | Without second shaft end |
| Shaft Diameter | 0.25 in (6.35 mm) |
| Shaft Length | 0.83 in (21 mm) |
| Supply Voltage Limits | 1855 V |
| Current Consumption | 3500 mA maximum continuous |
| Associated Fuse Rating | 16 A |
| Commissioning Interface | RS485 Modbus TCP 9.6, 19.2 and 38.4 kbauds) |
| Input/Output Type | 4 signals (each be used as input or output) |
| Voltage State 0 Guaranteed | -34.5 V |
| Voltage State 1 Guaranteed | 1530 V |
| Discrete Input Current | 10 mA at 24 V safety input 2 mA at 24 V 24 V signal interface |
| Discrete Output Voltage | 2325 V |
| Maximum Switching Current | 100 mA per output 200 mA total |
| Protection Type | Overload of output voltage Short circuit of the output voltage Safe torque off |
| Peak Stall Torque | 3.98 lbf.in (0.45 N.m) |
| Continuous Stall Torque | 3.98 lbf.in (0.45 N.m) |
| Speed Feedback Resolution | 20000 points/turn |
| Accuracy Error | +/- 6 arc min |
| Rotor Inertia | 0.1 kg.cm² |
| Maximum Mechanical Speed | 3000 rpm |
| Maximum Radial Force Fr | 24 N |
| Maximum Axial Force Fa | 100 N tensile force) 8.4 N force pressure) |
| Service Life In Hours | 20000 h bearing |
| Marking | CE |
| Type Of Cooling | Natural convection |
| Net Weight | 2.87 lb(US) (1.3 kg) |

Environment

| Standards | IEC 50178 EN 61800-3 : 2001-02 IEC 61800-3 IEC 50347 IEC 61800-3, Ed 2 IEC 60072-1 EN 61800-3:2001, second environment |
|--|--|
| Product Certifications | cUL UL TÜV |
| Ambient Air Temperature For Operation | 104131 °F (4055 °C) with power derating of 2 % per °C) 32104 °F (040 °C) without derating) |
| Permissible Ambient Air Temperature Around The Device | 221 °F (105 °C) power amplifier 230 °F (110 °C) motor |

| Ambient Air Temperature For Storage | -13158 °F (-2570 °C) |
|-------------------------------------|--|
| Operating Altitude | <= 3280.84 ft (1000 m) without derating |
| Relative Humidity | 1585 % without condensation |
| Vibration Resistance | 20 m/s² 10500 Hz) 10 cycles IEC 60068-2-6 |
| Shock Resistance | 150 m/s² 1000 shocks IEC 60068-2-29 |
| Ip Degree Of Protection | IP41 shaft bushing: conforming to IEC 60034-5 IP54 total except shaft bushing: conforming to IEC 60034-5 |

Ordering and shipping details

| Category | US1PC5618288 |
|-------------------|---------------|
| Discount Schedule | PC56 |
| Gtin | 3606485189833 |
| Returnability | No |
| Country Of Origin | DE |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.15 in (8.0 cm) |
| Package 1 Width | 7.28 in (18.5 cm) |
| Package 1 Length | 13.98 in (35.5 cm) |
| Package 1 Weight | 3.53 lb(US) (1.6 kg) |

Contractual warranty

Warranty 18 months

Sustainability Green Premium"

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Mercury Free | |
|----------|----------------------------|-----|
| | Rohs Exemption Information | Yes |
| ② | Pvc Free | |


Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| | |

Dimensions Drawings

Integrated Drive


Dimensions



- 1 Accessories: I/O signal insert with industrial connectors
- 2 Option: industrial connectors
- 3 Earth (ground) terminal
- 4 Accessories: cable entries $\emptyset = 3 \dots 9 \text{ mm}/0.12 \dots 0.35 \text{ in.}$
- L 101.9 mm/4.01 in.
- D 6.35 mm/0.25 in.

Connections and Schema

Connection Example with 4 I/O Signals




Product data sheet

ILS2T571PB1A0

Performance Curves

Torque Characteristics



- X Speed of rotation in rpm
- Y Torque in Nm
- 1.1 Max. torque at 24 V
- 1.2 Max. torque at 48 V