# **Product data sheet**

Specification





## Miniature circuit breaker (MCB), Multi9 C60N, 3P, 1A, C curve, 10kA (IEC/EN 60947-2)

M9F11301

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 300.00 USD

### Main

| Range                     | Multi9   |  |
|---------------------------|--|--|
| Product Name              | Multi9 C60   |  |
| Product Or Component Type | Miniature circuit-breaker  |  |
| Device Short Name         | C60N   |  |
| Device Application        | Distribution   |  |
| Poles Description         | 3P   |  |
| Number Of Protected Poles | 3  |  |
| Line Rated Current        | 1 A 122 °F (50 °C) EN/IEC 60947-2  |  |
| Network Type              | DC<br>AC   |  |
| Trip Unit Technology      | Thermal-magnetic   |  |
| Curve Code                | С  |  |
| Breaking Capacity         | 30 kA Icu <= 125 V DC EN/IEC 60947-2<br>10 kA Icu 415 V AC 50/60 Hz between phases EN/IEC 60947-2<br>20 kA Icu 240 V AC 50/60 Hz between phases EN/IEC 60947-2<br>6 kA Icu 440 V AC 50/60 Hz between phases EN/IEC 60947-2 |  |
| Utilisation Category      | Category A EN/IEC 60947-2  |  |
| Suitability For Isolation | y For Isolation Yes EN/IEC 60947-2   |  |
| Standards                 | EN/IEC 60947-2   |  |
| Product Certifications    | EAC<br>KC<br>CCC   |  |

### Complementary

| Network Frequency              | 50/60 Hz                                       |
|--------------------------------|--|
| [Ue] Rated Operational Voltage | 240 V AC 50/60 Hz between phases               |
|                                | 415 V AC 50/60 Hz between phases               |
|                                | 440 V AC 50/60 Hz between phases               |
|                                | <= 125 V DC                                    |
| Magnetic Tripping Limit        | 8.5 x ln +/- 20 % AC                           |
|                                | 12 x In +/- 20 % DC                            |
| [Ics] Rated Service Breaking   | 7.5 kA 75 % EN/IEC 60947-2 - 415 V AC 50/60 Hz |
| Capacity                       | 16 kA 75 % EN/IEC 60947-2 - 240 V AC 50/60 Hz  |
|                                | 4.5 kA 75 % EN/IEC 60947-2 - 440 V AC 50/60 Hz |
|                                | 30 kA 100 % EN/IEC 60947-2 - <= 125 V DC       |
| Limitation Class               | 3  |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| [Ui] Rated Insulation Voltage          | 500 V AC 50/60 Hz EN/IEC 60947-2  |  |
|--|---|--|
| [Uimp] Rated Impulse Withstand Voltage | 6 kVEN/IEC 60947-2  |  |
| Contact Position Indicator             | Yes   |  |
| Control Type                           | Toggle  |  |
| Local Signalling                       | ON/OFF indication   |  |
| Mounting Mode                          | Clip-on   |  |
| Mounting Support                       | DIN rail  |  |
| 9 Mm Pitches                           | 6   |  |
| Height                                 | 3.19 in (81 mm)   |  |
| Width                                  | 2.13 in (54 mm)   |  |
| Depth                                  | 2.83 in (72 mm)   |  |
| Net Weight                             | 0.79 lb(US) (0.36 kg)   |  |
| Color                                  | Gray  |  |
| Mechanical Durability                  | 20000 cycles  |  |
| Electrical Durability                  | 10000 cycles  |  |
| Provision For Padlocking               | Padlockable   |  |
| Connections - Terminals                | Tunnel type terminal top or bottom) 0.000.04 in² (125 mm²) - rigid Tunnel type terminal top or bottom) 0.000.04 in² (125 mm²) - flexible Tunnel type terminal top or bottom) 0.000.04 in² (125 mm²) - flexible with ferrule |  |
| Wire Stripping Length                  | 0.55 in (14 mm) for top or bottom connection  |  |
| Tightening Torque                      | 17.70 lbf.in (2 N.m) top or bottom  |  |
| Earth-Leakage Protection               | Separate block  |  |

### **Environment**

| Heat Dissipation                      | 6.9 W 415 V - 1 A   |
|---------------------------------------|---|
| Ip Degree Of Protection               | IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529 |
| Pollution Degree                      | 3 EN/IEC 60947-2  |
| Overvoltage Category                  | IV  |
| Tropicalisation                       | 2 IEC 60068-1   |
| Relative Humidity                     | 95 % 131 °F (55 °C)   |
| Ambient Air Temperature For Operation | -22158 °F (-3070 °C)  |
| Ambient Air Temperature For Storage   | -40176 °F (-4080 °C)  |

# Ordering and shipping details

| Category          | US10DE200908  |
|-------------------|---------------|
| Discount Schedule | 0DE2          |
| Gtin              | 3606480576324 |
| Returnability     | No            |
| Country Of Origin | BG            |

## **Packing Units**

| Unit Type Of Package 1         | PCE                      |  |
|--------------------------------|--------------------------|--|
| Number Of Units In Package 1   | 1                        |  |
| Package 1 Height               | 2.13 in (5.4 cm)         |  |
| Package 1 Width                | 2.95 in (7.5 cm)         |  |
| Package 1 Length               | 3.35 in (8.5 cm)         |  |
| Package 1 Weight               | 11.53 oz (327.0 g)       |  |
| Unit Type Of Package 2         | BB1                      |  |
| lumber Of Units In Package 2 4 |                          |  |
| Package 2 Height               | 3.15 in (8.0 cm)         |  |
| Package 2 Width                | 3.46 in (8.8 cm)         |  |
| Package 2 Length               | 8.66 in (22.0 cm)        |  |
| Package 2 Weight               | 2.98 lb(US) (1.351 kg)   |  |
| Unit Type Of Package 3         | S03                      |  |
| Number Of Units In Package 3   | 48                       |  |
| Package 3 Height               | 11.81 in (30.0 cm)       |  |
| Package 3 Width                | 11.81 in (30.0 cm)       |  |
| Package 3 Length               | 15.75 in (40.0 cm)       |  |
| Package 3 Weight               | 36.82 lb(US) (16.699 kg) |  |

### Sustainability Green Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

|          | Mercury Free               |     |
|----------|----------------------------|-----|
|          | Rohs Exemption Information | Yes |
| <b>⊘</b> | Halogen Free Product       |     |

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration  |
|--------------------------|--|
| Eu Rohs Directive        | Compliant with Exemptions  |
| China Rohs Regulation    | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.                         |
| Environmental Disclosure | Product Environmental Profile  |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile      | No need of specific recycling operations   |