

Product data sheet

Specifications



PM3250 power meter - RS485

METSEPM3250

Product availability : Non-Stock - Not normally stocked in distribution facility

Price* : 619.00 USD

Main

Range	PowerLogic
Product name	PowerLogic PM3000
Device short name	PM3250
Product or Component Type	Power meter

Complementary

Power quality analysis	up to the 15th harmonic
Device Application	Multi-tariff Power monitoring Sub billing
Type of measurement	Active and reactive power Apparent power Current Voltage Energy Power factor Frequency Total current harmonic distortion THD (I) Total voltage harmonic distortion THD (U)
Supply voltage	100...277 V AC 45...65 Hz 173...480 V AC 45...65 Hz 100...300 V DC
Network Frequency	60 Hz 50 Hz
Line Rated Current	5 A 1 A
Type of network	1P + N 3P 3P + N
Power Consumption in VA	5 VA
Display Type	Backlit LCD
Display Resolution	128 x 96 pixels
Sampling rate	32 samples/cycle
Measurement current	0.02...1.2 A 0.05...6 A
Analogue input type	current 0...5 A current 0...1 A
Measurement voltage	50...330 V AC 45...65 Hz direct 50...330 V AC 45...65 Hz phase to neutral 80...570 V AC 45...65 Hz direct

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

80...570 V AC 45...65 Hz phase to phase
570...999000 V AC 45...65 Hz with external VT

Frequency measurement range	45...65 Hz
Number of inputs	0
Measurement accuracy	Current 0.3 % 0.5...6 A Current 0.5 % 0.1...1.2 A Voltage 0.3 % 50...330 V Voltage 0.3 % 80...570 V
Accuracy class	Class 0.5S active energy IEC 62053-22 Class 1 active energy IEC 62053-21 Class 2 reactive energy IEC 62053-23 Class C active energy EN 50470-3
Number of Outputs	0
Information displayed	Tariff 4)
Communication port protocol	Modbus 9.6...38.4 kbauds
Communication port support	RS485
Data recording	Time stamping Min/max of instantaneous values 5 alarms
Mounting Mode	Clip-on
Mounting support	DIN rail
Standards	IEC 61557-12 EN 50470-3 EN 61010-1 EN 50470-1 EN 61557-12 UL 61010-1 IEC 62052-11
Product certifications	CE EN 61010-1 CULus UL 61010-1 UL
Width	3.54 in (90 mm)
Depth	2.76 in (70 mm)
Height	3.74 in (95 mm)
Product Weight	0.57 lb(US) (0.26 kg)

Environment

Electromagnetic compatibility	Electrostatic dischargelevel 4 IEC 61000-4-2 Susceptibility to electromagnetic fieldslevel 3 IEC 61000-4-3 Electrical fast transient/burst immunity testlevel 4 IEC 61000-4-4 1.2/50 μ s shock waves immunity testlevel 4 IEC 61000-4-5 Conducted RF disturbanceslevel 3 IEC 61000-4-6 Magnetic field at power frequency 0.5 mT IEC 61000-4-8 Conducted and radiated emissionsclass B EN 55022
Overvoltage category	III
IP degree of protection	Front panel IP40 IEC 60529 Body IP20 IEC 60529
Relative humidity	5...95 % 122 °F (50 °C)
Pollution degree	2
Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Operating altitude	0...9842.52 ft (0...3000 m)

Ordering and shipping details

Category	09786 - SE ENTRY POWER METER
Discount Schedule	PL1

GTIN	3606480481604
Nbr. of units in pkg.	1
Package weight(Lbs)	14.46 oz (410 g)
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.31 in (13.5 cm)
Package 1 width	5.31 in (13.5 cm)
Package 1 Length	3.54 in (9 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	16
Package 2 Weight	15.51 lb(US) (7.036 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Unit Type of Package 3	P12
Number of Units in Package 3	384
Package 3 Weight	392.12 lb(US) (177.864 kg)
Package 3 Height	37.40 in (95 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	47.24 in (120 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------