## **Product data sheet**

Specification





PowerLogic

Power quality meter, PowerLogic PM8000, Standard, transducer and remote display, 512 MB, 256 s/c

METSEPM8244

Product availability: Stock - Normally stocked in distribution facility

Price\*: 9,737.57 USD

### Main Range

Product Name	PowerLogic PM8000
Device Short Name	PM8244
Product Or Component Type	Power meter
Complementary	
Power Quality Analysis	EN 50160 2010 compliance report IEEE 519 2014 compliance report IEC 61000-4-30 class S power quality measurement up to the 63rd harmonic harmonic distortion waveform capture voltage sag and swell detection programmablity (logic and math functions) IEC 62586 power quality monitoring disturbance direction detection rapid voltage change
Device Application	WAGES metering Power monitoring
Type Of Measurement	Current Voltage Frequency Active and reactive power total Apparent power total Power factor total Active and reactive power per phase, rms Apparent power per phase, rms Power factor per phase, rms
Supply Voltage	90415 V AC 4565 Hz +/- 10 % 110415 V DC +/- 10 %
Network Frequency	50 Hz 60 Hz
Line Rated Current	10 A 5 A 1 A
Poles Description	3P 1P + N 3P + N
Power Consumption In Va	18 VA 415 V AC
Display Type	Remote LCD display
Display Resolution	320 x 240 pixels QVGA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sampling Rate	256 samples/cycle
Measurement Current	5010000 mA
Analogue Input Type	Voltage (impedance 5 MOhm) Current (impedance 0.3 mOhm)
Measurement Voltage	57400 V AC 4269 Hz between phase and neutral 100690 V AC 4269 Hz between phases
Frequency Measurement Range	4269 Hz
Number Of Inputs	3 digital 30 V AC 3 digital 60 V DC
Measurement Accuracy	Current +/- 0.1 % Voltage +/- 0.1 % Active energy +/- 0.2 %
Accuracy Class	Class 0.2S active energy IEC 62053-22 Class 0.2 active energy ANSI C12.20 Class 0.2 active power IEC 61557-12 Class 0.5S reactive energy IEC 62053-24 Class 0.5 power factor IEC 61557-12 Class 0.2 voltage IEC 61557-12 Class 0.2 current IEC 61557-12
Number Of Outputs	1 pulse
Information Displayed	Voltage Current Frequency Power Energy consumption Harmonic distortion
Communication Port Protocol	Modbus RTU 115 kbauds - 2-wire ION 115 kbauds - 2-wire DNP3 IEC 61850 Modbus TCP/IP Ethernet Modbus TCP/IP daisy chain 10/100 Mbit/s RSTP 801.1d 2004
Communication Port Support	ETHERNET Screw terminal block RS485
Communication Network Type	IPv6 (internet protocol)
Data Recording	Sequence of event recording Event logs Min/max of instantaneous values Harmonics logs Alarm logs GPS synchronisation Waveform logs Data logs Time stamping Trending/forecasting Sag and swell logs 50 data recorders
Memory Capacity	512 MB
Web Services	Customizable home page File upload/download via FTP File upload/download via SFTP Web server Alarm notification by e-mail Viewing of captured waveform (FTP) Viewing of captured waveform (web) HTTPS server
Communication Service	SMTP e-mail notification RSTP support NTP time synchronization DHCP PTP time synchronization

Cybersecurity	Password protection Syslog protocol support Port hardening Robust security logs Enable/disable communication ports
Mounting Mode	Flush-mounted Clip-on
Mounting Support	DIN rail meter device Framework remote display
Provided Equipment	Remote display
Installation Category	III
Safety Construction	III400690 V conforming to IEC 61010-1:ed. 3 III400690 V conforming to EN 61010-1:ed. 3 III347600 V conforming to UL 61010-1:ed. 3 III347600 V conforming to CSA C22.2 No 61010-1:ed. 3
Standards	IEC 62053-22 IEC 62053-24 IEC 62052-11 IEC 61557-12 IEEE 1588 IEC 62586-2 IEC 61326-1
Product Certifications	CE CULus N998
Width	3.56 in (90.5 mm)
Depth	3.57 in (90.8 mm)
Height	3.56 in (90.5 mm)
Net Weight	18.62 oz (528 g)

# Environment Electromagnetic Compet

Electromagnetic Compatibility	Electrostatic discharge conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test conforming to IEC 61000-4-4 Surge immunity test conforming to IEC 61000-4-5 Conducted RF disturbances conforming to IEC 61000-4-6 Magnetic field at power frequency conforming to IEC 61000-4-8 Voltage dips and interruptions immunity test conforming to IEC 61000-4-11 Immunity to impulse waves conforming to IEC 61000-4-12 Conducted and radiated emissions conforming to EN 55022 Conducted and radiated emissions conforming to FN 55011 Conducted and radiated emissions conforming to FCC part 15 Conducted and radiated emissions conforming to ICES-003 Conducted RF disturbances (2150 Hz) conforming to CLC/TR 50579 Surge withstand conforming to IEEE C37.90.1
Ip Degree Of Protection	IP30 conforming to IEC 60529
Relative Humidity	595 %
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Operating Altitude	9842.52 ft (3000 m)

## Ordering and shipping details

Category	US10PL109797	
Discount Schedule	0PL1	
Gtin	3606480701979	

Returnability	Yes
Country Of Origin	CA

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.51 in (14.0 cm)
Package 1 Width	5.51 in (14.0 cm)
Package 1 Length	14.57 in (37.0 cm)
Package 1 Weight	3.17 lb(US) (1.437 kg)
Unit Type Of Package 2	S03
Number Of Units In Package 2	4
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	13.64 lb(US) (6.189 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	8
Package 3 Height	27.56 in (70.0 cm)
Package 3 Width	23.62 in (60.0 cm)
Package 3 Length	31.50 in (80.0 cm)
Package 3 Weight	44.09 lb(US) (20.0 kg)



Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Rohs Exemption Information


#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

#### **Dimensions Drawings**

#### **Approximate Dimensions**

#### PM8000 DIN Rail Mount Meter



#### PM8000 Remote Display

