# Product data sheet

Specifications





# Climasys Ultra thin resistance heater low starting current 12W 240V 110x140mm

NSYCRS10W240V

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 323.17 USD

### Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Ultra thin resistance heater
Power Range	12 W
Input Voltage	240 V AC 50/60 Hz
Electrical Connection	Cable 6.56 ft (2 m)

## Complementary

Operating Position	Vertical Horizontal
Ambient Air Temperature For Operation	-76158 °F (-6070 °C)
Temperature Setting Range	-40158 °F (-4070 °C)
Material	silicone rubber
Height	External 4.33 in (110 mm)
Width	External 5.51 in (140 mm)
Depth	External 0.06 in (1.6 mm)
Device Composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts fixing accessories
Condition Of Use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing Mode	By 4 screws
Mounting Support	Standard mounting plate Adhesive Velcro DIN rail Teleguick mounting plate

## Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480530128
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin ES

# **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5.0 cm)
Package 1 Width	10.04 in (25.5 cm)
Package 1 Length	11.22 in (28.5 cm)
Package 1 Weight	9.88 oz (280.0 g)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	440
Package 2 Height	67.72 in (172.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	302.03 lb(US) (137.0 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations