

Product data sheet

Specifications



ClimaSys indoor slim cooling unit block stainless steel - 1100W at 460 V - UL

NSYCUSX1K12P4UL

 **Discontinued on:** Dec 31, 2023

 **To be discontinued**

**Product availability: Non-Stock - Not normally stocked in
distribution facility**

Price*: 10,909.92 USD

Main

Range	ClimaSys
Product Name	CU
Product Or Component Type	Slim cooling unit block
Mounting Type	Door of enclosure
Installation	Indoor side
Product Destination	For enclosure
Mounting Mode	By screws
Supply Voltage	460 V AC 60 Hz, 2 phases 400...460 V AC 50/60 Hz
Rated Power	1100 W
Cooling Power	3753 Btu/h 60 Hz L35-L35 2934 Btu/h 60 Hz L35-L50

Complementary

Height	66.77 in (1696 mm)
Width	19.49 in (495 mm)
Depth	7.68 in (195 mm)
Line Rated Current	2.7 A
Inrush Current	8.5 A
Power Consumption In W	790 W 60 Hz, L35-L50 660 W 60 Hz, L35-L35
Energy Efficiency Ratio	1.7
Control Type	Electronic controller
Temperature Setting Range	68...122 °F (20...50 °C)
Ambient Air Temperature For Operation	Maximum 122 °F (50 °C) Inside the enclosure 68...115 °F (20...46 °C) Outside the enclosure 68...122 °F (20...50 °C)
Noise Level	64 dB EN/ISO 3746
Pressure	406.11 psi (28 bar)
Flow Rate	Internal circuit 227192.03 Gal/hr(US) (860 m3/h) 60 Hz External circuit 227192.03 Gal/hr(US) (860 m3/h) 60 Hz

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	114.64 lb(US) (52 kg)
Cooling Gas Type	R134a 1.10 lb(US) (0.5 kg))
Type Of Filter	Optional external circuit filter
Protection Type	Thermal protection T 4 A Short-circuit protection (magnetic)
Material	Stainless steel
Color	Gray RAL 7035)

Environment

Product Certifications	UL
Ip Degree Of Protection	IP55 IEC 60529 on the internal circuit) IP34 IEC 60529 on the external circuit)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480703973
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.68 in (19.5 cm)
Package 1 Width	19.49 in (49.5 cm)
Package 1 Length	66.77 in (169.6 cm)
Package 1 Weight	114.64 lb(US) (52.0 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	2
Package 2 Height	81.50 in (207.0 cm)
Package 2 Width	31.50 in (80.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	394.19 lb(US) (178.8 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.