## Product data sheet

Specifications





TeSys Deca, auxiliary contact block, 3 NO and 1 NC, top mount, screw clamp terminals, for LC1D09 to LC1D150 contactors

LADN31

Product availability: Stock - Normally stocked in distribution facility

Price\*: 49.80 USD

#### Main

Man		
Range	TeSys	
	TeSys Deca	
Product Name	TeSys Deca	
Product Or Component Type	Auxiliary contact block	
Device Short Name	LADN	
Range Compatibility	TeSys D CAD	
	TeSys D LC1D	
	TeSys F LC1F	
	TeSys F CR1F	
	TeSys Deca CAD	
	TeSys Deca LC1D	
Mounting Location	Front	
Pole Contact Composition 3 NO + 1 NC		
Contacts Operation	ts Operation Instantaneous	
[Ue] Rated Operational Voltage	690 V AC 25400 Hz	
[le] Rated Operational Current	6 A at 120 V AC-15	
	1.04 A at 690 V AC-15	
	0.55 A at 125 V DC-13	
	0.1 A at 600 V DC-13	
[Ui] Rated Insulation Voltage	690 V IEC 60947-5-1	
	600 V UL	
	600 V CSA	
[Ith] Conventional Free Air Thermal Current	10 A (at 140 °F (60 °C))	
Standards	EN/IEC 60947-5-1	
	UL 60947-5-1	
	CSA C22.2 No 60947-5-1	
	GB/T 14048.5	
Product Certifications	СВ	
	UL	
	CSA	
	CCC	
	EAC	
	UKCA	

### Complementary

Irms Rated Making Capacity
140 A AC conforming to IEC 60947-5-1
250 A DC conforming to IEC 60947-5-1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Permissible Short-Time Rating	100 A 140 °F (60 °C) 1 s 120 A 140 °F (60 °C) 500 ms 140 A 140 °F (60 °C) 100 ms	
Protection Type	GG fuse 10 A	
Mechanical Durability	30 Mcycles	
Minimum Switching Current	5 mA	
Minimum Switching Voltage	17 V	
Non-Overlap Time	1.5 ms on de-energisation no overlap between NC and NO contact     1.5 ms on energisation no overlap between NC and NO contact	
Insulation Resistance > 10 MOhm		
Connections - Terminals	screw clamp terminals 1 0.000.01 in² (14 mm²)flexible with cable end screw clamp terminals 1 0.000.01 in² (14 mm²)flexible without cable end screw clamp terminals 2 0.000.00 in² (12.5 mm²)flexible with cable end screw clamp terminals 2 0.000.01 in² (14 mm²)flexible without cable end screw clamp terminals 1 0.000.01 in² (14 mm²)rigid without cable end screw clamp terminals 2 0.000.01 in² (14 mm²)rigid without cable end	
Tightening Torque	15.05 lbf.in (1.7 N.m) flat Ø 6 mm 15.05 lbf.in (1.7 N.m) Philips No 2 15.05 lbf.in (1.7 N.m) pozidriv No 2	
<b>Height</b> 1.89 in (48 mm)		
Width	1.73 in (44 mm)	
Depth	1.65 in (42 mm)	
Net Weight	0.11 lb(US) (0.05 kg)	
Color	Dark grey	

### **Environment**

Environmental Characteristic	Normal environment
Ip Degree Of Protection	IP2X conforming to IEC 60529
Protective Treatment	TH IEC 60068
Ambient Air Temperature For Storage	-76176 °F (-6080 °C)
Ambient Air Temperature For Operation	23140 °F (-560 °C)
Operating Altitude	9842.52 ft (3000 m)

# Ordering and shipping details

Category	US10I1222341
Discount Schedule	0112
Gtin	3389110384178
Returnability	Yes
Country Of Origin	FR

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.89 in (4.800 cm)
Package 1 Width	1.65 in (4.200 cm)
Package 1 Length	1.97 in (5.000 cm)

Package 1 Weight	2.19 oz (62.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	1.89 in (4.800 cm)
Package 2 Width	3.39 in (8.600 cm)
Package 2 Length	10.24 in (26.000 cm)
Package 2 Weight	22.15 oz (628.000 g)
Unit Type Of Package 3	S03
Number Of Units In Package 3	160
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	22.81 lb(US) (10.345 kg)

## **Contractual warranty**

Warranty 18 months

### Sustainability Screen Premium\*

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations

**Dimensions Drawings** 

### **Approximate Dimensions**

