# **Product data sheet**





### TeSys Deca contactor - 4P(2 NO + 2 NC) - AC-1 - <= 440 V 20 A -480 V AC coil

LC1D098T7

! Discontinued on: Oct 8, 2021



Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range	TeSys
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load
Utilisation Category	AC-1 AC-3 AC-3e AC-4
Poles Description	4P
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC
[le] Rated Operational Current	20 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit
[Uc] Control Circuit Voltage	480 V AC 50/60 Hz

### Complementary

Compatibility Code	LC1D
Pole Contact Composition	2 NO + 2 NC
Contact Compatibility	M6
Protective Cover	With
[Ith] Conventional Free Air Thermal Current	25 A (at 140 °F (60 °C)) for power circuit 10 A (at 140 °F (60 °C)) for signalling circuit
Irms Rated Making Capacity	250 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1
Rated Breaking Capacity	250 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	105 A 104 °F (40 °C) - 10 s for power circuit 210 A 104 °F (40 °C) - 1 s for power circuit 30 A 104 °F (40 °C) - 10 min for power circuit 61 A 104 °F (40 °C) - 1 min for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 25 A gG at <= 690 V coordination type 1 for power circuit 20 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2.5 mOhm - Ith 25 A 50 Hz for power circuit

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Power Dissipation Per Pole	1.56 W AC-1
[Ui] Rated Insulation Voltage	Power circuit 690 V IEC 60947-4-1 Power circuit 600 V CSA Power circuit 600 V UL Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA Signalling circuit 600 V UL
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	15 Mcycles
Electrical Durability	0.6 Mcycles 25 A AC-1 <= 440 V
Control Circuit Type	AC 50/60 Hz
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.30.6 Uc -40158 °F (-4070 °C) drop-out AC 50/60 Hz 0.81.1 Uc -40140 °F (-4060 °C) operational AC 50 Hz 0.851.1 Uc -40140 °F (-4060 °C) operational AC 60 Hz 11.1 Uc 140158 °F (6070 °C) operational AC 50/60 Hz
Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 68 °F (20 °C)) 70 VA 50 Hz cos phi 0.75 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C)) 7 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat Dissipation	23 W at 50/60 Hz
Operating Time	1222 ms closing 419 ms opening
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)
Connections - Terminals	Power circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 0.000.00 in² (12.5 mm²) - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: solid without cable end Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 2 0.000.00 in² (12.5 mm²) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: solid without cable end
Tightening Torque	Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2 Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2
Auxiliary Contact Composition	1 NO + 1 NC
Auxiliary Contacts Type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz

Minimum Switching Voltage	17 V for signalling circuit	
Minimum Switching Current	5 mA for signalling circuit	
Insulation Resistance	> 10 MOhm for signalling circuit	
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact     1.5 ms on energisation between NC and NO contact	
Mounting Support	Plate Rail	

### **Environment**

Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508
Product Certifications	CCC DNV RINA GOST LROS (Lloyds register of shipping) GL UL CSA BV
Ip Degree Of Protection	IP20 front face IEC 60529
Protective Treatment	THIEC 60068-2-30
Climatic Withstand	IACS E10 exposure to damp heat IEC 60947-1 Annex Q category D exposure to damp heat
Permissible Ambient Air Temperature Around The Device	-40140 °F (-4060 °C) 140158 °F (6070 °C) with derating
Operating Altitude	09842.52 ft (03000 m)
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open 2 Gn, 5300 Hz) Vibrations contactor closed 4 Gn, 5300 Hz) Shocks contactor open 10 Gn for 11 ms) Shocks contactor closed 15 Gn for 11 ms)
Height	3.35 in (85 mm)
Width	1.77 in (45 mm)
Depth	3.62 in (92 mm)
Net Weight	0.80 lb(US) (0.365 kg)

## Ordering and shipping details

Category	US10I1222354
Discount Schedule	0112
Gtin	3389110277180
Returnability	No
Country Of Origin	FR

# **Packing Units**

Unit Type Of Package 1	PCE

Number Of Units In Package 1	1
Package 1 Height	3.34 in (8.48 cm)
Package 1 Width	1.77 in (4.5 cm)
Package 1 Length	3.62 in (9.2 cm)
Package 1 Weight	12.52 oz (355 g)

## **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>②</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov