Product data sheet

Specifications





IEC contactor, TeSys Deca, nonreversing, 200A resistive, 4 pole, 4 NO, 24VDC coil, open style

LC1D1150046BD

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 673.00 USD

Main

Range	TeSys
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load
Utilisation Category	AC-1 AC-3 AC-3e AC-4
Poles Description	4P
[Ue] Rated Operational Voltage	Power circuit <= 1000 V AC 25400 Hz Power circuit <= 460 V DC
[Ie] Rated Operational Current	200 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit
[Uc] Control Circuit Voltage	24 V DC

Complementary

Compatibility Code	LC1D
Pole Contact Composition	4 NO
Protective Cover	With
[Ith] Conventional Free Air Thermal Current	200 A (at 140 °F (60 °C)) for power circuit
Irms Rated Making Capacity	1260 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	1100 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	250 A 104 °F (40 °C) - 10 min for power circuit 550 A 104 °F (40 °C) - 1 min for power circuit 950 A 104 °F (40 °C) - 10 s for power circuit 1100 A 104 °F (40 °C) - 1 s for power circuit
Associated Fuse Rating	250 A gG at <= 690 V coordination type 1 for power circuit 200 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	0.6 mOhm - Ith 200 A 50 Hz for power circuit
Power Dissipation Per Pole	24 W AC-1
[Ui] Rated Insulation Voltage	Power circuit 600 V CSA Power circuit 600 V UL Power circuit 1000 V IEC 60947-4-1
Overvoltage Category	III

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Pollution Degree	3	
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947	
Safety Reliability Level	B10d = 684932 cycles contactor with nominal load EN/ISO 13849-1 B10d = 10000000 cycles contactor with mechanical load EN/ISO 13849-1	
Mechanical Durability	8 Mcycles	
Electrical Durability	0.8 Mcycles 200 A AC-1 <= 440 V	
Control Circuit Type	DC standard	
Coil Technology	With integral suppression device	
Control Circuit Voltage Limits	0.751.2 Uc -40131 °F (-4055 °C) operational DC 0.150.4 Uc -40158 °F (-4070 °C) drop-out DC 11.2 Uc 131158 °F (5570 °C) operational DC	
Inrush Power In W	270365 W 68 °F (20 °C))	
Hold-In Power Consumption In W	2.45.1 W 68 °F (20 °C)	
Operating Time	2035 ms closing 4075 ms opening	
Time Constant	25 ms	
Maximum Operating Rate	1200 cyc/h 140 °F (60 °C)	
Connections - Terminals	Control circuit: lugs-ring terminals - external diameter: 0.31 in (8 mm) Power circuit: lugs-ring terminals - external diameter: 0.98 in (25 mm) Power circuit: bars 1 - busbar cross section: 5 x 25 mm	
Tightening Torque	Control circuit 10.62 lbf.in (1.2 N.m) lugs-ring terminals flat Ø 6 mm M3.5 Control circuit 10.62 lbf.in (1.2 N.m) lugs-ring terminals Philips No 2 M3.5 Power circuit 106.21 lbf.in (12 N.m) lugs-ring terminals hexagonal 0.51 in (13 mm) M8 Power circuit 106.21 lbf.in (12 N.m) bars hexagonal 0.51 in (13 mm) M8 Control circuit 10.62 lbf.in (1.2 N.m) lugs-ring terminals pozidriv No 2 M3.5	
Mounting Support	Plate Rail	

Environment

Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508	
Product Certifications	LROS (Lloyds register of shipping) RINA CSA DNV GOST CCC UL GL BV UKCA	
Ip Degree Of Protection	IP20 front face IEC 60529	
Protective Treatment	THIEC 60068-2-30	
Climatic Withstand	IACS E10 exposure to damp heat IEC 60947-1 Annex Q category D exposure to damp heat	
Permissible Ambient Air Temperature Around The Device	-40140 °F (-4060 °C) 140158 °F (6070 °C) with derating	
Operating Altitude	09842.52 ft (03000 m)	
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1	

Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Vibrations contactor open 2 Gn, 5300 Hz) Vibrations contactor closed 4 Gn, 5300 Hz) Shocks contactor closed 15 Gn for 11 ms) Shocks contactor open 6 Gn for 11 ms)	
Height	6.22 in (158 mm)	
Width	6.10 in (155 mm)	
Depth	4.53 in (115 mm)	
Net Weight	6.31 lb(US) (2.86 kg)	

Ordering and shipping details

Category	US10I1222359	
Discount Schedule	0112	
Gtin	3389110882025	
Returnability	No	
Country Of Origin	CZ	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.61 in (16.8 cm)
Package 1 Width	8.35 in (21.2 cm)
Package 1 Length	7.28 in (18.5 cm)
Package 1 Weight	5.22 lb(US) (2.37 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov