Product data sheet

Specifications





IEC contactor, TeSys Deca, nonreversing, 80A resistive, 4 pole, 2 NO and 2 NC, 120VAC 50/60Hz coil, open style

LC1D65008G7

Product availability: Stock - Normally stocked in distribution facility

Price*: 748.80 USD

Main

Range	TeSys
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load
Utilisation Category	AC-1
Poles Description	4P
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC
[le] Rated Operational Current	80 A (at <140 $^{\circ}$ F (60 $^{\circ}$ C)) at <= 440 V AC AC-1 for power circuit
[Uc] Control Circuit Voltage	120 V AC 50/60 Hz

Complementary

LC1D
2 NO + 2 NC
Without
80 A (at 140 °F (60 °C)) for power circuit
1000 A at 440 V for power circuit conforming to IEC 60947
1000 A at 440 V for power circuit conforming to IEC 60947
640 A 104 °F (40 °C) - 10 s for power circuit 900 A 104 °F (40 °C) - 1 s for power circuit 110 A 104 °F (40 °C) - 10 min for power circuit 260 A 104 °F (40 °C) - 1 min for power circuit
125 A gG at <= 690 V coordination type 1 for power circuit 125 A gG at <= 690 V coordination type 2 for power circuit
1.5 mOhm - Ith 80 A 50 Hz for power circuit
9.6 W AC-1
Power circuit 600 V CSA Power circuit 600 V UL Power circuit 690 V IEC 60947-4-1
III
3

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	6 Mcycles
Electrical Durability	1.4 Mcycles 80 A AC-1 <= 440 V
Control Circuit Type	AC 50/60 Hz
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.30.6 Uc -40158 °F (-4070 °C) drop-out AC 50/60 Hz 0.81.1 Uc -40140 °F (-4060 °C) operational AC 50 Hz 0.851.1 Uc -40140 °F (-4060 °C) operational AC 60 Hz 11.1 Uc 140158 °F (6070 °C) operational AC 50/60 Hz
Inrush Power In Va	140 VA 60 Hz cos phi 0.75 (at 68 °F (20 °C)) 160 VA 50 Hz cos phi 0.75 (at 68 °F (20 °C))
Hold-In Power Consumption In Va	13 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C)) 15 VA 50 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat Dissipation	45 W at 50/60 Hz
Operating Time	419 ms opening 1226 ms closing
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)
Connections - Terminals	Control circuit: screw clamp terminals 2 0.000.00 in ² (12.5 mm ²) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 0.000.01 in ² (14 mm ²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 0.000.01 in ² (14 mm ²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 0.000.01 in ² (14 mm ²) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 0.000.01 in ² (14 mm ²) - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 0.000.01 in ² (14 mm ²) - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 0.000.05 in ² (135 mm ²) - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 2 0.000.04 in ² (125 mm ²) - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 2 0.000.04 in ² (125 mm ²) - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 0.000.05 in ² (135 mm ²) - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 0.000.04 in ² (125 mm ²) - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 0.000.04 in ² (125 mm ²) - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 0.000.04 in ² (125 mm ²) - cable stiffness: solid without cable end Power circuit: screw clamp terminals 1 0.000.05 in ² (135 mm ²) - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 0.000.04 in ² (125 mm ²) - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 0.000.04 in ² (125 mm ²) - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 0.000.04 in ² (125 mm ²) - cable stiffness: solid without cable end
Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2 Power circuit 70.81 lbf.in (8 N.m) screw clamp terminals 0.040.05 in ² (2535 mm ²) hexagonal 0.16 in (4 mm) Power circuit 44.25 lbf.in (5 N.m) screw clamp terminals 0.000.04 in ² (125 mm ²) hexagonal 0.16 in (4 mm) Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2

Environment

Standards

CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508

Product Certifications	CSA CCC UL BV LROS (Lloyds register of shipping) DNV GL GOST RINA
Ip Degree Of Protection	IP20 front face IEC 60529
Protective Treatment	THIEC 60068-2-30
Climatic Withstand	IACS E10 exposure to damp heat
Permissible Ambient Air Temperature Around The Device	-40140 °F (-4060 °C) 140158 °F (6070 °C) with derating
Operating Altitude	09842.52 ft (03000 m)
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Shocks contactor open 8 Gn for 11 ms) Shocks contactor closed 10 Gn for 11 ms) Vibrations contactor opened 2 Gn, 5300 Hz) Vibrations contactor closed 3 Gn, 5300 Hz)
Height	5.00 in (127 mm)
Width	3.35 in (85 mm)
Depth	4.92 in (125 mm)
Net Weight	3.20 lb(US) (1.45 kg)

Ordering and shipping details

Category	US10I1222357
Discount Schedule	0112
Gtin	3389110265521
Returnability	Yes
Country Of Origin	CZ

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.58 in (9.1 cm)
Package 1 Width	4.96 in (12.6 cm)
Package 1 Length	5.20 in (13.2 cm)
Package 1 Weight	3.31 lb(US) (1.5 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov