

# Product data sheet

Specifications



## Active harmonic filter 120 amp 380-480 VAC N12 Enclosure

PCSP120D5N12

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 119,136.00 USD

### Main

Range Of Product	AccuSine
Product Name	AccuSine PCS+
Product Or Component Type	Active harmonic filter

### Complementary

Network Type	3P
Network Configuration	3 or 4 wires
Network Rated Voltage	380...480 V AC
Input Frequency	50/60 Hz +/- 3 Hz auto sensing
Maximum Permissible Voltage	1.1 x Un
Neutral Correction	Not provided
Rms Output Current Rating	120 A
Reactive Power Rating	100 kvar 480 V AC 50/60 Hz
Operating Modes	Harmonic cancellation Mains current balancing Power factor correction
Installation Location	Indoor
Enclosure Mounting	Floor-standing
Protection Type	Circuit breaker protection
Disconnect Type	Door-interlocked with rotary handle
Interrupt Capacity	200 kA
Heat Dissipation	Rear plenum with forced ventilation for high heat flow
Electromagnetic Compatibility	Conducted EMC, class A EN 61000-6-4
Accessibility For Operation	Front
Location Of Connection	Top or bottom

### Environment

Enclosure Degree Of Protection	UL type 12
Environmental Characteristic	Operating 3C2 IEC 60721-3-3 Operating 3S2 IEC 60721-3-3 Storage 3C3 IEC 60721-3-3 Storage 3S3 IEC 60721-3-3
Operating Altitude	<= 3280.84 ft (1000 m) 1 % per 100 m

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	32...104 °F (0...40 °C) 32...122 °F (0...50 °C) maximum with current derating of 2 % per °C
Relative Humidity	0...95 %
Pcba Protection	Conformal coated
Standards	EN 61000-6-4 UL 60947-1 UL 508 CSA C22.2 No 60947-1-07 EN 60439-1 CSA C22.2 No 14
Product Certifications	RCM ABS cULus CE
Ambient Air Temperature For Storage	-4...140 °F (-20...60 °C)
Net Weight	573.20 lb(US) (260 kg)
Height	82.68 in (2100 mm)
Width	31.50 in (800 mm)
Color	Light gray RAL 7035)
Depth	19.69 in (500 mm)

## Ordering and shipping details

Category	US1DE2C00089
Discount Schedule	DE2C
Gtin	3606480851162
Returnability	Yes

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	91.77 in (233.1 cm)
Package 1 Width	47.01 in (119.4 cm)
Package 1 Length	47.01 in (119.4 cm)
Package 1 Weight	844.37 lb(US) (383.0 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability




**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	<a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>	Product out of China RoHS scope. Substance declaration for your information.
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>	