





Circuit breaker, PowerPacT P, 1200A, 3 pole, 600VAC, 18kA, I-Line, Micrologic 5.0, 80%, ABC

PGA36120U33A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 21,131.00 USD

Main

Breaking Capacity

Range	PowerPact
Product Name	PowerPact P
Product Or Component Type	Circuit breaker
Device Application	Distribution
Complementary	
Line Rated Current	1200 A
Number Of Poles	3P
Control Type	Toggle
Breaking Capacity Code	G

AIR 65 kA 240 V AC 50/60 Hz UL 489 AIR 35 kA 480 V AC 50/60 Hz UL 489 AIR 18 kA 600 V AC 50/60 Hz UL 489 Icu 50 kA 240 V AC 50/60 Hz IEC 60947-2

Icu 35 kA 380/415 V AC 50/60 Hz IEC 60947-2 [Ue] Rated Operational Voltage 600 V AC 50/60 Hz UL 489

Network Frequency [Ics] Rated Service Breaking 25 kA 240 V AC 50/60 Hz IEC 60947-2 20 kA 380/415 V AC 50/60 Hz IEC 60947-2

[Uimp] Rated Impulse Withstand 8 kV IFC 60947-2 Voltage **Trip Unit Technology** Electronic, standard, MicroLogic 5.0, LSI **Continuous Current Rating** 80 %

[Ui] Rated Insulation Voltage 750 V IEC 60947-2

Trip Unit Name MicroLogic 5.0 Awg Gauge 4 x AWG 3/0...500 kcmil aluminium/copper

Local Signalling Overload 1 1 LED amber) 1 trip indicator green)

Mounting Mode I-Line bracket) **Mounting Support** Bracket

Electrical Connection I-Line connection, line Lugs, load

Long Time Pick-Up Adjustment 0.4...1 x lr

Terminal Identifier

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

AL1200P25K

Mounting Height	9 in (228.60 mm)
Tightening Torque	442.54 lbf.in (50 N.m) 0.150.37 in² (95240 mm²) (4 x AWG 3/0500 kcmil) 8.8511.51 lbf.in (1.01.3 N.m)
Number Of Slots	2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in)
Power Wire Stripping Length	1.18 in (30 mm)
Height	16.16 in (410.46 mm)
Width	8.27 in (210.06 mm)
Depth	8.05 in (204.47 mm)
Net Weight	32 lb(US) (14.51 kg)
Quantity Per Set	1
Phase Connection	ABC
Circuit Breaker Application	HACR rated

Environment

Quality Labels	CE
Standards	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2
Product Certifications	UL CSA NOM
Ip Degree Of Protection	Front cover IP40
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	< 6561.68 ft (2000 m) without derating 13123.36 ft (4000 m) with derating

Ordering and shipping details

Category	US10DE201210
Discount Schedule	0DE2
Gtin	3606486285619
Returnability	Yes
Country Of Origin	IIS

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.14 in (41.0 cm)
Package 1 Width	8.27 in (21.0 cm)
Package 1 Length	8.03 in (20.4 cm)
Package 1 Weight	32.00 lb(US) (14.515 kg)

Contractual warranty

Warranty

Apr 25, 2024

18 months

Sustainability Screen Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov