





Circuit breaker, PowerPacT P, 600A, 3 pole, 600VAC, 25kA, busbar, Micrologic 6.0P, 100%, modbus

PJF36060CU64AE1

### Main

| Range                     | PowerPact       |
|---------------------------|-----------------|
| Product Name              | PowerPact P     |
| Product Or Component Type | Circuit breaker |
| Device Application        | Distribution    |

### Complementary

| •  |   |
|--|---|
| Line Rated Current                       | 600 A   |
| Number Of Poles                          | 3P  |
| Control Type                             | Toggle  |
| Breaking Capacity Code                   | J   |
| Breaking Capacity                        | AIR 100 kA 240 V AC 50/60 Hz UL 489<br>AIR 65 kA 480 V AC 50/60 Hz UL 489<br>AIR 25 kA 600 V AC 50/60 Hz UL 489<br>Icu 65 kA 240 V AC 50/60 Hz IEC 60947-2<br>Icu 50 kA 380/415 V AC 50/60 Hz IEC 60947-2 |
| [Ue] Rated Operational Voltage           | 600 V AC 50/60 Hz UL 489  |
| Network Frequency                        | 50/60 Hz  |
| [Ics] Rated Service Breaking<br>Capacity | 35 kA 240 V AC 50/60 Hz IEC 60947-2<br>25 kA 380/415 V AC 50/60 Hz IEC 60947-2  |
| [Uimp] Rated Impulse Withstand Voltage   | 8 kV IEC 60947-2  |
| Trip Unit Technology                     | Electronic, power, MicroLogic 6.0 P, LSI  |
| Continuous Current Rating                | 100 %   |
| [Ui] Rated Insulation Voltage            | 750 V IEC 60947-2   |
| Trip Unit Name                           | MicroLogic 6.0 P  |
| Accessory / Separate Part Type           | Modbus connecting cable   |
| Awg Gauge                                | 3 x AWG 3/0500 kcmil aluminium/copper   |
| Local Signalling                         | Overload 1 trip indicator green) 1 trip indicator green) Trip causes 1 trip indicator green)  |
| Mounting Mode                            | Unit mount busbar)  |
| Mounting Support                         | Busbar  |
| Electrical Connection                    | Busbar connection, line<br>Busbar connection, load  |
| Terminal Identifier                      | AL800M23K   |
| Long Time Pick-Up Adjustment<br>Range    | 0.41 x lr   |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Tightening Torque           | 442.54 lbf.in (50 N.m) 0.150.37 in² (95240 mm²) (3 x AWG 3/0500 kcmil) 8.8511.51 lbf.in (1.01.3 N.m)                                 |
|-----------------------------|--|
| Number Of Slots             | 2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in) |
| Power Wire Stripping Length | 0.98 in (25 mm)  |
| Height                      | 12.86 in (326.64 mm)   |
| Width                       | 8.27 in (210.06 mm)  |
| Depth                       | 8.05 in (204.47 mm)  |
| Net Weight                  | 32 lb(US) (14.51 kg)   |
| Quantity Per Set            | 1  |
| Communication Interface     | Modbus   |
| Circuit Breaker Application | HACR rated   |

### **Environment**

| Quality Labels                        | CE  |
|---------------------------------------|---|
| Standards                             | UL<br>CSA<br>NEMA<br>NOM-003-SCFI-2000<br>IEC 60947-2                     |
| Product Certifications                | UL<br>CSA<br>NOM  |
| Ip Degree Of Protection               | Front cover IP40  |
| Pollution Degree                      | 3 IEC 60947-1   |
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C)  |
| Ambient Air Temperature For Storage   | -58185 °F (-5085 °C)  |
| Operating Altitude                    | < 6561.68 ft (2000 m) without derating 13123.36 ft (4000 m) with derating |

# Ordering and shipping details

| Category          | 01215-PG,H,J,K,L,N UNIT MT BREAKERS |
|-------------------|-------------------------------------|
| Discount Schedule | DE2                                 |
| Returnability     | No                                  |
| Country Of Origin | US                                  |

## **Packing Units**

| Unit Type Of Package 1       | PCE                      |
|------------------------------|--------------------------|
| Number Of Units In Package 1 | 1                        |
| Package 1 Weight             | 32.00 lb(US) (14.515 kg) |

### **Contractual warranty**

| Warranty 18 months |  |
|--------------------|--|
| warranty 18 months |  |



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

| <b>②</b> | Mercury Free               |     |
|----------|----------------------------|-----|
| <b>⊘</b> | Rohs Exemption Information | Yes |
| <b>⊘</b> | Pvc Free                   |     |

#### **Certifications & Standards**

| Reach Regulation          | REACh Declaration  |
|---------------------------|--|
| Eu Rohs Directive         | Compliant with Exemptions  |
| China Rohs Regulation     | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.   |
| Environmental Disclosure  | Product Environmental Profile  |
| Circularity Profile       | End of Life Information  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |