

Product data sheet

Specifications



TeSys F contactor - 4P (4 NO) - AC-1 - <= 440 V 200 A - coil 380 V AC

LC1F1154Q5

⚠ Discontinued on: Jul 12, 2021

⚠ Discontinued

Main

Range	TeSys
Range Of Product	TeSys F
Product Or Component Type	Contactor
Device Short Name	LC1F
Contactor Application	Resistive load
Utilisation Category	AC-1
Poles Description	4P
[Ue] Rated Operational Voltage	<= 690 V AC 50/60 Hz <= 460 V DC
[Uc] Control Circuit Voltage	380 V AC 50 Hz
[Ie] Rated Operational Current	200 A (at <104 °F (40 °C)) at <= 440 V AC-1

Complementary

[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	200 A (at 104 °F (40 °C))
Rated Breaking Capacity	920 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand Current	1100 A 104 °F (40 °C) - 10 s 640 A 104 °F (40 °C) - 30 s 520 A 104 °F (40 °C) - 1 min 400 A 104 °F (40 °C) - 3 min 320 A 104 °F (40 °C) - 10 min
Associated Fuse Rating	125 A aM at <= 440 V 200 A gG at <= 440 V
Average Impedance	0.37 mOhm - Ith 200 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V IEC 60947-4-1 1500 V VDE 0110 group C
Power Dissipation Per Pole	15 W AC-1
Overvoltage Category	III
Power Pole Contact Composition	4 NO
Control Circuit Voltage Limits	Operational 0.85...1.1 Uc 50/60 Hz 131 °F (55 °C)) Drop-out 0.35...0.55 Uc 50/60 Hz 131 °F (55 °C))
Mechanical Durability	10 Mcycles
Inrush Power In Va	550 VA, 50 Hz 0.3 68 °F (20 °C))
Hold-In Power Consumption In Va	45 VA, 50 Hz 0.3 68 °F (20 °C))

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Maximum Operating Rate	2400 cyc/h 131 °F (55 °C)
Operating Time	23...35 ms closing 5...15 ms opening
Connections - Terminals	Power circuit bar 2 20 x 3 mm Power circuit lugs-ring terminals 1 0.15 in² (95 mm²) Power circuit connector 1 0.15 in² (95 mm²) Control circuit screw clamp terminals 1 0.00...0.01 in² (1...4 mm²)flexible without cable end Control circuit screw clamp terminals 2 0.00...0.01 in² (1...4 mm²)flexible without cable end Control circuit screw clamp terminals 1 0.00...0.01 in² (1...4 mm²)flexible with cable end Control circuit screw clamp terminals 2 0.00...0.00 in² (1...2.5 mm²)flexible with cable end Control circuit screw clamp terminals 1 0.00...0.01 in² (1...4 mm²)solid without cable end Control circuit screw clamp terminals 2 0.00...0.01 in² (1...4 mm²)solid without cable end Power circuit bolted connection
Tightening Torque	Power circuit 88.51 lbf.in (10 N.m) Control circuit 10.62 lbf.in (1.2 N.m)
Mounting Support	Plate
Heat Dissipation	12...16 W
Standards	IEC 60947-1 EN 60947-4-1 JIS C8201-4-1 IEC 60947-4-1 EN 60947-1
Product Certifications	UL LROS (Lloyds register of shipping) CCC ABS DNV BV RINA CB RMRoS
Compatibility Code	LC1F
Control Circuit Type	AC 50 Hz

Environment

Ip Degree Of Protection	IP2X front face with shrouds IEC 60529 IP2X front face with shrouds VDE 0106
Protective Treatment	TH
Ambient Air Temperature For Operation	-40...140 °F (-40...60 °C)
Ambient Air Temperature For Storage	-76...176 °F (-60...80 °C)
Permissible Ambient Air Temperature Around The Device	140...158 °F (60...70 °C) at Uc
Height	6.38 in (162 mm)
Width	7.89 in (200.5 mm)
Depth	6.73 in (171 mm)
Operating Altitude	9842.52 ft (3000 m) without derating
Net Weight	8.44 lb(US) (3.83 kg)

Ordering and shipping details

Category	22336-CTR,F-LINE,AC,OPEN,NONREV
----------	---------------------------------

Discount Schedule	I12
Gtin	3389118093447
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.66 in (22 cm)
Package 1 Width	8.46 in (21.5 cm)
Package 1 Length	10.43 in (26.5 cm)
Package 1 Weight	10.63 lb(US) (4.82 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov