# Product data sheet

Specification





# TeSys F contactor - 3P (3 NO) - AC-3 - <= 440 V 115 A - coil 240 V AC

LC1F115U7

! Discontinued on: Jun 15, 2023

! Discontinued

Product availability: Stock - Normally stocked in distribution facility

#### Main

Range	TeSys
Range Of Product	TeSys F
Product Or Component Type	Contactor
Device Short Name	LC1F
Contactor Application	Resistive load Motor control
Utilisation Category	AC-4 AC-1 AC-3
Poles Description	3P
[Ue] Rated Operational Voltage	<= 690 V AC 50/60 Hz <= 460 V DC
[Uc] Control Circuit Voltage	240 V AC 40400 Hz
[le] Rated Operational Current	200 A (at <104 °F (40 °C)) at <= 440 V AC-1 115 A (at <131 °F (55 °C)) at <= 440 V AC-3

### Complementary

[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	200 A (at 104 °F (40 °C))
Rated Breaking Capacity	920 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand Current	1100 A 104 °F (40 °C) - 10 s 640 A 104 °F (40 °C) - 30 s 520 A 104 °F (40 °C) - 1 min 400 A 104 °F (40 °C) - 3 min 320 A 104 °F (40 °C) - 10 min
Associated Fuse Rating	125 A aM at <= 440 V 200 A gG at <= 440 V
Average Impedance	0.37 mOhm - Ith 200 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V IEC 60947-4-1 1500 V VDE 0110 group C
Power Dissipation Per Pole	15 W AC-1 5 W AC-3
Overvoltage Category	III
Power Pole Contact Composition	3 NO

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Motor Power Kw	55 kW at 380400 V AC 50/60 Hz (AC-3)
	59 kW at 415 V AC 50/60 Hz (AC-3)
	59 kW at 440 V AC 50/60 Hz (AC-3) 75 kW at 500 V AC 50/60 Hz (AC-3)
	80 kW at 660690 V AC 50/60 Hz (AC-3)
	30 kW at 220230 V AC 50/60 Hz (AC-3)
	18.5 kW at 400 V AC 50/60 Hz (AC-4)
Control Circuit Voltage Limits	Operational 0.851.1 Uc 40400 Hz 131 °F (55 °C))
	Drop-out 0.20.55 Uc 40400 Hz 131 °F (55 °C))
Mechanical Durability	10 Mcycles
Inrush Power In Va	770 VA, 40400 Hz 0.9 68 °F (20 °C))
Hold-In Power Consumption In Va	8.1 VA, 40400 Hz 0.9 68 °F (20 °C))
Maximum Operating Rate	2400 cyc/h 131 °F (55 °C)
Operating Time	35 ms closing at Uc)
	130 ms opening at Uc)
Connections - Terminals	Power circuit bar 2 20 x 3 mm
	Power circuit lugs-ring terminals 1 0.15 in² (95 mm²)
	Power circuit connector 1 0.15 in² (95 mm²)
	Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)flexible without cable end
	Control circuit screw clamp terminals 2 0.000.01 in² (14 mm²)flexible without
	cable end
	Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)flexible with cable
	end
	Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²)flexible with cable end
	Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)solid without cable
	end Control circuit screw clamp terminals 2 0.000.01 in² (14 mm²)solid without cable
	end
	Power circuit bolted connection
Tightening Torque	Power circuit 88.51 lbf.in (10 N.m)
	Control circuit 10.62 lbf.in (1.2 N.m)
Mounting Support	Plate
Heat Dissipation	5.97.2 W
Standards	EN 60947-1
	IEC 60947-1
	JIS C8201-4-1
	EN 60947-4-1
	IEC 60947-4-1
Product Certifications	LROS (Lloyds register of shipping)
	BV RINA
	RMRoS
	DNV
	UL
	СВ
	CCC
	ABS UKCA
Compatibility Code	LC1F
Control Circuit Type	AC 40400 Hz
Environment	
	IP2X front face with shrouds IEC 60529 IP2X front face with shrouds VDE 0106
lp Degree Of Protection	
Ip Degree Of Protection  Protective Treatment  Ambient Air Temperature For	IP2X front face with shrouds VDE 0106
Environment  Ip Degree Of Protection  Protective Treatment  Ambient Air Temperature For Operation  Ambient Air Temperature For	IP2X front face with shrouds VDE 0106  TH

Permissible Ambient Air Temperature Around The Device	140158 °F (6070 °C) at Uc
Height	6.38 in (162 mm)
Width	6.43 in (163.3 mm)
Depth	6.73 in (171 mm)
Operating Altitude	9842.52 ft (3000 m) without derating
Net Weight	7.56 lb(US) (3.43 kg)

## Ordering and shipping details

Category	US10I1222336
Discount Schedule	0112
Gtin	3389110350937
Returnability	Yes
Country Of Origin	CR

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.80 in (19.81 cm)
Package 1 Width	7.30 in (18.54 cm)
Package 1 Length	8.90 in (22.61 cm)
Package 1 Weight	8.80 lb(US) (3.99 kg)

## **Contractual warranty**

Warranty 18 months

## Sustainability Screen Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Circularity Profile	End of Life Information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Eu Rohs Directive	Compliant with Exemptions
Reach Regulation	REACh Declaration