Product data sheet

Specifications





contactor body withou coil, TeSys F, 3P(3NO), AC-3, <=440V 780A,use with coil LX1/LX9 110…500V AC 40/400Hz, LX4 110...440V DC

LC1F780

Product availability: Stock - Normally stocked in distribution facility

Price*: 6,993.00 USD

Main

Mann	
Range	TeSys
Product Name	TeSys F
Product Or Component Type	Contactor
Device Short Name	LC1F
Contactor Application	Resistive load Motor control
Utilisation Category	AC-4 AC-3 AC-1
Poles Description	3P
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	<= 1000 V AC 50/60 Hz <= 460 V DC
[le] Rated Operational Current	780 A 131 °F (55 °C)) <= 440 V AC AC-3 1600 A 104 °F (40 °C)) <= 440 V AC AC-1
Motor Power Kw	450 kW at 1000 V AC 50/60 Hz (AC-3) 400 kW at 380400 V AC 50/60 Hz (AC-3) 425 kW at 415 V AC 50/60 Hz (AC-3) 425 kW at 440 V AC 50/60 Hz (AC-3) 450 kW at 500 V AC 50/60 Hz (AC-3) 220 kW at 220240 V AC 50/60 Hz (AC-3) 475 kW at 660690 V AC 50/60 Hz (AC-3) 110 kW at 400 V AC 50/60 Hz (AC-4)

Complementary

[Uc] Control Circuit Voltage	110500 V AC 40400 Hz with LX1/LX9 coil 48440 V DC with LX4 coil
[Uimp] Rated Impulse Withstand Voltage	8 kV
Overvoltage Category	III
[Ith] Conventional Free Air Thermal Current	1600 A (at 104 °F (40 °C))
Irms Rated Making Capacity	7800 A AC conforming to IEC 60947-4-1
Rated Breaking Capacity	6240 A conforming to IEC 60947-4-1

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

[Icw] Rated Short-Time Withstand Current	3000 A 104 °F (40 °C) - 3 min 6250 A 104 °F (40 °C) - 10 s 5600 A 104 °F (40 °C) - 30 s
	4600 A 104 °F (40 °C) - 1 min 2200 A 104 °F (40 °C) - 10 min
Associated Fuse Rating	800 A aM at <= 440 V 1600 A gG at <= 440 V
Average Impedance	0.1 mOhm - Ith 1600 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V IEC 60947-4-1 1500 V VDE 0110 group C
Power Dissipation Per Pole	60 W AC-3 250 W AC-1
Control Circuit Voltage Limits	Operational: 0.851.1 Uc AC 40400 Hz with LX1/LX9 coil Drop-out: 0.20.4 Uc AC 40400 Hz with LX1/LX9 coil Operational: 0.851.1 Uc DC with LX4 coil Drop-out: 0.20.4 Uc DC with LX4 coil
Heat Dissipation	22 W
Operating Time	4080 ms closing with LX1/LX9 coil 130230 ms opening with LX1/LX9 coil 7080 ms closing with LX4 coil 100130 ms opening with LX4 coil
Mounting Support	Plate
Standards	IEC 60947-1 IEC 60947-4-1 EN 60947-1 JIS C8201-4-1 EN 60947-4-1
Product Certifications	UL LROS (Lloyds register of shipping) RINA DNV CCC BV CB ABS UKCA
Connections - Terminals	Power circuit bar 2 100 x 5 mm Power circuit bolted connection Control circuit screw clamp terminals 1 0.000.01 in ² (14 mm ²)flexible without cable end Control circuit screw clamp terminals 2 0.000.01 in ² (14 mm ²)flexible with cable end Control circuit screw clamp terminals 1 0.000.01 in ² (14 mm ²)flexible with cable end Control circuit screw clamp terminals 2 0.000.00 in ² (14 mm ²)flexible with cable end Control circuit screw clamp terminals 2 0.000.00 in ² (14 mm ²)solid without cable end Control circuit screw clamp terminals 1 0.000.01 in ² (14 mm ²) Control circuit screw clamp terminals 2 0.000.01 in ² (14 mm ²)
Tightening Torque	Power circuit 513.34 lbf.in (58 N.m) Control circuit 10.62 lbf.in (1.2 N.m)
Mechanical Durability	5 Mcycles
Inrush Power In Va	19002300 VA, 40400 Hz cos phi 0.9 (at 68 °F (20 °C))with LX1/LX9 coil 19602420 VA (at 68 °F (20 °C))with LX4 coil
Hold-In Power Consumption In Va	4455 VA, 40400 Hz cos phi 0.9 (at 68 °F (20 °C))with LX1/LX9 coil 4252 VA (at 68 °F (20 °C))with LX4 coil
Maximum Operating Rate	600 cyc/h 131 °F (55 °C)
Compatibility Code	LC1F

Environment

Ip Degree	Of F	Protection
-----------	------	------------

IP20 front face with shrouds IEC 60529 IP20 front face with shrouds VDE 0106

Protective Treatment	ТН
Ambient Air Temperature For Operation	23131 °F (-555 °C)
Ambient Air Temperature For Storage	-76176 °F (-6080 °C)
Permissible Ambient Air Temperature Around The Device	-40158 °F (-4070 °C)
Operating Altitude	9842.52 ft (3000 m) without derating
Mechanical Robustness	Vibrations contactor open2.5 Gn, 5300 Hz Vibrations contactor closed5.5 Gn, 5300 Hz Shocks contactor open5 Gn for 1/2 sine wave (11 ms) Shocks contactor closed15 Gn for 1/2 sine wave (11 ms)
Height	17.09 in (434 mm)
Width	27.64 in (702 mm)
Depth	10.04 in (255 mm)
Net Weight	105.82 lb(US) (48 kg)

Ordering and shipping details

Category	US10I1222336
Discount Schedule	0112
Gtin	3389110227239
Returnability	No
Country Of Origin	US

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.40 in (31.500 cm)
Package 1 Width	16.14 in (41.000 cm)
Package 1 Length	35.63 in (90.500 cm)
Package 1 Weight	90.39 lb(US) (41.000 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	2
Package 2 Height	29.53 in (75.000 cm)
Package 2 Width	31.50 in (80.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	220.46 lb(US) (100.000 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Circularity Profile	End of Life Information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Eu Rohs Directive	Compliant with Exemptions
Reach Regulation	REACh Declaration