## **Product data sheet**

Specifications





TeSys

Contactor

# Contactor, TeSys K, 3P, AC-3, It or eq to 440V 12 A, 1 NO aux., 220 to 230VAC coil

LC1K1210M7

Product availability: Stock - Normally stocked in distribution facility

Price\*: 86.00 USD

#### Main Range

**Product Or Component Type** 

[Ith] Conventional Free Air Thermal Current

Device Short Name	LC1K
Device Application	Control
Contactor Application	Motor control Resistive load
Complementary	
Utilisation Category	AC-3
	AC-3e
	AC-1
	AC-4
Poles Description	3P
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC <= 400 Hz
	Signalling circuit <= 690 V AC <= 400 Hz
[le] Rated Operational Current	12 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit
	12 A (at <140 °F (60 °C)) at <= 440 V AC AC-3e for power circuit
	20 A (at <140 °F (60 °C)) at <= 690 V AC AC-1 for power circuit
Control Circuit Type	AC 50/60 Hz
[Uc] Control Circuit Voltage	220230 V AC 50/60 Hz
Motor Power Kw	3 kW 220230 V AC 50/60 Hz AC-3
	5.5 kW 380415 V AC 50/60 Hz AC-3
	5.5 kW 440 V AC 50/60 Hz AC-3
	4 kW 690 V AC 50/60 Hz AC-3
	3 kW 220230 V AC 50/60 Hz AC-3e
	5.5 kW 380415 V AC 50/60 Hz AC-3e
	5.5 kW 440 V AC 50/60 Hz AC-3e
	4 kW 690 V AC 50/60 Hz AC-3e 3 kW 220230 V AC 50/60 Hz AC-4
	5.5 kW 380415 V AC 50/60 Hz AC-4
	5.5 kW 440 V AC 50/60 Hz AC-4
	4 kW 690 V AC 50/60 Hz AC-4
Auxiliary Contact Composition	1 NO
[Uimp] Rated Impulse Withstand Voltage	8 kV
Overvoltage Category	III

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

20 A (at 140 °F (60 °C)) for power circuit 10 A (at 122 °F (50 °C)) for signalling circuit

Irms Rated Making Capacity	144 A AC for power circuit conforming to IEC 60947 110 A AC for signalling circuit conforming to IEC 60947
Rated Breaking Capacity	110 A at 440 V conforming to IEC 60947
	80 A at 500 V conforming to IEC 60947
	70 A at 660690 V conforming to IEC 60947
[Icw] Rated Short-Time Withstand	115 A 122 °F (50 °C) - 1 s for power circuit
Current	105 A 122 °F (50 °C) - 5 s for power circuit
	100 A 122 °F (50 °C) - 10 s for power circuit 75 A 122 °F (50 °C) - 30 s for power circuit
	55 A 122 °F (50 °C) - 1 min for power circuit
	50 A 122 °F (50 °C) - 3 min for power circuit
	25 A 122 °F (50 °C) - >= 15 min for power circuit 80 A - 1 s for signalling circuit
	90 A - 500 ms for signalling circuit
	110 A - 100 ms for signalling circuit
Associated Fuse Rating	25 A gG at <= 440 V for power circuit
J	25 A aM for power circuit
	10 A gG for signalling circuit conforming to IEC 60947
	10 A gG for signalling circuit conforming to VDE 0660
Average Impedance	3 mOhm - Ith 20 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit 600 V UL 508
	Power circuit 690 V IEC 60947-4-1 Signalling circuit 690 V IEC 60947-4-1
	Signalling circuit 690 V IEC 60947-4-1
	Signalling circuit 600 V UL 508
	Power circuit 600 V CSA C22.2 No 14
	Signalling circuit 600 V CSA C22.2 No 14
Insulation Resistance	> 10 MOhm for signalling circuit
Inrush Power In Va	30 VA (at 68 °F (20 °C))
Hold-In Power Consumption In Va	4.5 VA (at 68 °F (20 °C))
Heat Dissipation	1.3 W
Control Circuit Voltage Limits	Operational: 0.81.15 Uc (at <122 °F (50 °C)) Drop-out: >= 0.20 Uc (at <122 °F (50 °C))
Connections - Terminals	screw clamp terminals 1 0.000.01 in² (1.54 mm²)solid
	screw clamp terminals 1 0.000.01 in² (0.754 mm²)flexible without cable end
	screw clamp terminals 1 0.000.00 in² (0.342.5 mm²)flexible with cable end screw clamp terminals 2 0.000.01 in² (1.54 mm²)solid
	screw clamp terminals 2 0.000.01 in² (0.754 mm²)flexible without cable end
	screw clamp terminals 2 0.000.00 in² (0.341.5 mm²)flexible with cable end
Maximum Operating Rate	3600 cyc/h
Auxiliary Contacts Type	Instantaneous 1 NO
Signalling Circuit Frequency	<= 400 Hz
Minimum Switching Current	5 mA for signalling circuit
Minimum Switching Voltage	17 V for signalling circuit
Mounting Support	Rail Plate
Tightening Torque	7.0811.51 lbf.in (0.81.3 N.m) screw clamp terminals Philips No 2
	7.0811.51 lbf.in (0.81.3 N.m) screw clamp terminals flat Ø 6 mm 7.0811.51 lbf.in (0.81.3 N.m) screw clamp terminals pozidriv No 2
Operating Time	1020 ms coil de-energisation and NO opening
. •	1020 ms coil energisation and NO closing
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1
• ····••	B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Non Overlap Distance	0.02 in (0.5 mm)
Mechanical Durability	10 Mcycles

Electrical Durability	1.3 Mcycles 12 A AC-3 <= 440 V
	1.3 Mcycles 12 A AC-3e <= 440 V
	0.3 Mcycles 20 A AC-1 <= 690 V
	0.02 Mcycles 72 A AC-4 <= 440 V
	0.02 Micycles 12 N/NO 4 1- 140 V
Mechanical Robustness	Shocks contactor closed, on X axis10 Gn for 11 ms IEC 60068-2-27
	Shocks contactor closed, on Y axis15 Gn for 11 ms IEC 60068-2-27
	Shocks contactor closed, on Z axis15 Gn for 11 ms IEC 60068-2-27
	Shocks contactor opened, on X axis6 Gn for 11 ms IEC 60068-2-27
	Shocks contactor opened, on Y axis10 Gn for 11 ms IEC 60068-2-27
	Shocks contactor opened, on Z axis10 Gn for 11 ms IEC 60068-2-27
	Vibrations contactor closed4 Gn, 5300 Hz IEC 60068-2-6
	Vibrations contactor opened2 Gn, 5300 Hz IEC 60068-2-6
	· · · · · · · · · · · · · · · · · · ·
Height	2.28 in (58 mm)
Width	1.77 in (45 mm)
Depth	2.24 in (57 mm)
Net Weight	0.40 lb(US) (0.18 kg)

#### **Environment**

Standards	EN/IEC 60947-4-1
	GB/T 14048.4
	UL 60947-4-1
	CSA C22.2 No 60947-4-1
	JIS C8201-4-1
Product Certifications	CB Scheme
	CCC
	UL
	CSA
	EAC
	CE
	UKCA
Ip Degree Of Protection	IP2X VDE 0106
Protective Treatment	TC IEC 60068
	TC DIN 50016
Ambient Air Temperature For Storage	-58176 °F (-5080 °C)
Operating Altitude	6561.68 ft (2000 m) without derating
Flame Retardance	V1 conforming to UL 94
	Requirement 2 conforming to NF F 16-101
	Requirement 2 conforming to NF F 16-102
	Requirement 2 conforming to NF F 16-102

## Ordering and shipping details

Category	US10l1222326
Discount Schedule	0112
Gtin	3389110733129
Returnability	Yes
Country Of Origin	ID

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5.000 cm)
Package 1 Width	2.36 in (6.000 cm)
Package 1 Length	2.56 in (6.500 cm)
Package 1 Weight	6.31 oz (179.000 g)

Unit Type Of Package 2	S02
Number Of Units In Package 2	50
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	20.27 lb(US) (9.193 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	800
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	341.91 lb(US) (155.088 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
<b>9</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
End of Life Information
WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov