# **Product data sheet**

Specification





# TeSys Deca reversing contactor - 3P(3 NO) - AC-3 - <= 440 V 12 A - 110 V DC coil

LC2D12FD

Product availability: Stock - Normally stocked in distribution

Price\*: 380.00 USD

#### Main

Range	TeSys TeSys Deca
Product Name	TeSys Deca TeSys Deca
Product Or Component Type	Reversing contactor
Device Short Name	LC2D
Contactor Application	Motor control Resistive load
Utilisation Category	AC-3 AC-1
Device Presentation	Preassembled with reversing power busbar
Poles Description	3P
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC
[le] Rated Operational Current	25 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit 12 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit
Motor Power Kw	3 kW at 220230 V AC 50 Hz 5.5 kW at 380400 V AC 50 Hz 5.5 kW at 415440 V AC 50 Hz 7.5 kW at 500 V AC 50 Hz 7.5 kW at 660690 V AC 50 Hz
Motor Power Hp (UI / Csa)	1 hp at 115 V AC 60 Hz for 1 phase motors 2 hp at 230/240 V AC 60 Hz for 1 phase motors 3 hp at 200/208 V AC 60 Hz for 3 phase motors 3 hp at 230/240 V AC 60 Hz for 3 phase motors 7.5 hp at 460/480 V AC 60 Hz for 3 phase motors 10 hp at 575/600 V AC 60 Hz for 3 phase motors
Control Circuit Type	DC standard
[Uc] Control Circuit Voltage	110 V DC
Auxiliary Contact Composition	1 NO + 1 NC
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947
Overvoltage Category	III
[Ith] Conventional Free Air Thermal Current	10 A (at 140 °F (60 °C)) for signalling circuit 25 A (at 140 °F (60 °C)) for power circuit
Irms Rated Making Capacity	250 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Rated Breaking Capacity	250 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand	30 A 104 °F (40 °C) - 10 min for power circuit
Current	61 A 104 °F (40 °C) - 1 min for power circuit
	105 A 104 °F (40 °C) - 10 s for power circuit
	210 A 104 °F (40 °C) - 1 s for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	40 A = 0 for signality a signality and supplies to IFO 00047 F.4
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 40 A gG at <= 690 V coordination type 1 for power circuit
	25 A gG at <= 690 V coordination type 1 for power circuit
Average Impedance	2.5 mOhm - Ith 25 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit 690 V IEC 60947-4-1
	Power circuit 600 V CSA
	Power circuit 600 V UL
	Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA
	Signalling circuit 600 V UL
	orginaling crodit coo v or
Electrical Durability	2 Mcycles 12 A AC-3 <= 440 V
	0.8 Mcycles 25 A AC-1 <= 440 V
Power Dissipation Per Pole	1.56 W AC-1
·	0.36 W AC-3
Front Cover	With
Interlocking Type	Mechanical
Mounting Support	Rail
mounting Support	Plate
Standards	CSA C22.2 No 14
	EN 60947-4-1
	EN 60947-5-1
	IEC 60947-4-1
	IEC 60947-5-1
	UL 508
	IEC 60335-1
Product Certifications	DNV
	CSA
	CCC
	UL
	GL
	LROS (Lloyds register of shipping)
	BV
	RINA GOST
	UKCA
Connections - Terminals	Power circuit screw clamp terminals 1 0.000.01 in² (14 mm²)flexible without
	cable end
	Power circuit screw clamp terminals 2 0.000.01 in <sup>2</sup> (14 mm <sup>2</sup> )flexible without cable end
	Power circuit screw clamp terminals 1 0.000.01 in² (14 mm²)flexible with cable
	end Power circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²)flexible with cable
	end
	Power circuit screw clamp terminals 1 0.000.01 in² (14 mm²)solid
	Power circuit screw clamp terminals 2 0.000.01 in² (14 mm²)solid
	Control circuit screw clamp terminals 1 0.000.01 in <sup>2</sup> (14 mm <sup>2</sup> )flexible without cable end
	Control circuit screw clamp terminals 2 0.000.01 in² (14 mm²)flexible without
	cable end  Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)flexible with cable
	end
	Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²)flexible with cable end
	Control circuit screw clamp terminals 1 0.000.01 in² (14 mm²)solid
	Control circuit screw clamp terminals 2 0.000.01 in² (14 mm²)solid

Tightening Torque	Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm	
	Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals that 9 0 mm	
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals 11mps No 2	
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals hat 2 5 mm	
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2	
	Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals pozidriv No 2	
Operating Time	53.5572.45 ms closing	
	1624 ms opening	
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1	
	B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1	
Mechanical Durability	30 Mcycles	
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)	

# Complementary

	-
Coil Technology	Built-in bidirectional peak limiting diode suppressor
Control Circuit Voltage Limits	0.10.25 Uc -40158 °F (-4070 °C) drop-out DC 0.71.25 Uc -40140 °F (-4060 °C) operational DC 11.25 Uc 140158 °F (6070 °C) operational DC
Time Constant	28 ms
Inrush Power In W	5.4 W 68 °F (20 °C))
Hold-In Power Consumption In W	5.4 W 68 °F (20 °C)
Auxiliary Contacts Type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Current	5 mA for signalling circuit
Minimum Switching Voltage	17 V for signalling circuit
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact     1.5 ms on energisation between NC and NO contact
Insulation Resistance	> 10 MOhm for signalling circuit

## **Environment**

Ip Degree Of Protection	IP20 front face IEC 60529
Climatic Withstand	IACS E10 IEC 60947-1 Annex Q category D
Protective Treatment	TH IEC 60068-2-30
Pollution Degree	3
Ambient Air Temperature For Operation	-40140 °F (-4060 °C) 140158 °F (6070 °C) with derating
Ambient Air Temperature For Storage	-76176 °F (-6080 °C)
Operating Altitude	09842.52 ft (03000 m)
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open2 Gn, 5300 Hz Vibrations contactor closed4 Gn, 5300 Hz Shocks contactor open10 Gn for 11 ms Shocks contactor closed15 Gn for 11 ms
Height	3.03 in (77 mm)
Width	3.54 in (90 mm)
Depth	3.74 in (95 mm)

## Ordering and shipping details

Category	US10I1222355
Discount Schedule	0112
Gtin	03389110392296
Returnability	No
Country Of Origin	SG

## **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.70 in (9.4 cm)
Package 1 Width	4.49 in (11.4 cm)
Package 1 Length	4.33 in (11 cm)
Package 1 Weight	25.75 oz (730 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	8
Package 2 Height	5.91 in (15 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	13.88 lb(US) (6.295 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	128
Package 3 Height	30.31 in (77 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	240.79 lb(US) (109.22 kg)

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>②</b>	Mercury Free	
	Rohs Exemption Information	Yes
	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov